



Ref. Certif. No.

ES1895

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

RESIDUAL CURRENT OPERATED CIRCUIT-BREAKER  
WITHOUT INTEGRAL OVERCURRENT PROTECTION  
(RCCB'S)

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS  
Electropole 38EQI Eybens - 31 Rue Pierre Mendes France  
30050 GRENOBLE CEDEX 9 (Francia)

Name and address of the manufacturer

SCHNEIDER ELECTRIC ESPAÑA, S.A.  
CM BARRANQUET, 57  
46133 MELIANA (Valencia - España)

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

SCHNEIDER ELECTRIC

Customer's Testing Facility (CTF) Stage used

Procedure CTF Stage 3

Model / Type Ref.

ID Resi9 XP / See Annex

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61008-2-1:1990  
IEC 61008-1:2010  
IEC 61008-1:2010/AMD1:2012  
IEC 61008-1:2010/AMD2:2013

As shown in the Test Report Ref. No. which forms part of this Certificate

GS118/17; GS50/17 UP TO GS58/17

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.  
Cl Génova, 6  
ES-28004 MADRID (SPAIN)

Date: 2017-09-07

Signature: Rafael GARCÍA  
Chief Executive Officer

# ANNEX TO CB CERTIFICATE N° ES1895

## CERTIFIED REFERENCES AND THEIR MAIN RATINGS

**Product:** RESIDUAL CURRENT OPERATED CIRCUIT-BREAKER WITHOUT INTEGRAL OVERCURRENT PROTECTION (RCCB'S)

**Trade mark:** SCHNEIDER ELECTRIC

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	I $\Delta$ m	I $m$	I $n$ c	I $\Delta$ c	Type	Additional information
IDSMR92P2530AC	2P	25 A	230/240 V~	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1) (3) (5)
IDSMR92P4030A	2P	40 A	230/240 V~	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(2) (4) (5)
IDSMR92P4030AC	2P	40 A	230/240 V~	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1) (3) (5)
IDSMR92P4030ASI	2P	40 A	230/240 V~	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	A-SI	(2) (4) (5)
IDSMR92P6330A	2P	63 A	230/240 V~	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	A	(2) (4) (6)
IDSMR92P6330AC	2P	63 A	230/240 V~	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2) (3) (6)
IDSMR94P4030A	4P	40 A	400/415 V~	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(2) (4) (5)
IDSMR94P4030AC	4P	40 A	400/415 V~	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2) (3) (5)
IDSMR94P6330A	4P	63 A	400/415 V~	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	A	(2) (4) (6)
IDSMR94P6330AC	4P	63 A	400/415 V~	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2) (3) (6)

- (1) Output terminal in Steel with tin coating Sn5
- (2) Output terminal in Copper with tin coating Sn5
- (3) Operating temperature range: -5/40°C
- (4) Operating temperature range: -25/40°C
- (5) Shall be back up protected by gG 50 A Fuse
- (6) Shall be back up protected by gG 100 A Fuse