# Preventa safety modules

For electrical monitoring of two-hand control stations

XPSBAE, XPSBCE, XPSBF

Catalog

October 2015







# How can you fit a 6000-page catalog in your pocket?

Schneider Electric provides you with the complete set of industrial automation catalogs all on a handy USB key for PC or in an application for tablets



## Digi-Cat, a handy USB key for PC





- > Convenient to carry
- > Always up-to-date
- > Environmentally friendly
- > Easy-to-share format



Contact your local representative to get your own Digi-Cat





## e-Library, the app for tablets

## If you have an iPad®:

- > Go to the App Store and search for e-Library
- > or scan the QR code





## If you have an Android tablet:

- > Go to the Google Play Store  $^{\!\mathsf{TM}}$  and search for eLibrary
- > or scan the QR code





# **General contents**

Preventa safety modules for electrical monitoring of two-hand control stations

	Type XPSBAE, electrical monitoring of two-hand control stations Operating principle, References	page 4
	Type XPSBCE,	
Fo	electrical monitoring of two-hand control stations Operating principle, References	page 5
	Гуре XPSBF,	
Fo	electrical monitoring of two-hand control statio <b>NS</b> Operating principle, References	page 6
	Product reference index	page 7

# Operating principle, selection, references

## Preventa safety modules

Type XPSBAE

For electrical monitoring of two-hand control stations



## **Operating principle**

Two-hand control stations are designed to provide protection against hand injury.

They require machine operators to keep their hands clear of the dangerous movement zone.

The use of two-hand control is an individual protective measure, which can safely protect only one operator. Separate two-hand control stations must be provided for each operator in a multiple-worker environment.

Safety modules **XPSBAE** for two-hand control stations comply with the requirements of European standard EN 574/ ISO 13851 for two-hand control systems.

The control stations must be designed and installed such that they cannot be activated involuntarily or easily rendered inoperative. Depending on the application, the requirements of type C standards specific to the machinery involved must be met (additional personal protection methods may have to be considered).

To initiate a dangerous movement, both operators (two-hand control pushbuttons) must be activated within an interval  $\leq 0.5$  s (synchronous activation). If one of the two pushbuttons is released during a dangerous operation, the control sequence is cancelled. Resumption of the dangerous operation is possible only if both pushbuttons are returned to their initial position and reactivated within the required time interval.

The safety distance between the control units and the hazardous zone must be sufficient to ensure that when only one operator is released, the hazardous zone cannot be reached before the dangerous movement has been completed or stopped.

#### Maximum achievable safety level

- PL c/Category 1 conforming to EN/ISO 13849-1
- SILCL1 conforming to EN/IEC 62061

#### **Product certifications**

- UI
- CSA
- TÜV

Selection						
Requirements of standard EN	Type I	Type II	Type III			
				Α	В	С
Standard EN 574/	Use of both hands (simultaneous action)					
ISO 13851 defines the	Link between input and output signals					
selection of two-hand controls according to its	Output signal inhibited					
behavior.	Prevention of accidental operation					
The following table details	Tamper-proof					
the 3 types of two-hand	Output signal reinitialised					
control conforming to EN	Synchronous action (specified time limit)					
574/ISO 13851. For each type, it lists the	Use of proven components (Category 1 conforming to EN/ISO 13849-1)			XPSBAE		
operating characteristics and minimum requirements.	Redundancy with partial error detection (Category 3 conforming to EN/ISO 13849-1)				XPSBCE XPSBF	
	Redundancy + Self-monitoring (Category 4 conforming to EN/ISO 13849-1)					XPSBCE XPSBF
	Two-hand control station	XY2SB	•			
	Conforming to standard EN/ISO 13849-1	574/ISO 1	Meets the	requireme	ents of star	ndard EN

Referenc	es						
Description	Type conforming to standard EN 574	Connection	Number of safety circuits	Additional outputs	Supply	Reference	Weight kg/ <i>Ib</i>
Safety modules for electrical monitoring of two-hand	IIIA	Captive screw clamp terminals Terminal block removable from module	1 NO	1 NC	$\sim$ and 24 V $\overline{\dots}$	XPSBAE5120P	0.100/ 0.220
control stations					∼ 115/230V	XPSBAE3920P	0.100/ 0.220
		Spring terminals Terminal block removable from module	1 NO	1 NC	∼ and 24 V ===	XPSBAE5120C	0.100/ 0.220
					∼ 115/230V	XPSBAE3920C	0.100/ 0.220





## Operating principle, selection. references

## Preventa safety modules

Type XPSBCE

For electrical monitoring of two-hand control stations



## **Operating principle**

Two-hand control stations are designed to provide protection against hand injury.

They require machine operators to keep their hands clear of the dangerous movement zone.

The use of two-hand control is an individual protective measure, which can safely protect only one operator. Separate two-hand control stations must be provided for each operator in a multiple-worker environment. Safety modules XPSBCE for two-hand control stations comply with the requirements of European standard EN 574/ISO 13851 for two-hand control systems.

The control stations must be designed and installed such that they cannot be activated involuntarily or easily rendered inoperative. Depending on the application, the requirements of type C standards specific to the machinery involved must be met (additional personal protection methods may have to be considered). To initiate a dangerous movement, both operators (two-hand control pushbuttons) must be activated within an interval ≤ 0.5 s (synchronous activation). If one of the two pushbuttons is released during a dangerous operation, the control sequence is cancelled. Resumption of the dangerous operation is possible only if both pushbuttons are returned to their initial position and reactivated within the required time interval.

The safety distance between the control units and the hazardous zone must be sufficient to ensure that when only one operator is released, the hazardous zone cannot be reached before the dangerous movement has been completed or stopped.

## Maximum achievable safety level

- PL e/Category 4 conforming to EN/ISO 13849-1
- SILCL3 conforming to EN/IEC 61508 and EN/IEC 62061


#### **Product certifications**

- UL
- CSA

References

BG

Selection						
Requirements of standard EN	Type I	Type II	Type III			
				Α	В	С
Standard EN 574/	Use of both hands (simultaneous action)					
ISO 13851 defines the	Link between input and output signals					
selection of two-hand controls according to its	Output signal inhibited					
behavior.	Prevention of accidental operation					
The following table details	Tamper-proof					
the 3 types of two-hand	Output signal reinitialised					
control conforming to EN	Synchronous action (specified time limit)					
574/ISO 13851. For each type, it lists the	Use of proven components (Category 1 conforming to EN/ISO 13849-1)			XPSBAE		
operating characteristics and minimum requirements.	Redundancy with partial error detection (Category 3 conforming to EN/ISO 13849-1)				XPSBCE XPSBF	
	Redundancy + Self-monitoring (Category 4 conforming to EN/ISO 13849-1)					XPSBCE XPSBF
	Two-hand control station	XY2SB	••			
	Conforming to standard EN/ISO 13849-1	574/ISO		requireme	ents of star	ndard EN







## Preventa safety modules

Type XPSBF

For electrical monitoring of two-hand control stations



## **Operating principle**

Two-hand control stations are designed to provide protection against hand injury.

They require machine operators to keep their hands clear of the dangerous movement zone.

The use of two-hand control is an individual protective measure, which can safely protect only one operator. Separate two-hand control stations must be provided for each operator in a multiple-worker environment.

Safety modules **XPSBF** for two-hand control stations comply with the requirements of European standard EN 574/ ISO 13851 for two-hand control systems.

The control stations must be designed and installed such that they cannot be activated involuntarily or easily rendered inoperative. Depending on the application, the requirements of type C standards specific to the machinery involved must be met (additional personal protection methods may have to be considered).

To initiate a dangerous movement, both operators (two-hand control pushbuttons) must be activated within an interval  $\leq 0.5$  s (synchronous activation). If one of the two pushbuttons is released during a dangerous operation, the control sequence is cancelled. Resumption of the dangerous operation is possible only if both pushbuttons are returned to their initial position and reactivated within the required time interval.

The safety distance between the control units and the hazardous zone must be sufficient to ensure that when only one operator is released, the hazardous zone cannot be reached before the dangerous movement has been completed or stopped.

#### Maximum achievable safety level

- PL e/Category 4 conforming to EN/ISO 13849-1
- SILCL3 conforming to EN/IEC 61508 and EN/IEC 62061

#### **Product certifications**

- UL
- CSA
- TÜV

Requirements of standard EN	Type I	Type II	Type III			
				Α	В	С
Standard EN 574/	Use of both hands (simultaneous action)					
ISO 13851 defines the	Link between input and output signals					
selection of two-hand controls according to its	Output signal inhibited					
behavior.	Prevention of accidental operation					
The following table details	Tamper-proof					
the 3 types of two-hand	Output signal reinitialised					
control conforming to EN	Synchronous action (specified time limit)					
574/ISO 13851. For each type, it lists the	Use of proven components (Category 1 conforming to EN/ISO 13849-1)			XPSBAE		
operating characteristics and minimum requirements.	Redundancy with partial error detection (Category 3 conforming to EN/ISO 13849-1)				XPSBCE XPSBF	
	Redundancy + Self-monitoring (Category 4 conforming to EN/ISO 13849-1)					XPSBCE XPSBF
	Two-hand control station	XY2SB	•			
	Conforming to standard EN/ISO 13849-1	Meets the requirements of standard E 574/ISO 13851				ndard EN

Referenc	es						
Description	Type conforming to standard EN 574	Connection	Number of safety circuits	Additional outputs	Supply	Reference	Weight kg/ <i>Ib</i>
Safety modules for electrical monitoring of two-hand control	III C	Captive screw clamp terminals Terminal block removable from module	2 NO	2 solid-state	24 V	XPSBF1132	0.150/ 0.331
stations			2 NO	2 solid-state	24 V	XPSBF1132P	0.150/ 0.331



## **Product reference index**

XPSBAE3920C	4
XPSBAE3920P	4
XPSBAE5120C	4
XPSBAE5120P	4
XPSBCE3110C	5
XPSBCE3110P	5
XPSBCE3410C	5
XPSBCE3410P	5
XPSBCE3710C	5
XPSBCE3710P	5
XPSBF1132	6
YPSRF1132P	6



## More information on http://www.schneider-electric.com/machinesafety

#### **Schneider Electric Industries SAS**

Head Office 35, rue Joseph Monier F-92500 Rueil-Malmaison France The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Design: Schneider Electric Photos: Schneider Electric