



Ref. Certif. No.

ES2051

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	TYPE F AND B RESIDUAL CURRENT OPERATED CIRCUIT-BREAKER WITHOUT INTEGRAL OVERCURRENT PROTECTION FOR HOUSEHOLD AND SIMILAR USES
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 35, RUE JOSEPH MONIER 92506 RUEIL MALMAISON CEDEX (France)
Name and address of the manufacturer	SCHNEIDER ELECTRIC ESPAÑA, S.A. CM BARRANQUET, 57 46133 MELIANA (Valencia - Spain)
Name and address of the factory	SAME AS ABOVE
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Annex
Trademark (if any)	SCHNEIDER ELECTRIC
Customer's Testing Facility (CTF) Stage used	CTF State 3
Model / Type Ref.	See Annex
Additional information (if necessary may also be reported on page 2)	<input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61008-2-1:1990 IEC 61008-1:2010 IEC 61008-1:2010/A1:2012 IEC 61008-1:2010/A2:2013 IEC 62423:2009
As shown in the Test Report Ref. No. which forms part of this Certificate	GS06 /18, GS8/18, GS7/18

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.  
CI Génova, 6  
ES-28004 MADRID (SPAIN)

Date: 2018-07-27

Signature:   
Rafael GARCÍA MEIRO  
Chief Executive Officer

# ANNEX TO CB CERTIFICATE N° ES2051

## CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

### PRODUCT: TYPE F AND B RESIDUAL CURRENT OPERATED CIRCUIT-BREAKER WITHOUT INTEGRAL OVERCURRENT PROTECTION FOR HOUSEHOLD AND SIMILAR USES

Trade mark: Schneider Electric

Type Ref.	Type	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	I $\Delta$ m	I $m$	I $n$ c	I $\Delta$ c	Additional information
IDS MR92P 6330FSI	F-SI	2P	63 A	230/240 V~	30 mA	50 Hz	630 A	630 A	3 kA	3 kA	Fuse 100 A, gG; (2) (4)
IDS MR94P 6330FSI	F-SI	4P	63 A	400/415 V~	30 mA	50 Hz	630 A	630 A	3 kA	3 kA	Fuse 100 A, gG; (2) (4)

(2) Output terminal in Copper with tin coating Sn5

(4) -25/40°C