

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product Circuit-breakers for overcurrent protection for household and similar installations

Name and address of the applicant SCHNEIDER ELECTRIC INDUSTRIES SAS
31 rue Pierre Mendès France, Eybens
F-38050 Grenoble Cedex 9
France

Name and address of the manufacturer SCHNEIDER ELECTRIC INDUSTRIES SAS
31 rue Pierre Mendès France, Eybens
F-38050 Grenoble Cedex 9
France

Name and address of the factory

Note: When more than one factory, please report on page 2

Additional information on page 2

SCHNEIDER ELECTRIC HUNGÁRIA VILLAMOSSÁGI ZRT.
Hock János utca 55
8900 Zalaegerszeg
Hungary

Ratings and principal characteristics

3P+N – Ue = 400 V – 50-60 Hz – Icn = 3000 A
Curve B, C or D – In = 6, 10, 13, 16, 20, 25 or 32 A
(see Additional Sheet and page 5 of Test Report No. PB18-0024952-01-00)

Trademark (if any)



Schneider Electric

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

Series Resi9 XP
(see Additional Sheet and page 9 of Test Report No. PB18-0024952-01-00)

Additional information (if necessary may also be reported on page 2)

Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60898-1:2002, IEC 60898-1:2002/AMD1:2002, IEC 60898-1:2002/AMD2:2003

National differences:

EU Group Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

PB18-0024952-01-00 and from PB18-0024952-01-01 to PB18-0024952-01-21

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43, IT-I-20138 Milano, Italy



Description of the circuit-breakers for overcurrent protection series Resi9 XP ($I_{cn} = 3000 \text{ A}$)

Curve	Rated current	Generic reference
B	6 A	R9XPQPN3B06
	10 A	R9XPQPN3B10
	13 A	R9XPQPN3B13
	16 A	R9XPQPN3B16
	20 A	R9XPQPN3B20
	25 A	R9XPQPN3B25
	32 A	R9XPQPN3B32
C	6 A	R9XPQPN3C06
	10 A	R9XPQPN3C10
	13 A	R9XPQPN3C13
	16 A	R9XPQPN3C16
	20 A	R9XPQPN3C20
	25 A	R9XPQPN3C25
	32 A	R9XPQPN3C32
D	6 A	R9XPQPN3D06
	10 A	R9XPQPN3D10
	13 A	R9XPQPN3D13
	16 A	R9XPQPN3D16
	20 A	R9XPQPN3D20
	25 A	R9XPQPN3D25
	32 A	R9XPQPN3D32