

Life Is On Schneid

IN THE

### High Fidelity Dynamic Simulation for Engineering & Operator Training Solutions

DYNSIM Dynamic Simulation<sup>•</sup> is a comprehensive, dynamic process simulator that enables users to meet and beat the dynamic challenges of designing and operating a modern process plant safely and profitably. By assisting in process design, controls checkout and control system design, DYNSIM Dynamic Simulation enables process yield improvement and reduction of capital investment costs. The DYNSIM Dynamic Simulation operator training simulator provides safer operation while improving performance and productivity.

DYNSIM Dynamic Simulation is now available via the cloud in addition to the traditional on-premise access method.

High Fidelity Dynamic Simulation for Engineering & Operator Training Solutions

#### Summary

State-of-the-art, field-proven dynamic process simulation program. Unified process plant modeling environment covers the entire lifecycle of the plant, from simulation through system checkout, operator training and start up. DYNSIM Dynamic Simulation is available online anywhere, anytime via Schneider Electric's cloud platform.

#### **Business Value**

- Meet and beat the dynamic challenges of designing and operating a process plant safely and profitably
- Reflects the combined experience of over 100 process plants worldwide, saving you time and increasing ROI
- Preserve the equity you have by leveraging and reusing model designs in any product such as DYNSIM Dynamic Simulation and PRO/II<sup>®</sup> Process Engineering
- DYNSIM Dynamic Simulation is the first commercially available dynamic process simulator bringing Increased Accessibility, Enhanced Availability, & Lower Cost of Ownership to the powerful DYNSIM Dynamic Simulation application

### Setting New Standards for Rigor, Robustness, Openness, Ease of Use

Process plants face the same real-world challenges to operational excellence that their predecessors did, but the stakes today are higher than ever before. The constantly changing nature of plants, and their internal and external environments, can threaten safe, profitable plant operations. Uncontrolled upsets can cause start-up delays, production outages, severe equipment damage, and even catastrophic failures.

DYNSIM Dynamic Simulation is a state-of-the-art, field-proven dynamic process simulation program. DYNSIM Dynamic Simulation enables you to meet and beat the dynamic challenges of designing and operating a modern process plant safely and profitably. DYNSIM Dynamic Simulation is an advanced, unified process plant modeling environment for use throughout a plant's lifecycle:

- Rigorous dynamic process simulation for engineering design
- High Fidelity modeling used for control system checkout
- Rigorous process modeling for Operator Training for first time startup
- Plant performance and operation improvement tool for operating plants

DYNSIM Dynamic Simulation offers a cost-effective, professional grade alternative to other commercial dynamic simulation products. Over 100 plants around the world have already used DYNSIM Dynamic Simulation to satisfy their process design, operator training, and operational analysis requirements in the upstream, gas processing/LNG, Refining, Petrochemical, and Chemical industries. The combination of industry experience, proven technology and service expertise can give you the right tools to achieve and maintain optimal control of your plant.

DYNSIM Dynamic Simulation is now available via the cloud in addition to the traditional on-premise access method. Our cloud access has not only many benefits over on-premise access, but also over other products with cloud access, due to platform technology developed with simulation users in mind.

- Increased efficiency due to the ability to adapt to changing needs by scaling up or down the computing power with varying number of machines of instances or simulation templates for engineering test or training scenarios.
- A secure user access control that allows the administrator to add & delete users or edit privileges as needed.
- Simplified IT overhead since the product is on pure on-demand cloud machines via a secure URL, new versions available as soon as they are released.
- Seamless Collaboration by splitting the content from the product allowing the content, such as simulation models, to be managed easily with file history log in a central repository.
- Flexible Usage and Pricing with a pure SaaS business model based on hourly usage.

High Fidelity Dynamic Simulation for Engineering & Operator Training Solutions

#### Industries Served

- Oil & Gas processing / LNG
- Refining
- Petrochemicals and Chemicals
- Engineering & Construction / Consulting

#### **Benefits Summary**

- Reduce the cost of process equipment designed to meet transient requirements
- Increase plant safety by evaluating flare and relief systems
- Validate process control strategy to reduce risk during abnormal events
- Evaluate plant start-up and shut-down procedures and operation to reduce the risk of startup delays
- Validate operation to prevent production interruptions and increase plant performance efficiency
- Evaluate Batch operations from dry startup
- Provide operator training simulator, process modeling, engine & instructor station interface

#### Simulation Applications

- Distillation tower relief analysis to accurately set flare capacity
- Compressor surge studies to reduce the possibility of damage to rotating equipment
- Cryogenic depressuring to determine low temperature metallurgy requirements
- Boiler draft studies to assess the risk of furnace implosion
- Refinery steam system analysis to improve reliability

### The Perfect Dynamic Simulation and Training Tool for Engineers and Operators

#### Scalability Protects Your Investment in DYNSIM Dynamic Simulation

DYNSIM Dynamic Simulation is unique in its ability to seamlessly scale from engineering design applications to control checkout and operator training, all within the same graphical user environment. Its modular architecture and open interfaces ensure that DYNSIM Dynamic Simulation meets all your simulation requirements throughout the lifecycle of your plant.

#### Import Existing PRO/II Simulations

DYNSIM Dynamic Simulation preserves the equity you have built in any existing PRO/II model. DYNSIM Dynamic Simulation can translate a steady-state PRO/II simulation into a running dynamic simulation to eliminate tedious data reentry and preserve the thermodynamic methods that you trust. All that is required is to complete the process control strategy to operate the plant.

#### First Principles Equipment Models Ensure Accuracy and Robustness

DYNSIM Dynamic Simulation's first principles models, including rigorous thermodynamic and fluid flow calculations, bring a superior level of robustness and accuracy to dynamic process simulation at your plant. DYNSIM Dynamic Simulation rigorously handles even the most complex plant layouts and systems, using a robust and high performance solution algorithm. Furthermore, DYNSIM Dynamic Simulation robustly models cold startup from purged conditions to normal operation and then back to shutdown.

#### Connect with DCS and PLC Control Systems

DYNSIM Dynamic Simulation takes full advantage of modern, open software standards to interface with other important plant applications, such as DCS and PLC control system emulators. DYNSIM Dynamic Simulation also connects easily with control system emulators (such as Foxboro Evo" Simulation and Triconex Control Simulation) to drive operator training systems with a rigorous simulation foundation. DYNSIM Dynamic Simulation provides an open API to connect any third-party simulation system.

#### **Runtime Licenses**

DYNSIM Dynamic Simulation is available in runtime licenses to reduce OTS deployment costs. Runtime licenses provide the full power of the operating model but restrict the modification of the simulation database that defines the process model. The Engineer environment access mode is disabled during instructor, administrator, and operator environments.



High Fidelity Dynamic Simulation for **Engineering & Operator Training Solutions** 

#### Unit Operation / Models

#### **Process Models**

- Source
- Relief Valve
- Drum
- Separator with Weir
- Reciprocating Compressor
- Multi Stream LNG Exchanger
- Fired Heater with refractory
- Slate Change
- OLGA Send/Receive

- Mixer / Splitter
- Distillation Tower w/packing
- Pump with NPSH
- Centrifugal Compressor
- Utility Exchanger (Air cooler)
- Segmented Pipe w/Sonic Flow

- Valve
- Header
- Atmospheric Tank
- Gas Expander and Turbines
- Rotating Equipment Shaft
- Heat Exchanger
- Plug Flow Reactors
- Stream Send/Receive

Voltage Transformer

#### **Electrical Models**

- Bus
- Power Source/Sink
- · Electrical Load

#### **Control Models**

- And
- Summation
- PID Controller
- · Lead/Lag
- Counter
- Timer

- Function Generator
- Or
- Surge Controller
- Pulse Positioner
- Custom Logic

Master

Motor

- Latch
- Calculation
- Dual Input Switch Timer
- Rate Limiter

- Circuit Breaker
- Circuit Disconnect

- Stream Set

Schneider Flectric

Combustor

- Sink

High Fidelity Dynamic Simulation for **Engineering & Operator Training Solutions** 

#### Thermodynamics

**Component Systems** 

#### Acids Alcohols • Amides Aromatic hydrocarbons • Elements • Esters • Ethers Ketones • Naphthenic hydrocarbons • Paraffinic hydrocarbons · Salts and minerals Sulfur derivatives Unsaturated hydrocarbons Thermodynamic Systems • Braun K10 (BK10) • Peng-Robinson (PR) • Grayson-Streed (GS) Glycol Redlich-Kwong Sour Water

• Two Bluck Coon

• SRK-Kabadi-Danner (SRKKD)

- SRK
- Steam Tables Scientific
- Steam Tables Industrial

- · Aldehydes
- · Halogenated derivatives
- Other nitrogen derivatives
- Silicon derivatives
- Soave-Redlich-Kwong (SRK)
- PR-Panagiotopoulos-Reid (PRP)
- PR-Modified Panagiotopolous-Reid (PRM)
- SRK-Modified Panagiotopoulos-Reid (SRKM)
- SRK-Panagiotopoulos-Reid (SRKP)

High Fidelity Dynamic Simulation for Engineering & Operator Training Solutions

#### System

#### Features

- Add C++ user added models
- Online help and search
- Color coded input guidance
- Disable any unit operation or flowsheet
- · Flowsheet interactive control widgets
- Add equations to model parameters

#### Instructor Features

- Administrator, engineer, instructor, and operator access modes
- Integrated model building graphical user interface
- Built in Control cross-referencing
- Snapshots for initial conditions and backtracks

- · Scenarios, trends, and profile plots
- Trainee performance monitoring
- Built-in model malfunctions
- Remote Functions/Field Operated Devices

#### Connectivity

- SPT OLGA
- Foxboro Evo Simulation (for Foxboro Evo)
- PRO/II Process Engineering Translator

- Microsoft Excel<sup>®</sup>
- OPC
- Triconex Control Simulation 
  Customized Solutions

High Fidelity Dynamic Simulation for Engineering & Operator Training Solutions



High Fidelity Dynamic Simulation for Engineering & Operator Training Solutions

#### **Dynamic Simulation Suite**

DYNSIM Dynamic Simulation is part of the Dynamic Simulation Suite (DSS) of products. DSS provides full-power rigorous dynamic simulation for plant engineers, operators, and managers to use in optimizing plant operations and design. DSS is comprised of DYNSIM Dynamic Simulation, Foxboro Control Simulation, Triconex Control Simulation, and Operator Training programs; offering a professional grade alternative to dated, fragmented and hard-to-use products with which many plants currently struggle. All DSS products can communicate with each other, allowing a perfect combination to suit your exact plant requirements.



26561 Rancho Pkwy South, Lake Forest, CA 92630 Phone: +1 (949)-727-3200 software.schneider-electric.com