

NOTIFICATION OF TEST RESULTS

Reference: CCA/B20/2010

Product: isolating switches

Tested by request of: Schneider Electric Industrie SAS
31, rue Pierre Mendès France, Eybens
38050 GRENOBLE CEDEX 09
France

Manufactured at (name and place): Schneider Electric NV/SA
Dieweg 3
1180 BRUSSEL
Belgium

Rating and principal characteristics: See page 2

Preliminary visit carried out by: SGS Belgium NV - Division SGS CEBEC
Riverside Business Park
Bld. Internationalelaan 55, Build. D
1070 BRUSSELS
Belgium

Trade mark (if any): SCHNEIDER ELECTRIC

Model/Type ref: Series I

Additional information (if any): See page 2 / WMT-procedure

A sample of the product has been tested and found to be in conformity with the current (HD/EN and equivalent national standard, number and edition)


EN 60947-3:1999 + A1:2001-04 + A2:2005

as shown in the test reports 58295601/00 up to 58295601/06

This notification of test results is the result of testing a sample of the product submitted, in accordance with the provisions of the relevant specific standard.

This Notification of Test Results has been established by a body which participates directly in the CENELEC Certification Agreement (CCA) of September 11th, 1973 as revised on March 29th, 1983, on September 3rd, 2004 and on April 18th, 2007 (including addendum 1 dated July 1984, addendum 2 dated March 1987, addendum 3 dated September 1989 and addendum 4 dated March 1995). Any other body participating in the CCA will take this Notification as a basis for granting a national mark of conformity or a national approval as specified in the CCA.

Brussels, 13/07/2010


G. LANA,
Certification Manager



Ratings:

number of poles	:	1, 2, 3 & 4
rated voltage (Un)	:	250 Vac (1P) and 415 Vac (2P, 3P & 4P)
rated current (In)	:	40 A up to 125 A
utilization category	:	AC22A
rated insulation voltage (Ui)	:	500 V
rated impulse withstand voltage (Uimp)	:	6 kV under frame / 4 kV
rated conditional short-circuit current	:	5 kA for all, excepted 4,5 kV for 2P 125 A
SCPD	:	fuse type gG
rated frequency	:	50 Hz / 60 Hz
degree of protection	:	IP 40 under frame / IP 20
method of actuating	:	tumbler
method of application	:	semi flush-type, DIN rail
terminals	:	screw-type

3 1 2 3 4 5



Product References:

References	Number of Pole	Rated current (A)	Rated Voltage (V)
15024	1	40	250V
15013	1	63	250V
15090	1	100	250V
15057	1	125	250V
15020	2	40	415V
15014	2	63	415V
15091	2	100	415V
15058	2	125	415V
15023	3	40	415V
15015	3	63	415V
15092	3	100	415V
15059	3	125	415V
15019	4	40	415V
15016	4	63	415V
15093	4	100	415V
15060	4	125	415V