


# LICENCE

No. 21142

Issued to:  
 Applicant:  
**Schneider Electric Industries SAS**  
 31, rue Pierre Mendès France, Eybens  
 38050 GRENOBLE CEDEX 09  
 France

Licensee:  
**Schneider Electric NV/SA**  
 Dieweg 3  
 1180 BRUSSEL  
 Belgium



Product : contactors  
 Trade name(s) : SCHNEIDER ELECTRIC  
 Type(s)/model(s) : Series ICT Hog (see appendix)

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 12


SGS CEBEC hereby grants the right to use the CEBEC certification mark  
 The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on: 18/02/2019

*p.o. Etienne Thibaut*

ir. C. Lana,  
 Certification Manager

© Only integral publication of this certificate, including the annex, is allowed  
 This certificate is only valid combined with the publication on the following web address: [www.sgs.com/ee](http://www.sgs.com/ee)



## SPECIFICATION OF THE CERTIFIED PRODUCT

### Product data

Product	:	contactors
Trade name(s)	:	SCHNEIDER ELECTRIC
Type(s)/Model(s)	:	Series ICT Hog (see appendix)
number of poles	:	3P+N
rated operational voltage (Ue)	:	400 VAC
rated current (In)	:	40 A up to 63 A
type of switch mechanism	:	Permanent
design of the switch	:	Electromagnetic-contactor
rated control circuit voltage (Ucoil)	:	230/240 V
kind of energization of the control circuit	:	AC
rated insulation voltage (Ui)	:	500 V
utilization category	:	AC7a / AC7b
rated making capacity	:	40 A up to 63 A AC7a / 15 A up to 20 A AC7b
rated breaking capacity	:	40 A up to 63 A AC7a / 15 A up to 20 A AC7b
rated conditional short-circuit current	:	3 kA
SCPD	:	Fuses gG 63A
contact opening (gap)	:	Normal gap
protection against electric shock	:	Unenclosed
protection against harmful ingress of water	:	IP 20
pollution degree	:	2
rated impulse withstand voltage (Uimp)	:	2,5 kV
method of actuating	:	with and without lever
method of operation	:	automatic
method of application	:	Din rail type
type of terminals	:	screw-type

### Additional information

See Appendix

**TESTS**

**Test requirements**

NBN EN 61095 based on EN 61095:2009

**Test results**

The test results are laid down in certification file ref.630162/01

**Remarks**

This certificate is based on certificate ref. STR-FR\_1033 and test reports ref. 98945-596122A, 98945-596122A1 to A28 , 60059447-560109B, 60059447-560109B1 to B18, 148454-703121, 157312-725716, 157312-725716A, 157312-725716B.

**Conclusion**

The examination proved that all certification requirements were met.

Reviewed by, project leader : Luigi Zanutto - 18/02/2019

Certification Manager : *Ehene Thibaut*

*[Signature]*  
2019-02-18

**FACTORY LOCATION(S)**

Schneider Electric Industries SAS (France)  
20, rue de la Croix Blanche  
PO Box 15  
86361 CHASSENEUIL DU POITOU CEDEX  
France

**Electromechanical contactors: Series iCT Hog**

Reference	Contacteur Type	I <sub>e</sub> AC7a (A)	I <sub>e</sub> AC7b (A)	NO contact	NC contact	U <sub>s</sub> min (V)	U <sub>s</sub> max (V)	Frequency (Hz)
A9C22740	Standard	40	15	0	4	230	240	50
A9C22763	Standard	63	20	0	4	230	240	50
A9C24740	Standard	40	15	4	0	230	240	50
A9C24763	Standard	63	20	4	0	230	240	50