


# LICENCE

No. 16741

Issued to:  
Applicant:  
**Schneider Electric Industrie SAS**  
31, rue Pierre Mendès France, Eybens  
38050 GRENOBLE CEDEX 09  
France



Licensee:  
**Schneider Electric NV/SA**  
Dieweg 3  
1180 BRUSSEL  
Belgium

Product : isolating switches  
Trade name(s) : SCHNEIDER ELECTRIC  
Type(s)/model(s) : Series I

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:


- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 12

SGS CEBEC hereby grants the right to use the CEBEC certification mark  
The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on: 13/07/2010

ir. C. Lana,  
Certification Manager

© Only integral publication of this certificate, including the annex, is allowed  
This certificate is only valid combined with the publication on the following web address: [www.sgs.com/ee](http://www.sgs.com/ee)



SGS Belgium NV-Division SGS CEBEC  
Business Riverside Park  
Bid Internationalelaan 55 Build. D  
B-1070 Brussels  
Tel.+32(0)2 556 00 20 Fax.+32(0)2 556 00 36

This certificate is issued by the company under its General Conditions for Certification Services accessible at [http://www.sgs.com/terms\\_and\\_conditions.htm](http://www.sgs.com/terms_and_conditions.htm). Attention is drawn to the limitations of liability defined therein and in the Test Report herein mentioned which findings are reflected in this Certificate. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	:	isolating switches
Trade name(s)	:	SCHNEIDER ELECTRIC
Type(s)/Model(s)	:	Series I
number of poles	:	1, 2, 3 & 4
rated voltage (Un)	:	250 Vac (1P) and 415 Vac (2P, 3P & 4P)
rated current (In)	:	40 A up to 125 A
utilization category	:	AC22A
rated insulation voltage (Ui)	:	500 V
rated impulse withstand voltage (Uimp)	:	6 kV under frame / 4 kV
rated conditional short-circuit current	:	5 kA for all, excepted 4,5 kV for 2P 125 A
SCPD	:	fuse type gG
rated frequency	:	50 Hz / 60 Hz
degree of protection	:	IP 40 under frame / IP 20
method of actuating	:	tumbler
method of application	:	semi flush-type, DIN rail
terminals	:	screw-type

**Additional information**

See Appendix

**TESTS****Test requirements**

NBN EN 60947-3 based on EN 60947-3:1999 + A1:2001-04 + A2:2005

**Test results**

The test results are laid down in test report(s) ref. 58295601/00 up to 58295601/06


**Conclusion**

The examination proved that all test requirements were met.

Checked by, project leader : Silvjo Piras - 13/07/2010

Department Manager,  
Product Certification :

Certification Manager :

A handwritten signature in black ink, which appears to be 'L. Piras', is written over the colon for the Department Manager and Certification Manager. To the right of the signature, the date '2010-07-14' is handwritten.

**FACTORY LOCATION(S)**

Schneider Electric NV/SA  
Dieweg 3  
1180 BRUSSEL  
Belgium

Product References:

References	Number of Pole	Rated current (A)	Rated Voltage (V)
15024	1	40	250V
15013	1	63	250V
15090	1	100	250V
15057	1	125	250V
15020	2	40	415V
15014	2	63	415V
15091	2	100	415V
15058	2	125	415V
15023	3	40	415V
15015	3	63	415V
15092	3	100	415V
15059	3	125	415V
15019	4	40	415V
15016	4	63	415V
15093	4	100	415V
15060	4	125	415V