

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Class I LED luminaire for fixed installation
Name and address of the applicant	SCHNEIDER ELECTRIC ESPANA S A C/LLOBREGAT 15 MOLINS DE REI 08750 SPAIN
Name and address of the manufacturer	SCHNEIDER ELECTRIC ESPANA S A C/LLOBREGAT 15 MOLINS DE REI 08750 SPAIN
Name and address of the factory	NINGBO QIYUANLIGHTING TECH CO. LTD NO.238 HENANGU CHAIQIAO BEILUN NINGBO, ZHEJIANG, 315800 CHINA
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	120-230 V~ 50/60 Hz 10 W Class I IP20
Trademark (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	NSYLAMLDS <input checked="" type="checkbox"/> Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	<input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60598-1:2014, IEC 60598-2-1:1979/AMD1:1987, IEC 60598-2-1:1979, IEC 60598-1:2014/AMD1:2017
As shown in the Test Report Ref. No. which forms part of this Certificate	4789846060.1-1 issued on 2021-05-21

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-05-31

Signature:
Jan-Erik Storgaard

Additional Model(s):

The main model:

Type ref.	Ratings	Details
NSYLAMLDS	120-230 V~ 50/60 Hz 10 W Class I IP20	With auxiliary socket outlet SHUKO

extends the following models:

Type ref.	Ratings	Details
NSYLAMLDF	120-230 V~ 50/60 Hz 10 W Class I IP20	With auxiliary socket outlet UTE
NSYLAMLDB	120-230 V~ 50/60 Hz 10 W Class I IP20	With auxiliary socket outlet UK

May be provided with the following accessories for supply connection or interconnection:

Type ref.	Description
NSYLAM3M	Supply cable
NSYLAM1M	Interconnecting cable
NSYLAM1MUL	Interconnecting cable

Additionally evaluated to:

 EN 60598-1:2015, EN 60598-1:2015/A1:2018, EN 60598-2-1:1989
 National differences specified in the CB Test Report


Additional information (if necessary)


- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

 For full legal entity names see www.ul.com/ncbnames

Date: 2021-05-31

Signature:



Jan-Erik Storgaard