

LICENCE

No. 16745

Issued to:
Applicant:
Schneider Electric Industrie SAS
31, rue Pierre Mendès France, Eybens
38050 GRENOBLE CEDEX 09
France



Licensee:
Schneider Electric NV/SA
Dieweg 3
1180 BRUSSEL
Belgium

Product : switches for household and similar fixed-electrical installations
Trade name(s) : SCHNEIDER ELECTRIC
Type(s)/model(s) : A9S61120 & A9S61132

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.


SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 12

SGS CEBEC hereby grants the right to use the CEBEC certification mark


The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on: 13/07/2010



ir. C. Lana,
Certification Manager

© Only integral publication of this certificate, including the annex, is allowed
This certificate is only valid combined with the publication on the following web address: www.sgs.com/ee



SGS Belgium NV-Division SGS CEBEC
Business Riverside Park
Bld Internationalelaan 55 Build. D
B-1070 Brussels
Tel.+32(0)2 556 00 20 Fax.+32(0)2 556 00 36

This certificate is issued by the company under its General Conditions for Certification Services accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitations of liability defined therein and in the Test Report herein mentioned which findings are reflected in this Certificate. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

| | | |
|-----------------------|---|---|
| Product | : | switches for household and similar fixed-electrical installations |
| Trade name(s) | : | SCHNEIDER ELECTRIC |
| Type(s)/Model(s) | : | A9S61120 & A9S61132 |
| pattern no(s). | : | 1 |
| rated voltage (Un) | : | 250 Vac |
| rated current (In) | : | 20 A , 32 A |
| method of actuating | : | tumbler |
| method of application | : | semi flush-type |
| terminals | : | srew-type |
| other characteristics | : | with pilot lamp |

TESTS

Test requirements

NBN EN 60669-1 based on EN 60669-1:1999 + A1:2002

Test results

The test results are laid down in test report(s) ref. 58182302/00 and 58182301/00 up to 58182301/01


Conclusion

The examination proved that all test requirements were met.

Checked by, project leader : Silvio Piras - 13/07/2010

Department Manager,
Product Certification :

Certification Manager :



2010-07-14

FACTORY LOCATION(S)

Schneider Electric NV/SA
Dieweg 3
1180 BRUSSEL
Belgium