

# CERTIFICATE

Issued to:  
Applicant:  
**Schneider Electric España, S.A.U.**  
**Camino Barranquet 57**  
**46133 Meliana, Spain**

Licensee:  
**Schneider Electric Industries SAS Electropole**  
**38EQI**  
**Rue Francois Quesnay**  
**38320 Eybens, France**

Product : Residual current operated circuit-breakers with integral overcurrent protection (RCBOs)  
Trade name(s) : SCHNEIDER ELECTRIC  
Type(s)/model(s) : Acti9 and Resi9

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:

- a type test according to EN 61009-1:2012, EN 61009-1:2012/A1:2014, EN 61009-1:2012/A2:2014, EN 61009-1:2012/A11:2015, EN 61009-1:2012/A12:2016, EN 61009-1:2012/A13:2021, EN 61009-2-1:1994 and EN 61009-2-1:1994/A11:1998
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 6067469


DEKRA hereby grants the right to use the DEKRA Mark.

The DEKRA Mark may be applied to the product as specified in this certificate for the duration and under the conditions of the DEKRA Mark certification agreement.

This certificate is issued on 3 March 2026 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-171721

DEKRA Certification B.V.



B.T.M. Holtus  
Managing Director



Susan Lehner  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



71-171721

**DEKRA Mark is the new KEMA-KEUR**

The DEKRA Mark certificate for this product is to all intents and purposes equivalent to a KEMA-KEUR certificate, the other certification mark used by DEKRA and should be valued and used as such. DEKRA Mark is gradually replacing KEMA-KEUR.

For more information please check: [Introducing DEKRA Mark](#)

**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	: Residual current operated circuit-breakers with integral overcurrent protection (RCBOs)
Trade name(s)	: SCHNEIDER ELECTRIC
Type(s)/model(s)	: Acti9 and Resi9
Number of poles	: 1P+N
Rated residual operating current (I <sub>dn</sub> )	: 30 mA
Rated voltage (U <sub>n</sub> )	: 230 Vac
Rated frequency	: 50 Hz
Time-delay	: without time delay
Behaviour in presence of d.c. components	: A
Method of mounting	: panel board (distribution board)
Instantaneous tripping overcurrent	: B, C
Energy limiting class	: 3
Degree of protection	: IP20
Rated impulse withstand voltage (U <sub>imp</sub> )	: 4 kV
Method of operation	: independent of line voltage
Reference ambient air temperature	: 30 °C
Ambient temperature	: -25 °C to +40 °C
Distance "a" (grid)	: 35 mm
Type of terminal	: pillar terminals

**Product data – type Acti9**

Rated current (I <sub>n</sub> )	: 10 A, 16 A, 20 A, 25 A, 32 A
Rated short-circuit capacity (I <sub>cn</sub> )	: 4500 A, 6000 A
Rated service short-circuit capacity (I <sub>cs</sub> )	: 4500 A, 6000 A
Rated residual making and breaking capacity (I <sub>Δm</sub> )	: 4500 A, 6000 A

**Product data – type Resi9**

Rated current (I <sub>n</sub> )	: 10 A, 13 A, 16 A
Rated short-circuit capacity (I <sub>cn</sub> )	: 6000 A
Rated service short-circuit capacity (I <sub>cs</sub> )	: 6000 A
Rated residual making and breaking capacity (I <sub>Δm</sub> )	: 6000 A

**TESTS****Test requirements**

EN 61009-1:2012  
EN 61009-1:2012/A1:2014  
EN 61009-1:2012/A2:2014

EN 61009-1:2012/A11:2015  
EN 61009-1:2012/A12:2016  
EN 61009-1:2012/A13:2021  
EN 61009-2-1:1994  
EN 61009-2-1:1994/A11:1998

**Test result**

The test results are documented in DEKRA test file 230474100.

**Conclusion**

The examination has confirmed that all requirements were met.

**Factory location**

Schneider Electric España, S.A.U.  
Camino Barranquet 57  
46133 Meliana, Spain

Model	Dimension	Commercial Reference	In (A)	Curve	lcn / lcs / lΔm (A)
Resi9	91 mm	R9DX01610	10	B	6000
Resi9	91 mm	R9DX01613	13	B	6000
Resi9	91 mm	R9DX01616	16	B	6000
Resi9	91 mm	R9DX55610	10	C	6000
Resi9	91 mm	R9DX55613	13	C	6000
Resi9	91 mm	R9DX55616	16	C	6000
Acti9	96 mm	A9DXC3610	10	C	6000
Acti9	96 mm	A9DXC3616	16	C	6000
Acti9	96 mm	A9DXC3620	20	C	6000
Acti9	96 mm	A9DXC3625	25	C	6000
Acti9	96 mm	A9DXC3632	32	C	6000
Acti9	96 mm	A9DXF3610	10	C	6000
Acti9	96 mm	A9DXF3616	16	C	6000
Acti9	96 mm	A9DXF3620	20	C	6000
Acti9	96 mm	A9DXF3625	25	C	6000
Acti9	96 mm	A9DXG3610	10	B	6000
Acti9	96 mm	A9DXG3616	16	B	6000
Acti9	96 mm	A9DXC2610	10	C	4500
Acti9	96 mm	A9DXC2616	16	C	4500
Acti9	96 mm	A9DXC2620	20	C	4500
Acti9	96 mm	A9DXC2625	25	C	4500
Acti9	96 mm	A9DXC2632	32	C	4500
Acti9	96 mm	A9DXG2610	10	B	4500
Acti9	96 mm	A9DXG2616	16	B	4500