



CCA Statement of Test Results (STR)

030/ES0152-M2-AENOR

AENOR states that by request of:

SCHNEIDER ELECTRIC INDUSTRIES SAS

registered office 35, RUE JOSEPH MONIER RUEIL MALMAISON CEDEX (Francia)

a sample of the product **Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBO's)**

has been tested and found to be in conformity with the standards

UNE-EN 61009-1:2013 (EN 61009-1:2012)
UNE-EN 61009-1:2013/A1:2015 (EN 61009-1:2012/A1:2014)
UNE-EN 61009-1:2013/A2:2015 (EN 61009-1:2012/A2:2014)
UNE-EN 61009-1:2013/A11:2016 (EN 61009-1:2012/A11:2015)
UNE-EN 61009-1:2013/A12:2016 (EN 61009-1:2012/A12:2016)
UNE-EN 61009-1:2013/A13:2022 (EN 61009-1:2012/A13:2021)
UNE-EN 61009-2-1:1996 (EN 61009-2-1:1994)
UNE-EN 61009-2-1/A11:1999 (EN 61009-2-1/A11:1998)

Test reports GS06/26 EMC, GS06/26, GS07/25-M1, GS07/26, GS08/26, GS11/25-M1, GS16/25-M1 to GS26/25-M1, GS385/26-M1 Head Report, GS535/25-M1 EMC, GS535/25-M1, 305068-TL3-0, 305068-TL3-1, 305068-TL7-2, SPEC25AA5848_v4, SPEC25AA5849_v2, SPEC25AA5850_v2, SPEC25AA5851_v3, SPEC25AA5852_v2 to SPEC25AA5859_v2, SPEC25AA5862_v3, SPEC25AA5864_v2, SPEC25AA5865_v3, SPEC26AA0653_v1 EMC

References Specified in Annex to the Certificate

Production site Camino BARRANQUET, 57 46133 MELIANA (Valencia - España)

Certification scheme This Statement of Test Results is the result of testing a sample of the product submitted, in accordance with the provisions of the relevant specific standard.

This Statement of Test Results has been established by a body which participates in the CENELEC Certification Agreement (CCA) of 11th September 1973 as revised on March 29th, 1983 and September 3rd, 2004. Any other body participating in the CCA may recognize this Statement as a basis for granting a national mark of conformity or a national approval as specified in OD 6, List of current decisions of CCA Group, point 2.11.

This certificate supersedes 030/ES0152-M1-AENOR, dated 2025-09-24

First issued on 2026-04-22

Rafael GARCÍA MEIRO
CEO





CCA Statement of Test Results (STR)

030/ES0152-M2-AENOR

Annex to Certificate

Trade mark: SCHNEIDER ELECTRIC

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual operating current	Rated short-circuit capacity	Rated residual making and breaking capacity	Tripping current	Type	Energy limiting class	Additional information
45A9DX1PN96B10A30mAA	1P+N	10 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B13A30mAA	1P+N	13 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B16A30mAA	1P+N	16 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B20A30mAA	1P+N	20 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B25A30mAA	1P+N	25 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B32A30mAA	1P+N	32 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96C10A30mAA	1P+N	10 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C10A30mAAC	1P+N	10 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C10A300mAA	1P+N	10 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C10A300mAAC	1P+N	10 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C13A30mAA	1P+N	13 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C13A30mAAC	1P+N	13 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C13A300mAA	1P+N	13 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C13A300mAAC	1P+N	13 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C16A30mAA	1P+N	16 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C16A30mAAC	1P+N	16 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C16A300mAA	1P+N	16 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C16A300mAAC	1P+N	16 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C20A30mAA	1P+N	20 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C20A30mAAC	1P+N	20 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C20A300mAA	1P+N	20 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C20A300mAAC	1P+N	20 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C25A30mAA	1P+N	25 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C25A30mAAC	1P+N	25 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C25A300mAA	1P+N	25 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C25A300mAAC	1P+N	25 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C32A30mAA	1P+N	32 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C32A30mAAC	1P+N	32 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C32A300mAA	1P+N	32 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C32A300mAAC	1P+N	32 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
6A9DS1PN91B10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 91mm
6A9DS1PN91B13A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 91mm
6A9DS1PN91B16A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 91mm
6A9DS1PN91C13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 91mm
6A9DS1PN91C16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 91mm
6A9DX1PN96B10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96B13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96B16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm

First issued on 2026-04-22



AENOR CONFÍA S.A.U.
 Génova, 6. 28004 Madrid. España
 Tel. 91 432 60 00.- www.aenor.com



CCA Statement of Test Results (STR)

030/ES0152-M2-AENOR

Annex to Certificate

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual operating current	Rated short-circuit capacity	Rated residual making and breaking capacity	Tripping current	Type	Energy limiting class	Additional information
6A9DX1PN96B20A30mAA	1P+N	20 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96B25A30mAA	1P+N	25 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96B32A30mAA	1P+N	32 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96C10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C10A30mAAC	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C10A300mAA	1P+N	10 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C10A300mAAC	1P+N	10 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C13A30mAAC	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C13A300mAA	1P+N	13 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C16A30mAAC	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C16A300mAA	1P+N	16 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C16A300mAAC	1P+N	16 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C20A30mAA	1P+N	20 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C20A30mAAC	1P+N	20 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C20A300mAA	1P+N	20 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C20A300mAAC	1P+N	20 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C25A30mAA	1P+N	25 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C25A30mAAC	1P+N	25 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C25A300mAA	1P+N	25 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C25A300mAAC	1P+N	25 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C32A30mAA	1P+N	32 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C32A30mAAC	1P+N	32 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C32A300mAA	1P+N	32 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C32A300mAAC	1P+N	32 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6R9DS1PN91C10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 91mm
6R9DX1PN91B10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Resi9 91mm
6R9DX1PN91B13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Resi9 91mm
6R9DX1PN91B16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Resi9 91mm
6R9DX1PN91C10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Resi9 91mm
6R9DX1PN91C13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Resi9 91mm
6R9DX1PN91C16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Resi9 91mm

Temperature of use:

- -5°C to 40°C for Type AC
- -25°C to 40°C for Type A

First issued on 2026-04-22



AENOR CONFÍA S.A.U.
 Génova, 6. 28004 Madrid. España
 Tel. 91 432 60 00.- www.aenor.com