



Modicon M171 / M172 / M173

Logic controllers for HVAC and Pumping applications



Modicon

Discover [Modicon](#)

Edge control for industrial internet of things (IoT)

Modicon IIoT-native edge controllers manage complex interfaces across assets and devices or directly into the cloud, with embedded functional safety and cybersecurity. Modicon provides performance and scalability for a wide range of industrial applications up to high-performance multi-axis machines and high-available redundant processes.

Explore our offer

- [Modicon HVAC Controllers](#)
- [Modicon PLC](#)
- [Modicon Motion Controllers](#)
- [Modicon PAC](#)
- [Modicon Edge I/O](#)
- [Modicon I/O](#)
- [Modicon Networking](#)
- [Modicon Power Supply](#)
- [Modicon Wiring](#)
- [Modicon Safety](#)

Life Is On

Schneider
Electric


Quick access to product information

Get technical information about your product

References

Modicon TM3 I/O expansion modules for Modicon controllers
Analog I/O modules


References	Modicon TM3 analog input modules	Input range	Resolution	Input terminal block (T)	Reference	Weight (kg)
2 voltage/current inputs	-10...+10 VDC 0...+10 VDC 0...20 mA / -20 mA	16 bits of	0.001	TM3AI201	0.150	
		16 bits of sign	0.002	TM3AI202	0.150	
4 voltage/current inputs	-10...+10 VDC 0...+10 VDC 0...20 mA / -20 mA	12 bits of	0.001	TM3AI401	0.200	
		11 bits of sign	0.002	TM3AI402	0.200	
4 voltage/current or temperature inputs (I, K, R, S, E, T, N, E, C)	-10...+10 VDC 0...+10 VDC 0...20 mA / -20 mA	16 bits of	0.001	TM3AI401	0.200	
		11 bits of sign	0.002	TM3AI402	0.200	
4 differential temperature inputs (I, K, R, S, E, T, N, E, C)	-10...+10 VDC 0...+10 VDC 0...20 mA / -20 mA	16 bits of	0.001	TM3AI401	0.200	
		11 bits of sign	0.002	TM3AI402	0.200	
4 voltage/current	-10...+10 VDC	16 bits of	0.001	TM3AI401	0.200	
		11 bits of sign	0.002	TM3AI402	0.200	




Each commercial reference presented in a catalog contains a hyperlink. Click on it to obtain the technical information of the product:

- Characteristics, Dimensions and drawings, Mounting and clearance, Connections and schemas, Performance curves
- Product image, Instruction sheet, User guide, Product certifications, End of life manual

Find your catalog



- > With just 3 clicks, you can access the Industrial Automation and Control catalogs, in both English and French
- > Consult digital automation catalogs at [Digi-Cat Online](#)




- Up-to-date catalogs
- Embedded product selectors, 360° pictures
- Optimized search by commercial references

Select your training



- > Find the right [Training](#) for your needs on our Global website
- > Locate the training center with the selector tool, using this [link](#)



Life Is On

Schneider Electric

General content

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

■ Introduction to EcoStruxure Machine HVAC	page 2
■ General overview	
- Maximize business and machine Performance.....	page 4
- Flexible.....	page 5
- Efficient.....	page 6
- Connected, Cybersecurity	page 7
- Modicon M171/M172/M173 range.....	page 8
- System components.....	page 9
- Configuration software.....	page 10
- Ethernet connection.....	page 11
- Architectures	page 12 & 13
<i>General selection: logic controllers.....</i>	<i>page 14 & 15</i>
■ Modicon M173 Optimized logic controllers	
<i>Selection guide: controllers and remote displays</i>	<i>page 16 & 17</i>
- Presentation, Description	page 18
- References.....	page 19
■ Modicon M172 logic controllers	
<i>Selection guide: controllers and remote displays</i>	<i>page 20 & 21</i>
□ Controllers	
- Presentation	page 22
- Description	page 23
- References.....	page 24 and 25
□ I/O Expansion modules	
- Presentation, Description	page 26
- References.....	page 27
□ Remote displays	
- Presentation, Description	page 28
- References.....	page 29
■ Modicon M171 Optimized logic controllers	
<i>Selection guide of controllers and remote displays</i>	<i>page 30 & 31</i>
□ Controllers	
- Presentation, Description	page 32
- References.....	page 33
□ I/O Expansion modules	
- Presentation, Description, References	page 34
□ Remote displays, Connection accessories	
- Presentation, References.....	page 35
■ Modicon M171 Performance logic controllers	
□ Controllers	
- Presentation, Description	page 36
- References.....	page 37
□ I/O Expansion modules	
- Presentation, Description	page 38
- References.....	page 39
■ Secure Interfaces	
- Presentation, Description	page 40
- References.....	page 41
■ Communication modules	
- Presentation, Description	page 42
- References.....	page 43
■ Electronic expansion valve drivers	
- Presentation, Description	page 44
- References.....	page 45
■ Measurement accessories: Temperature & Humidity control	page 46
■ Compatibility with Variable speed drives and machines	page 47
■ EcoStruxure™ Machine Expert – HVAC programming software	
- Presentation, Characteristics.....	page 48
- Product offer, References	page 49
■ Product reference index.....	page 50

Our solution for Smart HVAC Control Systems

EcoStruxure™ Machine, our open, interoperable, IoT-enabled system architecture, helps OEMs quickly build smarter cost-optimized HVAC control systems with onboard energy-efficiency solutions while reducing maintenance and improving reliability. EcoStruxure Machine encompasses key technologies for product technology and edge control on premises, using cloud technologies to provide analytics and digital services.

EcoStruxure™ Machine



Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Maximize business and machine performance with EcoStruxure™ Machine

Maximize business and machine performance with EcoStruxure Machine


To be competitive in today's digital era, machine builders must be innovative. Smart machines, those that are better connected, more flexible, more efficient, and safe, are enabling machine builders to innovate in ways never before possible.

- > EcoStruxure Machine™, our open, interoperable, IoT-enabled system architecture, helps you build smarter machines and equipment faster, making your business more efficient, profitable, and sustainable.
- > EcoStruxure Machine combines key on-premises technologies for product connectivity and edge control with cloud technologies to provide analytics and digital services.
- > EcoStruxure Machine helps you bring more innovation and added value to your customers throughout the entire machine life cycle.

Ready-to-use architectures and function blocks

- > Tested, Validated, and Documented Architectures (TVDA) are just one way we reduce design time.
- > Whether machines are simple or complex, Application Function Blocks (AFBs) make system design fast and easy.

Modicon M171/M172/M173 is part of EcoStruxure Machine



HVAC/Chiller/Modbus SL/Modicon M172 Performance logic controller

Solution breakdown

- | | |
|--|--|
| 1 Compact NSX circuit breaker | 10 Modicon M171 remote display |
| 2 iEM3000 energy meter | 11 Harmony XALK Emergency stop push button |
| 3 TeSys Deca contactor | 12 TeSys Deca magnetic circuit breaker |
| 4 Multi9 circuit breaker | 13 TeSys Deca contactor |
| 5 Modicon Power supply | 14 Altivar 212 variable speed drive , for 0.75 to 75 kW (1.0 to 100 hp) motors |
| 6 Multi9 circuit breaker | 15 Modicon TM1S humidity and temperature probes |
| 7 Modicon M172 IIoT Secure Interface | 16 Pressure transmitter |
| 8 Modicon M172 performance logic controller | 17 Electronic expansion valve |
| 9 Modicon M172 Electronic expansion valve driver module for single valve | 18 Harmony XB4, Harmony XB5 signaling units |

Flexible

Flexible and scalable Performance

Whether you specialize in chillers, Air Handling Units for commercial buildings, residential, industrial and Pumping applications, etc.

With the Modicon M171/M172/M173 range, EcoStruxure Machine is well-positioned.

Multiple BMS (Building Management System) connectivity, embedded or as an option, and an embedded web server make remote control and remote access simple to implement. A unique software environment supports the development of algorithms and functions that can be used on any platform.



M172 Performance and Optimized



M173 Optimized



M171 Optimized

Performance and connectivity

- > **M173 and M171 Optimized:** logic controllers for simple and compact machines, also available for flush mounting, they requires minimal installation time and offers tremendous versatility. M173 provide high level of field connectivity.
- > **M172 Performance and Optimized:** logic controllers for any size of connectable or connected HVAC machine: manage small to large HVAC machines, and boosters for buildings, connectable to BMS or the cloud.



- > Best-in-class versatility and compact size
- > Best-in-class Performance

Efficient

Everything needed is embedded

The high degree of flexibility makes it very easy to install additional modules and still keep everything in just one configuration:


- > IIoT Edge unit (1)
- > Controllers
- > Remote displays
- > Expansion modules
- > Communication modules
- > Wide range of humidity and temperature probes

IIoT Secure Interfaces	Logic controllers	Remote displays	I/O Expansion modules Communication modules	Measurement accessories
 <p>IIoT Plug-in</p> <p>IIoT Gateway</p>	 <p>M172: for any size of connectable or connected machine</p>  <p>M173 Optimized: for compact and efficient machines</p>  <p>M171 Optimized: for simple and compact machines</p>			 <p>Temperature sensors</p> <p>Humidity and temperature sensors</p>

(1) IIoT: Industrial Internet of Things.

Intuitive automation with EcoStruxure Machine Expert - HVAC

- > EcoStruxure Machine Expert - HVAC is the universal programming software for machines automated by Modicon M171, M172 and M173 logic controllers
- > Simplified navigation that requires only a few clicks delivers a more efficient engineering process
- > EcoStruxure Machine Expert - HVAC simplifies each of the steps in machine design and commissioning



Connected



Connected everywhere

Depending on your connectivity needs, select the right product

> **M172 Secure Interfaces:**

- FTPs
- HTTPs
- SMTPs
- SNMT
- MQTT
- Cybersecure VPN

> **M172 Optimized and M172 Performance:**

- Modbus RTU
- Modbus TCP
- BACnet MS/TP (B-AAC Profile certified BTL)
- BACnet /IP (B-AAC Profile certified BTL)
- ASCII support for GSM Modem
- CAN Expansion Bus
- LonWorks (FFT-10)
- Webserver, FTP Client/Server, Email, Proxy management, Allow list, SNTP

> **M173 Optimized:**

- Modbus RTU
- CAN Expansion Bus
- LAN Expansion Bus

> **M171 Optimized:**

- Modbus RTU
- LAN Expansion Bus

Customization and services

Our experts help you every step of the way, from perfecting machine design to on-site servicing of the finished machine

- > Global support, 24/7 hotline services, and replacement parts centers around the world enable you to deliver superior customer support and satisfaction

Fully customized solution and co-design with our Application Design Experts (ADE)

- > Design an optimized solution for your machine to create added value, with the help of our experienced ADEs

Turnkey control panel

- > Engineering expertise for codes and standards compliance
- > Custom engineering to provide the optimum solution and meet specific needs

Collaboration from design to commissioning

- > Recruited directly from the industries they serve, ADEs collaborate with you from design through to programming, as well as in the commissioning of turnkey installations

Expert support throughout your system's life cycle

- > A dedicated team of Schneider Electric application design experts provides worldwide support for your HVAC solution

Cybersecure



Cybersecurity fo HVAC systems

IIoT-enabled systems are exposed to other devices and networks, which potentially increases the risk of cyberattacks and data privacy breaches.

HVAC machine builders need to implement mechanisms and cybersecurity best practices

- > Ensure data protection: Authentication - Authorization - Encryption
- > Prohibit unauthorized access: violations, logging, and notification
- > Comply with evolving regulations: IEC 62443 standard for cybersecure control system components

Our cybersecurity solutions

- > Secure Development Life Cycle Process (SDL)
- > A framework for secure product design
- > Allows the controller to connect to secured networks

VPN (Virtual Private Network)

- > Enables a secure connection to the cloud
- > Alternative to a more complex and expensive gateway

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Modicon M171/M172/M173 range

Modicon M171/M172/M173 range

The range has been developed to manage digital and analog inputs and outputs for controlling HVAC machines, Pumping applications, and to offer numerous possibilities for connection to different Building Management System communication networks.

- The offer is made up of:
 - several types of controller depending on the requested performance and connectivity
 - a variety of communication modules to connect them to the BMS
 - Secure Interfaces (Plug and Use IIoT Gateway) to perform Cybersecure communications based on HTTPs and TLS
 - a choice of expansion modules to increase and adapt the number and type of I/O
 - monochrome and color displays
 - EcoStruxure Machine Expert - HVAC, the dedicated software used to program, commission and debug applications
 - and a set of sensors.

Applications

- M173 logic controllers are suitable for:
 - Heat pumps (up to two circuits)
 - Process chillers
 - Pumping
 - Boilers/Heaters
 - and any small and compact machines
- M171 and M172 logic controllers are suitable for:
 - Air/water-cooled chiller
 - Rooftop unit
 - Heat pump
 - Compressor rack
 - Ventilation unit
 - Precision air conditioner
 - Heat recovery unit
 - Air handling unit
 - Small chillers (up to two circuits)
 - Process chillers

- The offer is flexible and scalable, depending on the application requirements.

Any existing controller can evolve later as all M171, M172, and M173 logic controllers are programmed with the same EcoStruxure Machine Expert - HVAC software.

- M171 Optimized logic controllers: up to 44 I/O, when only Modbus SL is needed
- M173 Optimized logic controllers: from 22 I/O (stand alone) to 78 I/O (with expansion modules)
- M172 logic controllers: from 7 to 238 I/O (with expansion modules)



HVAC



Heat pump






Chiller




Pumping



Air handling unit



EcoStruxure Machine Expert - HVAC programming software



Measurement accessories

System components

M171, M172 and M173 logic controllers are available with or without an embedded display, with or without SSR output depending on the base product.

- M171 and M172 logic controllers, are available in both an Optimized and Performance version
- M173 logic controllers are available in Optimized version
- M172 Performance controllers embed connectivity, and M172 Optimized controllers offer optional connectivity.
- I/O expansion modules are mixed digital and analog I/O types

■ **M173 Optimized** logic controllers, and **TM173DLED** remote display see [page 18](#), and **TM172E●●R** I/O expansion module, see [page 26](#)

■ **M172 Optimized** and **M172 Performance** logic controllers, see [page 22](#) and **TM172E●●R** I/O expansion module, see [page 26](#) and **TM172DC●●●●** remote color touch screen displays, see [page 28](#)

■ **M171 Optimized** logic controllers, see [page 32](#) and **TM171E●●R** I/O expansion modules, see [page 34](#) and **TM171D●●●●** remote displays, see [page 35](#)

■ **M171 Performance** logic controllers, see [page 36](#) and **TM171EP●●R** I/O expansion modules, see [page 38](#)

■ **TM172SI●** Secure Interfaces, designed to establish secure internet connections with Plug-in and Gateway versions, see [page 40](#)

■ **TM171A●●●●** communication modules (BMS fieldbus Interfaces) provide the **M171 Performance**, **M172 Optimized**, **M172 Performance**, and **M173 Optimized** logic controllers with a connection to:

- BACnet MS/TP (B-AAC profile) or IP
- Modbus SL (Serial Link)
- Modbus TCP
- LonWorks (FFT-10)
- Profibus
- CAN bus

See [page 42](#)

■ **TM172EVEV●●**: electronic expansion valve drivers compatible with **M172** and **M173 Optimized** logic controllers, and also with third party controllers and electronic expansion valves, see [page 44](#)

■ **TM171VEVM4**: an autonomous expansion valve driver compatible with **M171**, **M172** logic controllers, and also with third party controllers and electronic expansion valves, see [page 44](#)

■ Specific measurement accessories **TM1S●●●●**: humidity and temperature probes, see [page 46](#)


■ EcoStruxure Machine Expert - HVAC programming software, and programming accessories, see [page 48](#)

■ Adapted connection accessories: I/O connectors and cables, see [page 35](#)

(1) Remote display can also be used with M171 Optimized with embedded display.



EcoStruxure Machine Expert - HVAC



5 languages compliant with IEC 61131-3

Configuration software

M171, M172 and M173 logic controllers are supported by an intuitive software package: EcoStruxure Machine Expert - HVAC, see [page 48](#).

This software follows a simple drag-and-drop function block approach to configuration and is completed with a library of Application Function Blocks (AFBs) and logic functions.


EcoStruxure Machine Expert - HVAC uses five languages compliant with IEC 61131-3.

Examples:


```

1: case stateDelay of
2:   (* ON *)
3:   if start then
4:     stateDelay := 1;
5:     mod_1;
6:   (* OFF--OFF *)
7:   stateDelay := 0;
8:   if stop then
9:     stateDelay := 0;
10:  end if;
11:  stateDelay := delayOn-TIME_ERROR then
12:    stateDelay := 0;
13:  end if;
14:  if not stop then
15:    stateDelay := 1;
16:    stateDelay := delayOn-TIME_ERROR then
17:      stateDelay := 0;
18:    end if;
19:  end if;
20:  stateDelay := 0;
21:  end case;
22:  mod_1;
  
```

Structured Text language (ST)



Function Block Diagram language (FBD)




Ladder Diagram language (LD)

```


11: LD in
12: JHPC 10
13: LD 0
14: ST et
15: LD sysTimer
16: ST start
17: LD FALSE
18: ST q
19: RET
20:
21: LD et
22: GE pt
23: ST q
24: RETC
25:
26: LD sysTimer
27: SUB start
28: ST et
29: GE pt
30: ST q
  
```

Instruction List language (IL)




Sequential Function Chart language (SFC)

	Logic controller type			
	M173 Optimized	M172 Optimized and Performance	M171 Optimized	M171 Performance
CPU	160 MHz	120 MHz, 32 MB RAM	14.7 MHz	72 MHz, 32 MB RAM
Available memory for application	1.0 MB	1.0 MB	188 kB	1.0 MB
Available memory for user Interface	– (Shared with application)	1.5 MB	–	1.5 MB
Flash memory data	– (External flash memory is not available to the user)	5 MB	–	126 MB
RAM memory (automatic mapping)	378 kB	512 kB (256000 words)	2048 B (1024 words)	512 kB (256000 words)
RAM memory (Modbus mapping)	10 kB (5000 words)	10 kB (5000 words)	1024 B (512 words)	10 kB (5000 words)
Parameters	10 kB (5000 words)	–	–	–
EEPROM variables	–	28 kB (14000 words)	1024 B (512 words)	28 kB (14000 words)



M172 Performance logic controllers linked to Ethernet via the embedded RJ45 ports

AVEVA



M172 Optimized, M173 Optimized, and M171 Performance logic controllers managed by AVEVA industrial software via the Secure Interface (IloT gateway)

Ethernet connection

Ethernet access is:

- embedded in M172 Performance logic controllers
- optional with M173 Optimized, M171 Performance, and M172 Optimized logic controllers by means of a communication module or Secure Interface (IloT gateway)

Ethernet access enables several functions, such as:

- HTTP Webserver (Webvisu)
- Remote access
 - Download program
 - Display program download
 - Download, upload parameters
 - Download firmware
 - Debug
 - File management
- Bridge: a specific function allowing controllers connected in Modbus SL to the same controller to be programmed via Modbus
- FTP client/server

These services are not always available:

- The service can be enabled or disabled via the controller programming
- An allowlist is used to provide access (no allowlist defined by default)

Logic controllers for compact and efficient machines

M173 Optimized logic controllers




- 1 **TM173DLED** remote display, see [page 16](#)
- 2 **TM173O** logic controller, see [page 16](#)
- 3 **TM172SIG** Secure Interface, see [page 40](#)
- 4 **TM173O** logic controller, see [page 16](#)

- 5 **TM172E12R** I/O expansion module (12 I/O in 4 DIN), see [page 26](#)
- 6 **Altivar 212** variable speed drive (1)
- 7 **TM1SH●●** humidity sensor, see [page 47](#)
- 8 **TM1ST●●** temperature sensor PT1000 or NTC, see [page 46](#)

Logic controllers for simple and compact machines

M171 Optimized logic controllers




- 1 **TM171PFE03** Performance logic controller, see [page 37](#)
- 2 **TM171OFM22R** Optimized logic controller - flush mounting, see [page 33](#)
- 3 **TM171EO●●** I/O expansion module, see [page 38](#)
- 4 **TM171DLED** remote display, see [page 35](#)

- 5 **TM171DLCD2U** remote display, see [page 35](#)
- 6 **TM171DWAL●●** remote wall mounting display, see [page 35](#)
- 7 **Altivar 212** variable speed drive (1)
- 8 **TM1SH●●** humidity sensor, see [page 47](#)
- 9 **TM1ST●●** temperature sensor PT1000 or NTC, see [page 46](#)

(1) Consult this offer on our website www.se.com

Logic controllers for any size of connectable or connected HVAC machines

M172 logic controllers



- 1 **TM172DCLF** flush mounting display, see [page 28](#)
- 2 **spaceLYnk gateway** (1)
- 3 **Harmony STO/STU HMI** (1)
- 4 **TM172SIG** Secure Interface see [page 40](#)
- 5 **TM171OD** Optimized logic controller (18 I/O in 4 DIN), see [page 33](#)
- 6 **TM172PB** Performance logic controller (7 or 18 I/O in 4 DIN), see [page 25](#)
- 7 **TM172PD** Performance logic controller (28 or 42 I/O in 8 DIN), see [page 25](#)
- 8 **TM172E12R** I/O expansion module (12 I/O in 4 DIN), see [page 26](#)
- 9 **TM172E28R** I/O expansion module (28 I/O in 4 DIN), see [page 26](#)
- 10 **TM172DCLWT** wall mounting remote display, see [page 28](#)
- 11 **TeSys Deca** circuit-breakers (1)
- 12 Solid state relays, Electromechanical relays (1)
- 13 Pressure transmitter (third-party product)
- 14 **TM1ST** temperature sensor PT1000 or NTC, see [page 46](#)
- 15 SPD310 Differential pressure sensor (1)
- 16 **H721LC-S6** current transducer (1)
- 17 **iEM 3000** energy meter (1)
- 18 **Altivar 212** variable speed drive (1)
- 19 **TM171VEVM4** electronic expansion valve driver, see [page 44](#)
- 20 **SE8000** room controller (thermostat) (1)
- 21 **TM1SH** humidity sensor, see [page 47](#)

(1) Consult this offer on our website www.se.com

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M173 Optimized, M172 Optimized / Performance, and M171 Optimized logic controllers

Application	Logic controllers for compact and efficient machines		Logic controllers for any size of connectable or connected HVAC machines		Logic controllers for simple and compact machines	
Product name	M173 Optimized	M172 Optimized	M172 Performance	M171 Optimized		
						
HVAC unit type	<ul style="list-style-type: none"> - Heat pumps (up to two circuits) - Process chillers - Pumping - Boilers/Heaters - and any small and compact machines 	<ul style="list-style-type: none"> - Air/water-cooled chiller - Rooftop unit - Heat pump - Shelters - Compressor rack - Ventilation unit - Precision air conditioner - Heat recovery unit - Packaged unit - AHU 	<ul style="list-style-type: none"> - Air/water-cooled chiller - Rooftop unit - Heat pump - Shelters - Compressor rack - Ventilation unit - Precision air conditioner - Heat recovery unit - Packaged unit - AHU 	<ul style="list-style-type: none"> - Air/water-cooled chiller - Rooftop unit - Heat pump - Shelters - Compressor rack - Ventilation unit - Precision air conditioner - Heat recovery unit - Packaged unit - AHU 		
Programming Software	EcoStruxure Machine Expert - HVAC V1.6 or higher	EcoStruxure Machine Expert - HVAC V1.0 or higher				
Secure communication over Internet	Yes, <ul style="list-style-type: none"> - with TM172SIG Gateway Secure Interface - with TM172SIP Plug-in Secure Interface (1) 	Yes, <ul style="list-style-type: none"> - with TM172SIG Gateway Secure Interface - with TM172SIP Plug-in Secure Interface 			Yes, with TM172SIG Gateway Secure Interface	
Maximum number of I/O with expansion modules	78	238			28 44	
Power Supply	24 VAC/DC or 230 VAC	24 VAC/DC			100...240 VAC, isolated 24 VAC/DC (except for TM171ODM22S: 12-24 VAC)	
Embedded I/Os	Analog Input	7	8 or 12	2, 8 or 12	5	
	Digital Input	6	2, 8 or 12	2, 8 or 12	2	
	Analog Output	4	2, 4 or 6	0, 2, 4 or 6	5	
	Digital Output	5	6, 8 or 12	3, 6, 8 or 12	4	
Communication fieldbus and networks	Embedded communication ports	<ul style="list-style-type: none"> ● 2 RS-485 (Modbus SL) ● 1 CAN expansion bus 	<ul style="list-style-type: none"> ● 2 RS-485 (Modbus SL or BACnet MS/TP) ● 1 CAN expansion bus 	<ul style="list-style-type: none"> ● 2 RS-485 (Modbus SL or BACnet MS/TP) ● 1 CAN expansion bus ● RJ45 connector ● Ethernet 	<ul style="list-style-type: none"> ● 1 RS-485 ● 1 LAN expansion bus 	
	Optional communication ports	None except with a gateway	With TM171A communication modules: <ul style="list-style-type: none"> ● RS-485 (Modbus SL or BACnet MS/TP) ● CAN bus ● RS232 ● LonWorks (FFT-10) ● Modbus TCP, BACnet/IP, ● Ethernet 	With TM171A communication modules: <ul style="list-style-type: none"> ● RS-485 (Modbus SL or BACnet MS/TP) ● CAN bus ● RS232 ● LonWorks (FFT-10) 	None except with a gateway	
	USB port	Yes, 1 USB-C	Yes, 1 USB-Mini-B	Yes, 1 USB-A and 1 USB-Mini-B	No (program can be downloaded with the TM171AMFK programming stick and TM171ADMI programming cable)	
	Services	<ul style="list-style-type: none"> ● Remote download via Modbus SL ● Download program and firmware via USB-C 	<ul style="list-style-type: none"> ● Download the program via USB-A or Modbus SL ● Optional services depending on the Ethernet communication module 	<ul style="list-style-type: none"> ● Download the program through USB-A or Modbus SL ● Remote access ● HTTP Webserver (Webvisu) ● FTP client/server ● SNPT 	<ul style="list-style-type: none"> ● Remote download via Modbus SL 	
Display	Built-in	Built-in versions available	Built-in versions available	Built-in versions available	Built-in versions available	
	Remote	Yes <ul style="list-style-type: none"> - with TM173DLED display - with TM172DCL color touch screen displays - with HMI Harmony STU/STO offer, see on our website 	Yes, <ul style="list-style-type: none"> - with TM172DGRP display - with TM172DCL color touch screen displays - with HMI Harmony STU/STO offer, see on our website 		Yes, <ul style="list-style-type: none"> - with TM171DLED, TM171DLCD, and TM171DWAL2 displays - with TM172DCL color touch screen displays - with HMI Harmony STU/STO offer, see on our website 	
Mounting	35 mm (1.38 in) DIN rail or Flush mounting	35 mm (1.38 in) DIN rail, or on panel with TM172AP12PM mounting accessory			35 mm (1.38 in) DIN rail or Flush mounting	
Product certifications	CÉ, cURus (UL Recognized), CSA, RCM, RoHS China, UKCA	CÉ, cURus (UL Recognized), CSA, EAC, RCM, RoHS China, BACnet BTL			CÉ, cURus (UL Recognized), CSA, EAC, RCM, RoHS China	
Reference	TM173O	TM172O	TM172P	TM171O		
Page	16	20			30	

(1) The TM172SIP module can only be connected to the TM173OD in DIN rail mounting version.

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M173 Optimized logic controllers

Application	Logic controllers for compact and efficient machines
Product name	M173 Optimized



Reference	TM173ODM15R	TM173OBM22R	TM173ODM22S	TM173ODM22R	TM173ODEM22R	TM173OFM22S	TM173OFM22R	TM173OBM22RH	TM173ODM22SH	TM173ODM22RH
Power supply	24 VAC/DC				24 VAC/DC			230 VAC		
Type of mounting	4 DIN, 35 mm/1.38 in L rail mounting				Flush mounting (1)			4 DIN, 35 mm/1.38 in L rail mounting		
Embedded display	Yes	–	Yes	Yes	Yes	Yes	Yes	–	Yes	Yes
Total I/Os	15	22	22	22	22	22	22	22	22	22
Analog Inputs	Total									
	4	7	7	7	7	7	7	7	7	7
	NTC (β3435 - 10 kW at 25 °C), or 5 V, or 10 V, or digital inputs, pt1000, 4-20mA, or 0-10 V									
Digital Inputs	Total									
	4	6	6	6	6	6	6	6	6	6
	volt-free or pulse reading - up to 2 kHz									
	2	2	2	2	2	2	2	2	2	2
	volt-free									
	2	4	4	4	4	4	4	4	4	4
Analog Outputs	Total									
	2	4	4	4	4	4	4	4	4	4
	0-10 V/ 4-20 mA									
	1	1	1	1	1	1	1	1	1	1
	0-10 V/PWM - 10 Hz...2 kHz									
	1	3	3	3	3	3	3	3	3	3
Digital Outputs	Total									
	5	5	5	5	5	5	5	5	5	5
	Relay 3 A SPST 3x 1 common, 100 k cycles- no UL derating									
	3	3	3	3	3	3	3	3	3	3
	Relay 3 A SPST 2x 1 common, 100 k cycles- no UL derating									
	2	2	–	2	2	–	2	2	–	2
	SSR (2x 75...240 VAC and 24 VAC)									
	–	–	2	–	–	2	–	–	2	–
Maximum I/Os expanded	–	106	106	106	106	–	–	106	106	106
Compatible Secure Interface	–	TM172SIG, TM172SIP			TM172SIG, TM172SIP	TM172SIG		TM172SIG, TM172SIP		
Compatible expansion module	–	TM172E12R, TM172E28R, TM171EP14R and TM171EP27R				–	–	TM172E12R, TM172E28R, TM171EP14R and TM171EP27R		
Compatible Electronic Expansion Valve driver	–	TM172EVEV1U, TM172EVEV1B, TM172EVEV2B (up to 3 expansion valve drivers or expansions module max.)				–	–	TM172EVEV1U, TM172EVEV1B, TM172EVEV2B (up to 3 expansion valve drivers or expansions module max.)		
Integrated Electronic Expansion Valve driver	–	–			Unipolar	–		–		
Embedded communication ports	RS-485 serial ports	2	2	2	2	2	2	2	2	2
	CAN expansion bus	–	3	3	3	3	–	–	3	3
	Connector for remote display	–	1	1	1	1	–	–	1	1
	Connector to communication module	–	1	1	1	1	1	1	1	1
	USB-C	1	1	1	1	1	1	1	1	1

Application	Remote display
-------------	----------------




Reference	TM173DLED (Compatible with M173 Optimized controllers except TM173ODM15R and M173OFM22)
Type of mounting	Flush mounting (1)
Description	LED display Keyboard: 4 buttons
Programming software	EcoStruxure Machine Expert - HVAC V1.6 or higher
Product certifications	EN 60730-1EN 60730-2-9 UKCA
Communication	<ul style="list-style-type: none"> ● CAN expansion bus ● Dedicated display bus

(1) With the specific brackets provided with logic controllers and remote display.

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M173 Optimized logic controllers



Make your machine smarter, more sustainable and more efficient with Modicon M173 Optimized logic controllers. [Click to open video \(1:52\)](#)


M173 Optimized logic controllers

M173 Optimized logic controllers comprise 5 models that can be used to control up to 22 embedded I/O (digital and analog).

- Power supply:
 - 24 VAC/DC
 - 230 VAC
- Two types of housing:
 - with built-in display
 - without display
- Two types of mounting:
 - On 35 mm/1.38 in rail mounting: controllers to be mounted inside a cabinet
 - Flush mounting: controllers to be mounted on a cabinet door or wall-mounted using the bracket accessories provided with controllers.
- Communication ports on **M173 Optimized** logic controllers:
 - One Modbus SL client/server
 - Three CAN expansion bus (depending on model)
 - One USB-C
- M173 Optimized logic controllers can be connected to I/O expansion modules, see [page 26](#).
- M173 Optimized logic controllers are certified CE, cURus (UL Recognized), CSA, RCM, RoHS China, UKCA.


35 mm/1.38 in rail mounting

24 VAC/DC




- 1 Connector for removable terminal block for digital outputs (1)- CN6
- 2 Connector for removable terminal block for isolated power supply (1)- CN7
- 3 Display (except for **TM173OBM22R** model)
- 4 4x control keys for setting controller parameters (Enter, Escape, Navigation)
- 5 USB-C port to connect a PC - CN11
- 6 Only on TM173ODEM22R: connector for removable terminal block to connect the unipolar electronic expansion valve driver ref. **TM172EVEV1U**
- 7 Connector for removable terminal block for analog inputs (1)- CN10
- 8 Remote display connector - CN4
- 9 Connector for removable terminal block for digital inputs (1) - CN9
- 10 Clip-on lock for 35 mm/1.38 in rail mounting
- 11 Connector for removable terminal block for analog outputs (1)- CN8
- 12 Connector for removable terminal block for CAN expansion bus - CN1
- 13 RS-485 serial port (Modbus SL) - CN2, CN3

230 VAC



- 1 Connector for removable terminal block for digital outputs (1)- CN6
- 2 Connector for removable terminal block for isolated power supply (1)- CN7
- 3 Display (except for **TM173OBM22RH** model)
- 4 4x control keys for setting controller parameters (Enter, Escape, Navigation)
- 5 USB-C port to connect a PC - CN11
- 6 Connector for removable terminal block for analog inputs (1)- CN10
- 7 Remote display connector - CN4
- 8 Connector for removable terminal block for digital inputs (1) - CN9
- 9 Clip-on lock for 35 mm/1.38 in rail mounting
- 10 Connector for removable terminal block for analog outputs (1)- CN8
- 11 Connector for removable terminal block for CAN expansion bus - CN1
- 12 RS-485 serial port (Modbus SL) - CN2, CN3

Flush mounting controllers



- 1 4x control keys for setting controller parameters (Enter, Escape, Navigation)
 - 2 Display
 - 3 USB-C port to connect a PC
- On the back of the controllers
- 4 Connector for removable terminal block for digital outputs
 - 5 Connector for removable terminal block for power supply
 - 6 Connector for removable terminal block digital inputs
 - 7 Connector for removable terminal block for analog outputs
 - 8 Connector for removable terminal block for analog inputs
 - 9 RS-485 serial port (Modbus SL)

(1) M173 Optimized logic controllers are provided with removable terminal blocks for IO, power connections.



TM173ODM15R



TM173ODM22S
TM173ODM22R



TM173ODEM22R (3)



TM173OBM22R



TM173OFM22S



TM173OFM22R



TM173ACB1M
TM173ACB2M



TM173ODM22RH
TM173ODM22SH



TM173OBM22RH

TM173DLED

M173 Optimized logic controllers, Power supply: 24 VAC/DC

No. of I/O	Number and type of channels	Outputs	Embedded communication ports	Display	Reference	Weight kg/lb
35 mm/1.38 in rail mounting (1)						
15	4 digital inputs: <ul style="list-style-type: none"> 2x Volt-free or pulse reading - up to 2 kHz 2x volt-free 4 analog inputs (configurable in pairs): <ul style="list-style-type: none"> 4x NTC (β3435 - 10 kW at 25°C), or PT1000, or 4-20 mA, or 5 V, or 10 V, or digital inputs 	5 digital outputs: <ul style="list-style-type: none"> 3x Relay 3 A SPST, 3x 1 common (2) 2 Relay 3 A SPST, 2x 1 common (2) 2 analog outputs: <ul style="list-style-type: none"> 1x 0-10 V/ 4-20 mA 1x 0-10 V/PWM (10Hz...2kHz) 	<ul style="list-style-type: none"> 2 RS-485 1 USB-C 	Built-in display	TM173ODM15R	0.267 0.591
22	6 digital inputs: <ul style="list-style-type: none"> 2x Volt-free or pulse reading - up to 2 kHz 4x volt-free 7 analog inputs (configurable in pairs): <ul style="list-style-type: none"> 1x NTC (β3435 - 10 kW at 25°C), or PT1000, or digital input, or 0-10 V 6x NTC (β3435 - 10 kW at 25°C), or PT1000, or 4-20 mA, or 5 V, or 10 V, or digital inputs 	5 digital outputs: <ul style="list-style-type: none"> 3x Relay 3 A SPST, 3x 1 common (2) 2x SSR (2x 75...240 VAC and 24 VAC) 4 analog outputs: <ul style="list-style-type: none"> 1x 0-10 V/ 4-20 mA 3x 0-10 V/PWM (10Hz...2kHz) 	<ul style="list-style-type: none"> 3 CAN 2 RS-485 1 USB-C 	Built-in display	TM173ODM22S	0.265 0.585
		5 digital outputs: <ul style="list-style-type: none"> 3x Relay 3 A SPST, 3x 1 common (2) 2 Relay 3 A SPST, 2x 1 common (2) 4 analog outputs: <ul style="list-style-type: none"> 1x 0-10 V/ 4-20 mA 3x 0-10 V/PWM (10Hz...2kHz) 	<ul style="list-style-type: none"> 3 CAN 2 RS-485 1 USB-C 	Built-in display	TM173ODM22R	0.267 0.591
			<ul style="list-style-type: none"> 3 CAN 2 RS-485 1 USB-C 	Remote display (optional)	TM173ODEM22R (3) TM173OBM22R	0.270 0.595 0.259 0.573

Flush mounting (provided with specific brackets) (1)

22	6 digital inputs: <ul style="list-style-type: none"> 2x Volt-free or pulse reading - up to 2 kHz 4x Volt-free 7 analog inputs (configurable in pairs): <ul style="list-style-type: none"> NTC (β3435 - 10 kW at 25°C), or 5 V, or 10 V, or digital inputs, or pt1000, or 4-20 mA, or 0-10 V 	5 digital outputs: <ul style="list-style-type: none"> 3x Relay 5 A SPST, 3x 1 common (2) 2x Relay 5 A SPST, 2x 1 common (2) 4 analog outputs: <ul style="list-style-type: none"> 1x 0-10 V/ 4-20 mA 3x 0-10 V/PWM (10Hz...2kHz) 	<ul style="list-style-type: none"> 2 RS-485 1 USB-C 	Built-in display	TM173OFM22R (4)	0.183 0.404
		5 digital outputs: <ul style="list-style-type: none"> 3x Relay 5 A SPST, 3x 1 common (2) 2x SSR (2x 75...240 VAC and 24 VAC) 4 analog outputs: <ul style="list-style-type: none"> 1x 0-10 V/ 4-20 mA 3x 0-10 V/PWM (10Hz...2kHz) 	<ul style="list-style-type: none"> 2 RS-485 1 USB-C 	Built-in display	TM173OFM22S (4)	0.180 0.399

Connection cables for M173 (Flush mounting) (to be ordered separately)

Designation	Description	Reference	Weight kg/lb
Flexible, unipolar I/O wire with PVC insulation, featuring a 22-pole microfit terminal	To use with TM173OFM22R and TM173OFM22S	TM173ACB1M	0.185 0.407
		TM173ACB2M	0.367 0.807

M173 Optimized logic controllers, Power supply: 230 VAC

No. of I/O	Number and type of channels	Outputs	Embedded communication ports	Display	Reference	Weight kg/lb
35 mm/1.38 in rail mounting (1)						
22	6 digital inputs: <ul style="list-style-type: none"> 2x Volt-free or pulse reading - up to 2 kHz 4x volt-free 7 analog inputs (configurable in pairs): <ul style="list-style-type: none"> 1x NTC (β3435 - 10 kW at 25°C), or PT1000, or digital input, or 0-10 V 6x NTC (β3435 - 10 kW at 25°C), or PT1000, or 4-20 mA, or 5 V, or 10 V, or digital inputs 	5 digital outputs: <ul style="list-style-type: none"> 3x Relay 3 A SPST, 3x 1 common (2) 2x SSR (2x 75...240 VAC and 24 VAC) 4 analog outputs: <ul style="list-style-type: none"> 1x 0-10 V/ 4-20 mA 3x 0-10 V/PWM (10Hz...2kHz) 	<ul style="list-style-type: none"> 3 CAN 2 RS-485 1 USB-C 	Built-in display	TM173ODM22RH	0.265 0.584
		5 digital outputs: <ul style="list-style-type: none"> 3x Relay 3 A SPST, 3x 1 common (2) 2 Relay 3 A SPST, 2x 1 common (2) 4 analog outputs: <ul style="list-style-type: none"> 1x 0-10 V/ 4-20 mA 3x 0-10 V/PWM (10Hz...2kHz) 	<ul style="list-style-type: none"> 3 CAN 2 RS-485 1 USB-C 	Built-in display	TM173ODM22SH	0.180 0.396
			<ul style="list-style-type: none"> 3 CAN 2 RS-485 1 USB-C 	Remote display (optional)	TM173OBM22RH	0.260 0.573

Remote display for M173 Optimized logic controllers (Compatible with M173 Optimized controllers except TM173ODM15, M173OFM22e)

Designation	Description	Reference	Weight kg/lb
Remote LED display	Powered by the controller	TM173DLED	0.099 0.220

(1) Removable terminal blocks are supplied with TM173 Optimized logic controllers.
 (2) 100 k cycles- no UL derating.
 (3) This controller is equipped with one valve driver output and is compatible with the electronic expansion valve driver ref. TM172EVEV1U.
 (4) This controller requires a connection cable type TM173ACB1M.







Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M172 Optimized and Performance logic controllers, Remote displays

Application	Logic controllers for any size of connectable machines																
Product name	M172 Performance			M172 Optimized			M172 Performance			M172 Optimized			M172 Performance				
Reference (1)	TM172PBG07R	TM172PDG07R	TM172OBM18R	TM172ODM18R	TM172PBG18R	TM172PDG18R	TM172PDG18S	TM172OBM28R	TM172ODM28R	TM172PBG28R	TM172PDG28R	TM172PDG28SI	TM172OBM42R	TM172ODM42R	TM172PBG42R	TM172PDG42R	TM172PDG42S
Power supply	24 VAC/DC							24 VAC/DC									
Type of mounting	4 DIN, 35 mm/1.38 in L-r rail mounting Performance controllers, and Panel mounting with TM172AP12PM mounting accessory(2)							8 DIN, 35 mm/1.38 in L-r rail mounting Performance controllers, and Panel mounting with TM172AP12PM mounting accessory (2)									
Embedded display	-	Yes	-	Built-in display 128x64 LCD with backlight	-	Built-in display 128x64 LCD with backlight	-	-	Built-in display 128x64 LCD with backlight	-	Built-in display 128x64 LCD with backlight	-	Built-in display 128x64 LCD with backlight	-	Built-in display 128x64 LCD with backlight	-	Built-in display 128x64 LCD with backlight
Total I/Os	7			18			18			28			42				
Analog Input	2			8			8			8			12				
NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital input	2			8			8			8			12				
Digital Inputs	2			2			2			8			12				
High speed counter (2 kHz), dry contact	2			2			2			2			2				
24 VAC/DC	-			-			-			6			10				
Analog Outputs	-			2			2			4			6				
0-10 V, or 4-20 mA, or PWM (2 kHz, 24 VDC)	-			2			2			2			2				
0-10 V	-			2			2			2			4				
Digital Outputs	3			6			6			8			12				
Relay 3 A	3			6			6			8			12				
SSR 0.5 A	-			-			2			-			2				
Compatible Secure Interface	TM172SIG, TM172SIP																
Compatible expansion module	TM172E12R, TM172E28R, TM171EP14R and TM171EP27R (up to 7 I/O expansions max.)								TM172SIG, TM172SIP								
Compatible expansion valve driver	TM172EVEV1U, TM172EVEV1B, TM172EVEV2B (up to 4 expansion valve drivers max.)								TM172EVEV1U, TM172EVEV1B, TM172EVEV2B (up to 4 expansion valve drivers max.)								
Embedded communication ports	1	-	-	-	1	-	-	-	1	-	-	-	-	-	1	-	-
Ethernet (Modbus TCP, BACnet IP (B-AAC profile), WebVisu)	1	-	-	-	1	-	-	-	1	-	-	-	-	-	1	-	-
RS-485 (Modbus SL or BACnet MS/TP (B-AAC profile))	2	-	2	-	2	-	-	2	-	2	-	-	2	-	2	-	-
CAN expansion bus	1	-	1	-	1	-	-	1	-	1	-	-	1	-	1	-	-
Communication module ports	1	-	1	-	1	-	-	1	-	1	-	-	1	-	1	-	-
USB-B	1	-	1	-	1	-	-	1	-	1	-	-	1	-	1	-	-
USB-A	1	-	-	-	1	-	-	-	-	1	-	-	-	-	1	-	-
µSD Card slot	1	-	-	-	1	-	-	-	-	1	-	-	-	-	1	-	-
Optional communication ports	<ul style="list-style-type: none"> • CAN expansion bus • Modbus TCP • Modbus SL(RS-485) • BACnet MS/TP (B-AAC profile) • BACnet IP (B-AAC profile) • RS232 Serial link • LonWorks (FFT-10) 																
With Secure Interfaces (see page 40)	<ul style="list-style-type: none"> • FTPs • HTTPs • SMTPs • SNMT • MQTT • Cybersecure VPN 																

(1) Products equipped with an isolated power supply, and two isolated RS-485 ports. (2) Accessories to be ordered separately.

Application	Remote displays (compatible with each M172 Logic controller)					
References						
Type of mounting	Remote wall	Remote wall	Remote wall	Remote wall	Remote flush	Remote flush
Description	LCD display with backlight	LCD display, Color touchscreen	LCD display, Color touchscreen	LCD display, Color touchscreen	LCD display, Color touchscreen	LCD display, Color touchscreen
Programming software	EcoStruxure Machine Expert - HVAC V1.0 or higher					
Product certifications	CE, cURus (UL Recognized), CSA, EAC, RCM, RoHS China					
Communication	• CAN expansion bus		• Modbus SL		• Modbus SL	

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M172 logic controllers

M172 Optimized and Performance logic controllers

M172 Optimized and M172 Performance logic controllers are differentiated by the connectivity: embedded on M172 Performance, optional on M172 Optimized. M172 logic controllers embed 7, 18, 28 or 42 I/O, and can be fitted with a display, with relay outputs, and with SSR outputs, depending on the model.

- The M172 logic controller offer comprises:
 - a M172 model to control from 7 up to 18 embedded I/O (digital and analog), in 4 DIN (controller width is 72 mm /2.83 in)
 - and M172 models to control from 28 up to 42 embedded I/O (digital and analog), in 8 DIN (controller width 144 mm /5.66 in)
- Power supply: 24 VAC/DC
- Two types of housing:
 - with built-in display
 - without display
- Two types of mounting:
 - On 35 mm/1.38 in \perp rail mounting: for M172 logic controller to be mounted inside a cabinet
 - On panel: with **TM172AP12PM** fixing accessory
- Communication ports on M172 Optimized logic controllers:
 - Two RS-485 for Modbus SL (client/server) (only 1 client) or 1 for BACnet MS/TP (B-AAC profile, BACnet BTL certified)
 - One for CAN expansion bus
 - Plus one communication module connector
- Communication ports on M172 Performance logic controllers: same as M172 Optimized, plus one RJ45 for Modbus TCP, BACnet IP (B-AAC profile, BACnet BTL certified) and Ethernet
- M172 logic controllers can be connected to communication modules, offering another connection to a CAN expansion bus, Modbus SL or LonWorks, etc., see [page 42](#).
- M172 logic controllers are certified CE, cURus (UL Recognized), CSA, EAC, RCM, RoHS China, and BACnet BTL certified.
- Micro SD card: a slot for a micro SD memory card is available on the front face of the M172 Performance logic controllers (1).
The micro SD card is used for:
 - Data logging
 - Webserver storage
- USB programming ports
 - The USB-A port is available on M172 Performance logic controllers, used to transfer programs with a memory stick.
 - USB mini B is available on M172 Optimized and Performance logic controllers, used to connect to a PC for programming, see [page 49](#).



4 DIN - with display

M172 Optimized logic controller




8 DIN - without display



4 DIN - without display

M172 Performance logic controller




8 DIN - with display

(1) M172 Optimized logic controllers do not have a slot for a micro SD card (no slot can be added later).


Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M172 logic controllers



4 DIN controller



8 DIN controller

M172 Optimized and Performance logic controllers

M172 logic controllers with 7 or 18 I/O (in 4 DIN: controller width is 72 mm / 2.83 in) (1)

- 1 RJ45 connector for Ethernet Modbus TCP, BACnet IP (B-AAC profile) (2)
- 2 Connector for removable terminal block for digital outputs
- 3 Connector for removable terminal block for power supply (24 VAC/DC) (3)
- 4 Connector for removable terminal block for analog inputs
- 5 Connector for removable terminal block for digital inputs
- 6 Connector for removable terminal block for fast digital inputs (high speed counter)
- 7 Connector for removable terminal block for analog outputs
- 8 Connector for removable terminal block for RS-485-1 (Modbus SL or BACnet MS/TP) (3)
- 9 Connector for removable terminal block for RS-485-2 (Modbus SL or BACnet MS/TP) (3)
- 10 Connector for removable terminal block for CAN expansion bus
- 11 Slot for micro SD card (2)
- 12 Slot for battery (behind the front flap)
- 13 On TM172●D●●●●: Built-in display, 4 status LEDs and 5 control keys for setting controller parameters
On TM172●B●●●●: 4 status LEDs and 5 control keys for setting controller parameters, behind a front panel
- 14 Connector for communication module
- 15 USB-B port to link a PC
- 16 USB-A port for USB stick (2)
- 17 Clip-on lock for 35 mm / 1.38 in \perp rail mounting
- 18 Two slots for the TM172AP12PM fixing accessory

M172 logic controllers with 28 or 42 I/O (in 8 DIN: controller width is 144 mm / 5.66 in) (1)

- 1 RJ45 connector for Ethernet Modbus TCP and BACnet IP (B-AAC profile) (2)
- 2 Connector for removable terminal block for digital outputs
- 3 Connector for removable terminal block for power supply (24 VAC/DC) (3)
- 4 Connector for removable terminal block for analog inputs
- 5 Connector for removable terminal block for digital inputs
- 6 Connector for removable terminal block for fast digital inputs (high speed counter)
- 7 Connector for removable terminal block for analog outputs
- 8 Connector for removable terminal block for RS-485-1 (Modbus SL or BACnet MS/TP) (3)
- 9 Connector for removable terminal block for RS-485-2 (Modbus SL or BACnet MS/TP) (3)
- 10 Connector for removable terminal block for CAN expansion bus
- 11 Slot for micro SD card (2)
- 12 Slot for battery (behind the front flap)
- 13 On TM172●D●●●●: Built-in display, 4 status LEDs and 5 control keys for setting controller parameters
On TM172●B●●●●: 4 status LEDs and 5 control keys for setting controller parameters, behind a front panel
- 14 Connector for communication modules
- 15 USB-B port to connect a PC
- 16 USB-A port for USB stick (2)
- 17 Clip-on lock for 35 mm / 1.38 in \perp rail mounting
- 18 Two slots for the TM172AP12PM fixing accessory

(1) TM172ASCTB●●●● removable terminal blocks to be ordered separately, see page 27.

(2) Only for M172 Performance.

(3) TM172O●●●●, TM172P●G07R, TM172P●G18●, TM172P●G28●I and TM172P●G42●I have an isolated power supply and two isolated RS-485 ports.

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M172 Optimized logic controllers

M172 Optimized logic controllers: Power supply: 24 VAC/DC

35 mm/1.38 in rail mounting, and Panel mounting with accessory

No. of I/O	Number and type of channels	Outputs	Embedded communication ports	Display	Reference	Weight kg/lb
18	2 digital inputs: ■ 2x high speed counter (2 kHz), dry contact 8 analog inputs (configurable in pairs): ■ 8x NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital input	6 digital outputs: ■ 1x SPDT relay 3 A ■ 2x SPST 3 A with the same common ■ 1x SPST 3 A ■ 2x SPST 3 A with independent common 2 analog outputs: ■ 2x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 VDC)	<ul style="list-style-type: none"> ● 1 CAN expansion bus ● 2 RS-485 ● 1 USB-B ● 1 Communication module port 	Remote display (optional)	TM172OBM18R (1)	0.170/ 0.375
				Built-in display 128x64 LCD with backlight	TM172ODM18R (1)	0.195/ 0.430
28	8 digital inputs: ■ 6x 24 VAC or DC ■ 2x high speed counters, dry contact 8 analog inputs (configurable in pairs): ■ 8x NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or digital input	8 digital outputs: ■ 1x SPDT Relay 3 A ■ 3x SPST 3 A with the same common ■ 2x SPST 3 A with the same common ■ 2x SPST 3 A with independent common 4 analog outputs ■ 2x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 VDC) ■ 2x 0-10 V	<ul style="list-style-type: none"> ● 1 CAN expansion bus ● 2 RS-485 ● 1 USB-B ● 1 Communication module port 	Remote display (optional)	TM172OBM28R (1)	0.390/ 0.859
				Built-in display 128x64 LCD with backlight	TM172ODM28R (1)	0.390/ 0.859
42	12 digital inputs: ■ 10x 24 VAC or DC ■ 2x high speed counters, dry contact 12 analog inputs (configurable in pairs): ■ 12x NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or digital input	12 digital outputs: ■ 2x SPDT Relay 3 A ■ 3x SPST 3 A with the same common ■ 3x SPST 3 A with the same common ■ 2x SPST 3 A with the same common ■ 2x SPST 3 A with independent common 6 analog outputs: ■ 2x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 VDC) ■ 4x 0-10 V	<ul style="list-style-type: none"> ● 1 CAN expansion bus ● 2 RS-485 ● 1 USB-B ● 1 Communication module port 	Remote display (optional)	TM172OBM42R (1)	0.480/ 1.058
				Built-in display 128x64 LCD with backlight	TM172ODM42R (1)	0.480/ 1.058

Accessories to be ordered separately

Designation	Use for	Reference	Weight kg/lb
I/O screw terminal blocks	TM172●●●07R logic controllers	TM172ASCTB07	0.025/ 0.055
	TM172●●●18● logic controllers	TM172ASCTB18	0.040/ 0.088
	TM172P●●●28●, TM172P●●●28●l logic controllers	TM172ASCTB28	0.100/ 0.220
	TM172P●●●42●, TM172P●●●42●l logic controllers	TM172ASCTB42	0.150/ 0.331
Fixing accessory: 12 clip-on locks for panel mounting	For mounting M172 logic controllers and M172 expansion modules on panel	TM172AP12PM	0.050/ 0.110

(1) Products equipped with an isolated power supply, and two isolated RS-485 ports.



TM172OBM18R



TM172ODM18R



TM172OBM28R



TM172ODM28R




TM172OBM42R




TM172ODM42R



TM172ASCTB18



TM172ASCTB28



TM172AP12PM

M172 Performance logic controllers: Power supply: 24 VAC/DC

35 mm/1.38 in rail mounting, and panel mounting with accessory

No. of I/O	Number and type of channels	Outputs	Embedded communication ports	Display	Reference	Weight kg/lb
7	2 digital inputs: ■ 2x high speed counter (2 kHz), dry contact 2 analog inputs (configurable in pairs): ■ 2x NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital input	3 digital outputs: ■ 1x SPDT relay 3 A ■ 2x SPST 3 A with the same common	<ul style="list-style-type: none"> ● 1 Ethernet ● 1 CAN expansion bus ● 2 RS-485 ● 1 USB-A ● 1 USB-B ● 1 Communication module port ● 1 μSD Card slot 	Remote display (optional)	TM172PBG07R (1)	0.175/ 0.386
				Built-in display 128x64 LCD with backlight	TM172PDG07R (1)	0.200/ 0.441
18	2 digital inputs: ■ 2x high speed counters, dry contact 8 analog inputs (configurable in pairs): ■ 8x NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital input	6 digital outputs ■ 1x SPDT relay 3 A ■ 2x SPST 3 A with the same common ■ 1x SPST 3 A ■ 2x SPST 3 A with independent common ■ Optional 2x SSR 0.5 A with independent common for TM172PDG18S only 2 Analog outputs: ■ 2x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 VDC)	<ul style="list-style-type: none"> ● 1 Ethernet ● 1 CAN expansion bus ● 2 RS-485 ● 1 USB-A ● 1 USB-B ● 1 Communication module port ● 1 μSD Card slot 	Remote display (optional)	TM172PBG18R (1)	0.200/ 0.441
				Built-in display 128x64 LCD with backlight	TM172PDG18R (1)	0.225/ 0.496
					TM172PDG18S (1)	0.225/ 0.496
28	8 digital inputs: ■ 6x 24 VAC or DC ■ 2x high speed counters, dry contact 8 analog inputs, (configurable in pairs): ■ 8x NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or digital input	8 digital outputs: ■ 1x SPDT Relay 1 A or 3 A for TM172P●G28● ■ 3x SPST 3 A with the same common ■ 2x SPST 3 A with the same common ■ 2x SPST 3 A with independent common ■ Optional 2x SSR 0.5 A with independent common for TM172PDG28SI only 4 analog outputs: ■ 2x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 VDC) ■ 2x 0-10 V	<ul style="list-style-type: none"> ● 1 Ethernet ● 1 CAN expansion bus ● 2 RS-485 ● 1 USB-A ● 1 USB-B ● 1 Communication module port ● 1 μSD Card slot 	Remote display (optional)	TM172PBG28R	0.300/ 0.661
				Built-in display 128x64 LCD with backlight	TM172PDG28R	0.300/ 0.661
				Remote display (optional)	TM172PBG28RI (1)	0.390/ 0.859
				Built-in display 128x64 LCD with backlight	TM172PDG28RI (1)	0.390/ 0.859
					TM172PDG28SI (1)	0.390/ 0.859
42	12 digital inputs: ■ 10x 24 VDC ■ 2x high speed counter, dry contact 12 analog inputs, (configurable in pairs): ■ 12x NTC, or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or digital input	12 digital outputs: ■ 2x SPDT relay 1 A or 3 A for TM172P●G42● ■ 3x SPST 3 A with the same common ■ 3x SPST 3 A with the same common ■ 2x SPST 3 A with the same common ■ 2x SPST 3 A with independent common ■ Optional 2x SSR 0.5 A with independent common for TM172PDG42S and TM172PDG42SI only 6 analog outputs: ■ 2x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 VDC) ■ 4x 0-10 V	<ul style="list-style-type: none"> ● 1 Ethernet ● 1 CAN expansion bus ● 2 RS-485 ● 1 USB-A ● 1 USB-B ● 1 Communication module port ● 1 μSD Card slot 	Remote display (optional)	TM172PBG42R	0.385/ 0.849
				Built-in display 128x64 LCD with backlight	TM172PDG42R	0.385/ 0.849
					TM172PDG42S	0.385/ 0.849
				Remote display (optional)	TM172PBG42RI (1)	0.480/ 1.058
					TM172PDG42SI (1)	0.480/ 1.058

Accessories to be ordered separately

I/O screw terminal blocks, Fixing accessory

See page 27

(1) Products equipped with an isolated power supply, and two isolated RS-485 ports.



TM172PBG07R



TM172PDG18R



TM172PBG28RI



TM172PDG28RI



TM172PBG42RI



TM172PDG42SI

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

I/O expansion modules for M173 and M172 logic controllers

I/O expansion modules

Two I/O expansion modules are available to increase the number of I/O:

- up to 78 on M173 logic controllers,
- up to 238 on M172 logic controllers.

- Expanded I/O types are digital and analog; the mix between inputs and outputs differs according to the module, making it easier to adapt the configuration to each need.
- They are connected via the CAN expansion bus of the logic controllers.
- The maximum number of expansion modules on the CAN expansion bus is 7, in any combination (if more expansions are needed, please contact our Customer Care Centre).
- The expansion modules are equipped with DIP switches which can be used to set the baud rate, the network address and also to incorporate a 120 ohm terminal resistor.
- The I/O can be configured in pairs, like M172 controllers.
- I/O expansion modules compatibility:

Logic controllers	Compatible I/O expansion module (reference)
M173 Optimized (TM173O●●●●)	TM172E12R TM172E28R
M172 Optimized (TM172O●●●●) M172 Performance (TM172P●●●●)	TM172E12R TM172E28R <i>Legacy TM171EP expansion modules are also compatible with M172 controllers.</i>


TM172E12R and TM172E28R expansion modules (1)

- 1 Connector for removable terminal block for power supply (24 VAC/DC)
- 2 Removable terminal block for digital outputs
- 3 Connector for removable terminal block for CAN expansion bus
- 4 DIP switches
- 5 Clip-on lock for 35 mm/1.38 in \sqcup rail mounting
- 6 Connector for removable terminal block for digital inputs
- 7 Connector for removable terminal block for analog inputs with 5 VDC/24 VDC output power supply

TM172E28R expansion module (1)

- 8 Connector for removable terminal block for analog outputs
- 9 Two slots for TM172AP12PM fixing accessory

(1) Removable terminal blocks to be ordered separately, see [page 27](#).



TM172E12R

TM172E28R



TM172E28R



TM172E12R



TM172E28R



TM172ASCTB12E



TM172ASCTB28E



TM172AP12PM

I/O expansion modules						
35 mm/1.38 in rail mounting						
No. of I/O	Number and type of channels		Compatibility	Embedded communication ports	Reference	Weight kg/lb
	Inputs (1)	Outputs (1)				
12	2 digital inputs: <ul style="list-style-type: none"> 2x high speed counters, dry contact 4 analog inputs: <ul style="list-style-type: none"> 4x NTC or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital inputs 	6 digital outputs: <ul style="list-style-type: none"> 3x SPST 3 A with the same common 3x SPST 3 A with the same common 	TM1730●●●● TM1720●●●● TM172P●●●●	<ul style="list-style-type: none"> 1 CAN expansion bus 	TM172E12R	0.140/ 0.308
28	6 digital inputs: <ul style="list-style-type: none"> 4x 24 VAC or DC 2x high speed counters, dry contact 10 analog inputs: <ul style="list-style-type: none"> 10x NTC or PT1000, or PTC, or 0-20 mA, or 4-20 mA, or 0-5 V, or 0-10 V, or hOhm, or daOhm, or digital inputs 	10 digital outputs: <ul style="list-style-type: none"> 3x SPST 3 A with the same common 3x SPST 3 A with the same common 2x SPST 3 A with the same common 2x SPST 3 A with the same common 2 analog outputs: <ul style="list-style-type: none"> 2x 0-10 V, or 4-20 mA, or PWM (2 kHz, 24 VDC) 	TM1730●●●● TM1720●●●● TM172P●●●●	<ul style="list-style-type: none"> 1 CAN expansion bus 	TM172E28R	0.190/ 0.418

Accessories to be ordered separately			
Designation	Compatibility	Reference	Weight kg/lb
Screw terminal blocks (inputs, outputs, and communication bus)	TM172E12R expansion module	TM172ASCTB12E	0.070/ 0.154
	TM172E28R expansion module	TM172ASCTB28E	0.100/ 0.220
Fixing accessory: 12 clip-on locks for panel mounting	TM172E●●R expansion modules	TM172AP12PM	0.055/ 0.110

(1) Removable terminal blocks to be ordered separately.

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Remote displays for M172 logic controllers

Remote displays

Remote color touch screen displays

Six remote color touch screen displays are dedicated to the M172 Optimized and Performance logic controllers, distinguished by use and type of mounting.

These displays can be also used with M171 controllers with Modbus SL or with third-party products equipped via Modbus SL.

They are all programmable with EcoStruxure Machine Expert - HVAC. The remote color touch screen displays have the same firmware, meaning they can be swapped interchangeably.

- TM172DCLWT●● are designed for wall mounting and indoor use, depending on the reference, for controlling temperature, relative humidity and PIR presence with built-in sensor.
- TM172DCLF● are designed for flush mounting, and wall mounting with an accessory, and either indoor or outdoor uses, with a or dark gray housing. An installation on a wall with TM172ABKP●● accessories, useful for a plant room.
- TM172DCLWT● and TM172DCLF● displays can be mounted vertically (portrait) or horizontally (landscape) (1). They can be configured for Modbus SL as client or server, by means of the software.
 - On Modbus SL Server, up to 8 displays can be installed in the same network.
 - On Modbus SL Client, up to 8 devices can be managed via the display.

Remote monochrome display

- TM172DGRP monochrome display is dedicated to the M172 Optimized and M172 Performance logic controllers. It is designed for flush mounting, and wall mounting with an accessory, and indoor use. It is programmable with EcoStruxure Machine Expert - HVAC.



TM172DCLWT●●



TM172DCLFW



TM172DCLFG



TM172DGRP

TM172DCLWT●●

- 1 3.5" color touch screen LCD (320 x 240 pixels)
- 2 Holes for presence (motion) detection
- 3 Input connector (USB Micro-B port)
- 4 Power Supply (24 VAC/DC)
- 5 RS-485 Modbus serial line
- 6 Holes for temperature and humidity measurement

TM172DCLFW, TM172DCLFG

- 1 3.5" color touch screen LCD (320 x 240 pixels)
- 2 Input connector (USB Micro-B port)
- 3 Power Supply (24 VAC/DC)
- 5 RS-485 Modbus serial line

TM172DGRP

- 1 Backlight monochrome LCD screen (240 x 140 pixels)
- 2 5 control keys
- 3 CAN bus connector

(1) With landscape mounting, temperature and humidity sensors cannot be used as they are not accurate.

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Remote displays for M172 logic controllers



TM172DCLWT●●




TM172DCLFW



TM172DCLFG



TM172DGRP



TM172ABKPG



TM171ABKPG

Remote displays					
Type	Description	Housing	Built-in sensor for	Reference	Weight kg/lb
Remote color touch screen wall mounting displays	<ul style="list-style-type: none"> ■ Power supply: 24 VAC/DC ■ Color touchscreen ■ Size: 3.5" ■ Resolution: 320 x 240 pixels ■ IP20 ■ Communication port: 1 RS-485, Modbus SL with terminal blocks 	White	■ Temperature	TM172DCLWT	0.340/ 0.749
			■ Temperature ■ Relative humidity	TM172DCLWTH	0.340/ 0.749
			■ Temperature ■ Relative humidity ■ Presence PIR	TM172DCLWTHP	0.340/ 0.749
Remote color touch screen flush mounting displays	<ul style="list-style-type: none"> ■ Power supply: 24 VAC/DC ■ Color touchscreen ■ Size: 3.5" ■ Resolution: 320 x 240 pixels ■ IP65 (front face) ■ Communication port: 1 RS-485, Modbus SL with terminal blocks 	White	–	TM172DCLFW	0.205/ 0.452
		Grey	–	TM172DCLFG	0.205/ 0.452
Remote display monochrome	<ul style="list-style-type: none"> ■ 5 control keys ■ Backlit LCD, ■ 240 x 140 pixels, ■ Monochrome, ■ With real time clock 	Grey		TM172DGRP	0.197/ 0.430
Accessories to be ordered separately					
Type	Use			Reference	Weight kg/lb
Mounting accessories (1)	White wall support for TM172DCLFW display			TM172ABKPW	0.060/ 0.132
	Grey wall support for TM172DCLFG display			TM172ABKPG	0.060/ 0.132
	Wall bracket For TM172DGRP display			TM171ABKPG	0.015/ 0.030

(1) With the use of TM172ABKP●● accessories, the degree of protection for the TM172DCLF● displays is IP20.

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M171 Optimized logic controllers and Remote displays

Application	Logic controllers for Simple and compact machines									
Product name	M171 Optimized									
Reference	TM171OBM14R (1)	TM171OD14R (1)	TM171ODM14R (1)	TM171OBM22R	TM171OD22R	TM171ODM22R	TM171ODM22S	TM171OF22R	TM171OFM22R	
Power supply	100-240 VAC			24 VAC/DC (3) (4)						
Type of mounting	4 DIN, 35 mm/1.38 in L rail mounting			4 DIN, 35 mm/1.38 in L rail mounting				Flush mounting		
Embedded display	Built-in display			Built-in display						
Total I/Os	14			22						
Analog Inputs	5			5						
Total	5			5						
NTC, or PT1000, or digital inputs	2			-						
NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs	2			2						
NTC, or PT1000, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital input	1			-						
NTC or digital inputs	-			3						
Digital Inputs	2			6						
Total	2			6						
open collector or digital inputs (2)	2			-						
volt-free in 1 group	-			6						
Analog Outputs	5			5						
Total	5			5						
open collector (2) for 12 V PWM/PPM or digital inputs	2			-						
open collector for 12 V PWM/PPM	-			2						
0-10 V	2			3						
4-20 mA	1			-						
Digital Outputs	4			6						
Total	4			6						
Relay 2 A, 230 VAC	4			5						
open collector	-			1						
SSR (3 A, 230 VAC)	-			-						
Maximum I/Os expanded	22			44						
Compatible Secure Interface	TM172SIG	TM172SIG (5)	TM172SIG	TM172SIG	TM172SIG (5)	TM172SIG	TM172SIG	TM172SIG (5)	TM172SIG	
Compatible expansion module	TM171EO14R			TM171EO15R, TM171EO22R						
Embedded communication ports	RS-485 1	LAN expansion bus -	LAN expansion bus 1	RS-485 1	LAN expansion bus -	LAN expansion bus 1	LAN expansion bus 1	LAN expansion bus -	LAN expansion bus 1	
Connection accessories references (sold in lots of 5)										
Low voltage connector	-			TM171ACB4OI1M, TM171ACB4OI2M						
Analog output connector	-			TM171ACB4OAO1M, TM171ACB4OAO2M						
Modbus SL connector	-			TM171ACB4ORS485	-	TM171ACB4ORS485	TM171ACB4ORS485	-	TM171ACB4ORS485	
LAN expansion bus connector	TM171ACB4OLAN			TM171ACB4OLAN						

(1) Terminal blocks are supplied with TM171OBM14R, TM171OD14R, and TM171ODM14R.
 (2) Both I/O are the same. On the same channel: 2 digital inputs or 2 analog outputs (depending on the configuration).
 (3) Except for for TM171ODM22S: 12-24 VAC.
 (4) Connectors to be ordered separately, see page 35.
 (5) When controller is associated to a TM171AMB Communication module.

Application	Remote Displays (compatible with each M171 Logic controller)									
Reference	TM171DLED	TM171DLCD2U	TM171DWAL2U	TM171DWAL2L	TM172DCLWT	TM172DCLWTH	TM172DCLWTHP	TM172DCLFW	TM172DCLFG	
Type of mounting	Remote flush	Remote flush	Remote wall	Remote wall	Remote wall	Remote wall	Remote wall	Remote wall	Remote flush	
Description	LED display Keyboard: 4 buttons	LCD display Keyboard: 7 buttons	LCD display Keyboard: 4 buttons Without backlight	LCD display Keyboard: 4 buttons With backlight	LCD display Color touchscreen Temperature	LCD display Color touchscreen Temperature, Relative humidity	LCD display Color touchscreen Temperature, Relative humidity Presence PIR	LCD display Color touchscreen IP65 (front face)	LCD display Color touchscreen IP65 (front face)	
Programming software	EcoStruxure Machine Expert - HVAC V1.0 or higher			EcoStruxure Machine Expert - HVAC V1.0 or higher						
Product certifications	CE, UL (recognized), cURus, CSA, EAC, RCM, RoHS China.			CE, UL (recognized), cURus, CSA, EAC, RCM, RoHS China.						
Communication	• LAN expansion bus			• LAN expansion bus	• Modbus SL	-	-	-	-	

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M171 Optimized logic controllers

M171 Optimized logic controllers


The M171 Optimized logic controllers comprise 10 models that can be used to control from 14 up to 22 embedded I/O (digital and analog).

- Two types of power supply are available:
 - 100-240 VAC
 - 12-24 VAC or 24 VDC
- Two types of housing:
 - with built-in display
 - with remote display that can be added by means of the LAN expansion bus
- Two types of mounting:
 - Flush mounting: controllers to be mounted on a cabinet door
 - On 35 mm/1.38 in τ rail mounting: controllers to be mounted inside a cabinet
- Communication ports on M171 Optimized logic controllers:
 - One optional Modbus SL bus
 - One LAN expansion bus
- M171 Optimized logic controllers are certified CE, UL (recognized), cURus, CSA, EAC, RCM, RoHS China.

35 mm/1.38 in τ rail mounting

TM171O●14R Optimized logic controllers

- 1 Display
- 2 4x control keys for setting controller parameters (Enter, Escape, Navigation)
- 3 Programming port (TTL)
- 4 Removable terminal block for RS-485 serial port (**TM171O●M14R**)
- 5 Wired connector for LAN expansion bus
- 6 Clip-on lock for 35 mm/1.38 in τ rail mounting
- 7 Removable terminal block for digital outputs
- 8 Removable terminal block for 100...240 VAC power supply
- 9 Removable terminal block for I/O



TM171O●22R● Optimized logic controllers (1)

- 1 Display
- 2 4x control keys for setting controller parameters (Enter, Escape, Navigation)
- 3 Programming port (TTL)
- 4 Wired connector for RS-485 serial port (**TM171O●M14R**)
- 5 Clip-on lock for 35 mm/1.38 in τ rail mounting
- 6 Removable terminal block for outputs
- 7 Wired connector for 12-24 VAC or 24 VDC power supply, and for low voltage I/O
- 8 Wired connector for analog output
- 9 Wired connector for LAN expansion bus



Flush mounting

TM171OF●22R● Optimized logic controllers (1)

- 1 Display
- 2 4x control keys for setting controller parameters (Enter, Escape, Navigation)
- 3 Wired connector for RS-485 serial port (**TM171OF●M22R**)
- 4 Wired connector for analog outputs
- 5 Wired connector for LAN expansion bus
- 6 Programming port (TTL)



(1) Connectors to be ordered separately, see [page 35](#).

M171 Optimized logic controllers: Power supply: 100-240 VAC

No. of I/O	Number and type of channels	Embedded communication	Display	Reference	Weight kg/lb	
	Inputs	Outputs				
35 mm/1.38 in rail mounting (1)						
14	2 digital inputs: ■ 2x open collector or digital inputs (2) 5 configurable analog inputs: ■ 3x NTC, or PT1000, or digital inputs ■ 2x NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs	4 digital outputs: ■ 3x SPST (2 A, 230 VAC) with the same common ■ 1x SPDT (2 A, 230 VAC) 5 analog outputs: ■ 2x open collector for 12 V PWM/PPM or digital inputs ■ 2x 0-10 V ■ 1x 4-20 mA	● 1 RS-485 ● 1 LAN expansion bus ● 1 LAN expansion bus ● 1 RS-485 ● 1 LAN expansion bus	Remote display (optional) Built-in display Built-in display	TM171OBM14R TM171OD14R TM171ODM14R	0.190/0.420 0.190/0.420 0.190/0.420



TM171OBM14R



TM171OD14R



TM171ODM14R



TM171OBM22R



TM171OD22R



TM171ODM22R



TM171OF22R



TM171OFM22R

M171 Optimized logic controllers: Power supply: 12-24 VAC or 24 VDC (3) (4)

35 mm/1.38 in rail mounting						
22	6 digital inputs: ■ 6x volt-free in 1 group 5 configurable analog inputs: ■ 3x NTC or digital inputs ■ 2x NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs	6 digital outputs: ■ 3x SPST (2 A, 230 VAC) with the same common ■ 2x SPST (2 A, 230 VAC) with independent common ■ 1x open collector 5 analog outputs: ■ 2x open collector for 12 V PWM/PPM ■ 3x 0-10 V 6 digital outputs: ■ 3x SPST (2 A, 230 VAC) with the same common ■ 2x SSR (3 A, 230 VAC) ■ 1x open collector 5 analog outputs: ■ 2x open collector for 12 V PWM/PPM ■ 3x 0-10 V	● 1 RS-485 ● 1 LAN expansion bus ● 1 LAN expansion bus ● 1 RS-485 ● 1 LAN expansion bus ● 1 RS-485 ● 1 LAN expansion bus	Remote display (optional) Built-in display Built-in display Built-in display	TM171OBM22R TM171OD22R TM171ODM22R TM171ODM22S	0.190/0.420 0.190/0.420 0.190/0.420 0.190/0.420

Flush mounting

22	6 digital inputs: ■ 6x volt-free in 1 group 5 configurable analog inputs: ■ 3x NTC or digital input ■ 2x NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs	6 digital outputs: ■ x3 SPST (2 A, 230 VAC) with the same common ■ 2x SPST (2 A, 230 VAC) with independent common ■ 1x open collector 5 analog outputs: ■ 2x open collector for 12 V PWM/PPM ■ 3x 0-10 V	● 1 LAN expansion bus ● 1 RS-485 ● 1 LAN expansion bus	Built-in display Built-in display	TM171OF22R TM171OFM22R	0.164/0.360 0.164/0.360
----	--	--	--	--------------------------------------	---	----------------------------

Remote display for M171 Optimized logic controllers

Remote displays See page 35

Connection accessories for M171 Optimized logic controllers

Connectors Low voltage connector, Analog output connector, Modbus SL connector, LAN expansion bus connector See page 35

(1) Terminal blocks are supplied with [TM171OBM14R](#), [TM171OD14R](#), and [TM171ODM14R](#).
 (2) Both I/O are the same. On the same channel: 2 digital inputs or 2 analog outputs (depending on the configuration).
 (3) Except for for [TM171ODM22S](#): 12-24 VAC.
 (4) Connectors to be ordered separately, see [page 35](#).

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

I/O expansion modules for M171 Optimized controllers

I/O expansion modules

Three I/O expansion modules are available to increase the number of I/O up to 44 on M171 Optimized logic controllers:

- Expanded I/O types are digital and analog
- I/O expansion modules are connected via the LAN expansion bus on M171 Optimized logic controllers
- I/O expansion modules compatibility:

Logic controller type	Reference	Compatible I/O expansion module Reference
M171 Optimized	TM171OBM14R, TM171OD14R, TM171ODM14R	TM171EO14R
	TM171OBM22R, TM171OD22R, TM171ODM22R, TM171ODM22S, TM171OF22R, TM171OFM22R	TM171EO15R
		TM171EO22R



35 mm/1.38 in rail mounting

- Service port (TTL)
- Wired connector for removable terminal block for Modbus SL
- Connector for removable terminal block for digital outputs
- Wired connector for removable terminal block for power supply (12-24 VAC or 24 VDC),
- Wired connector for low voltage I/O
- Clip-on lock for 35 mm/1.38 in rail mounting
- Wired connector for removable terminal block for analog outputs
- Wired connector for removable terminal block for LAN expansion bus

(1) Removable terminal blocks to be ordered separately, except for TM171EO14R.

I/O expansion modules (1)

35 mm/1.38 in rail mounting

No. of I/O	Number and type of channels	Compatibility	Embedded communication ports	Reference	Weight kg/lb
	Inputs	Outputs			
14	2 digital inputs: 2x open collector or digital inputs (1) 5 configurable analog inputs: ■ 3x NTC or digital inputs ■ 2x NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or 0-5 V, or 0-1 V, or digital inputs	4 digital outputs: ■ 3x SPST (2 A, 230 VAC) with the same common ■ 1x SPDT (2 A, 230 VAC) 5 analog outputs: ■ 2x open collector for 12 V PWM/PPM or digital inputs (1) ■ 2x 0-10 V ■ 1x 4-20 mA	TM171OBM14R, TM171OD14R, TM171ODM14R ● 1 LAN expansion bus	TM171EO14R	0.190/ 0.420
15	6 digital inputs: volt-free 3 analog inputs: NTC or digital inputs	4 digital outputs: ■ 3x 2 A, 250 VAC ■ 1x open collector 2 analog outputs: open collector (PPM/PWM)	TM171OBM22R, TM171OD22R, TM171ODM22R, TM171ODM22S, TM171OF22R, TM171OFM22R ● 1 LAN expansion bus	TM171EO15R	0.190/ 0.420
22	6 digital inputs: volt-free 5 analog inputs: ■ 3x NTC or digital inputs ■ 2x NTC, or 0-20 mA, or 4-20 mA, or 0-10 V, or digital inputs	6 digital outputs: ■ 5x 2 A, 250 VAC ■ 1x open collector 5 analog outputs: ■ 2x open collector (PPM/PWM) ■ 3x 0-10 V	TM171OBM22R, TM171OD22R, TM171ODM22R, TM171ODM22S, TM171OF22R, TM171OFM22R ● 1 LAN expansion bus	TM171EO22R	0.190/ 0.420



TM171EO14R



TM171EO15R



TM171EO22R

Accessories for I/O expansion modules

Designation	Description	Cable length (m/ft.)	Unit reference	Weight kg/lb
Accessories to be ordered separately				
Analog output connector (0-10 V outputs) Sold in lots of 5 (item 1)	Cordset equipped with a 4-pin connector at one end	1/3.3 2/6.6	TM171ACB4OAO1M TM171ACB4OAO2M	0.075/ 0.170 0.125/ 0.280
Low voltage connector Sold in lots of 5 (item 2)	Screw terminal block and a cordset equipped with a 20-pin connector at one end	1/3.3 2/ 6.6	TM171ACB4OI1M TM171ACB4OI2M	0.575/ 1.270 1.120/ 2.470
Accessory – Supplied with each expansion module				
LAN expansion bus connector Sold in lots of 5 (item 3)	Cordset equipped with a 3-pin connector at each end	2/6.6	TM171ACB4OLAN	0.060/ 0.130

(1) On the same channel: 2 digital inputs or 2 analog outputs (depending on the configuration).

(2) Minimum set for operating controllers.



Connection accessories (2) for expansion modules:
TM171EO15R, M171EO22R

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Remote displays, Connection accessories for M171 Optimized logic controllers

Remote displays for M171 Optimized logic controllers

The four available remote displays are distinguished by:

- Technology: LED display or LCD display, with or without backlight
- Mounting: flush mounting or wall mounting

The remote displays are connected to the LAN expansion bus which provides the power supply.



TM171DLED (1)



TM171DLCD2U




TM171DWAL2U



TM171DWAL2L



Connection accessories (2) for M171 Optimized logic controller (rail mounting): TM171OBM22R, TM171OD22R, TM171ODM22R and TM171ODM22S for M171 Optimized logic controller (flush mounting): TM171OF22R and TM171OFM22R



Connection accessories (2) for M171 Optimized logic controller (rail mounting): TM171OBM14R, TM171OD14R, TM171ODM14R
N.B.: terminal blocks are supplied with TM171OBM14R, TM171OD14R, and TM171ODM14R



TM171ALAN

Type	Description	Reference	Weight kg/lb
Remote flush mounting displays With realtime clock	<ul style="list-style-type: none"> ■ LED display: 4 digits, 7 segments ■ Keyboard: 4 buttons ■ Communication port: 1 for LAN expansion bus – with wired connector (1) or screw terminal blocks 	TM171DLED	0.042/ 0.090
	<ul style="list-style-type: none"> ■ LCD display (with segments) ■ Keyboard: 7 buttons ■ Flush mounting ■ Communication port: 1 for LAN expansion bus – with screw terminal blocks ■ 2 analog inputs: <ul style="list-style-type: none"> - 1 NTC or digital input - 1 NTC or 4-20 mA or digital input 	TM171DLCD2U	0.170/ 0.370
Remote wall mounting displays With realtime clock	<ul style="list-style-type: none"> ■ Without backlight 	TM171DWAL2U	0.143/ 0.320
	<ul style="list-style-type: none"> ■ With backlight 	TM171DWAL2L	0.143/ 0.320

Connection accessories for M171 Optimized logic controllers to be ordered separately

Type	Item	Description	Cable length (m/ft.)	Unit reference	Weight kg/lb
Low voltage connector Sold in lots of 5	1	Screw terminal block and a cordset equipped with a 20-pin connector at one end	1/3.3	TM171ACB4OI1M	0.575/ 1.270
			2/6.6	TM171ACB4OI2M	1.120/ 2.470
Analog output connector (0-10 V outputs) Sold in lots of 5	2	Cordset equipped with a 4-pin connector at one end	1/3.3	TM171ACB4OAO1M	0.075/ 0.170
			2/6.6	TM171ACB4OAO2M	0.125/ 0.280
Modbus connector Sold in lots of 5	3	Cordset equipped with a 3-pin connector at one end	1/3.3	TM171ACB4ORS485 (3)	0.052/ 0.110
LAN expansion bus connector Sold in lots of 5	4	Cordset equipped with a 3-pin connector at each end	2/6.6	TM171ACB4OLAN	0.060/ 0.130
LAN Communication adaptor Supplied with removable terminal blocs for bus connections		LAN-RS-485 converter (accessory which allows to connect Modbus devices through the LAN connector of the M171 Optimized controller)		TM171ALAN	0.170/ 0.374

(1) Supplied with LAN expansion bus connector TM171ACB4OLAN.

(2) Minimum set for operating controllers.

(3) This product is only compatible for modbus version of M171 Optimized 22 I/Os.

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M171 Performance logic controllers

M171 Performance logic controllers

M171 Performance logic controllers comprise four models that can be used to control from 3 up to 27 embedded I/O (digital and analog).

- Power supply: 24 VAC/DC or 48 VDC
- Two types of housing:
 - with built-in display
 - without display

Each controller includes a connection (through the CAN expansion bus or through Modbus SL) for a remote display, available in the catalog.


- Two types of mounting:
 - On 35 mm/1.38 in rail mounting: controllers to be mounted inside a cabinet
 - Flush mounting: controllers to be mounted on a cabinet door or wall-mounted using the wall bracket accessory;
- Communication ports on M171 Performance logic controllers:
 - One Modbus SL client/server
 - Two USB
 - One CAN expansion bus

On flush mounting version:

- One Modbus SL client/server
- One Modbus TCP and BACnet IP (B-AAC profile) (WebVisu)
- One CAN expansion bus

- M171 Performance logic controllers can be connected to communication modules, adding another connection for the CAN expansion bus, Ethernet network, or Profibus, etc., see [page 42](#).

- M171 Performance logic controllers are certified CE, cURus (UL Recognized), CSA, EAC, RCM, RoHS China.



35 mm/1.38 in rail mounting

TM171P●M27● Performance logic controllers (1)

- 1 Connector for removable terminal block for digital inputs
- 2 Connector for removable terminal block for analog inputs
- 3 Connector for removable terminal block for Modbus SL
- 4 Connector for removable terminal block for CAN expansion bus
- 5 4-position DIP switches for address selection
- 6 Five control keys for setting controller parameters
- 7 Connector for removable terminal block for power supply (24 VAC/DC, 48 VDC)
- 8 Connector for removable terminal block for fast digital inputs (high speed counter)
- 9 Connector for removable terminal block for digital outputs
- 10 Connector for removable terminal block for analog outputs
- 11 Mounting clips for 35 mm/1.38 in rail mounting
- 12 On **TM171PDM27●**: display
On **TM171PBM27R**: 6- and 10-position DIP switches, behind a front panel

Behind the removable protective cover: 13 and 14

- 13 USB-B port to connect a PC
- 14 USB-A port for USB stick
- 15 Connector for communication module
- 16 Three status LEDs


Flush mounting

TM171PFE03R●●● Performance logic controllers (2)

- 1 Display
- 2 Three status LEDs
- 3 Five control keys for setting controller parameters

On the rear side of the controller

- 4 Terminal block for power supply (24 VAC/DC or 48 VDC)
- 5 Terminal block for CAN expansion bus
- 6 Terminal block for Modbus SL
- 7 Terminal block for analog input
- 8 RJ45 connector for Ethernet
- 9 Built-in NTC sensor (analog)



(1) **TM171ASCTB27** removable terminal blocks to be ordered separately, see [page 37](#).

(2) Terminal blocks supplied with flush mounting version of Performance controllers.

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

M171 Performance logic controllers

M171 Performance logic controllers: Power supply: 24 VAC/DC, 48 VDC

35 mm/1.38 in rail mounting

No. of I/O	Number and type of channels	Embedded communication ports	Display	Reference	Weight kg/lb	
	Inputs	Outputs				
27	9 digital inputs (8 + 1): <ul style="list-style-type: none"> 2 groups of 4 digital inputs, 24 VAC/DC or 48 VDC 1x fast digital input, or high speed counter volt-free 6 configurable analog inputs: <ul style="list-style-type: none"> 2x NTC or digital inputs, 4x NTC, or PT1000, or 4-20 mA, or 0-5 V, or 0-10 V, or 0-30 kΩ/0-5 kΩ variable resistor, or digital inputs 	7 digital outputs: <ul style="list-style-type: none"> 2x SPDT (8 A, 230 VAC) with independent common 5x SPST (5 A, 230 VAC) with independent common 5 analog outputs: <ul style="list-style-type: none"> 3x 0...+10 V or 4-20 mA 2x 0...+10 V, or 4-20 mA, or digital output open collector 	<ul style="list-style-type: none"> 1 RS-485 1 CAN expansion bus 	Remote display (optional)	TM171PBM27R	0.385/ 0.850
		7 digital outputs: <ul style="list-style-type: none"> 2x SPDT (8 A, 230 VAC) with independent common 3x SPST (5 A, 230 VAC) with independent common 2x SSR (1 A, 230 VAC) outputs 5 analog outputs: <ul style="list-style-type: none"> 3x 0...+10 V or 4-20 mA 2x 0...+10 V, or 4-20 mA, or digital output open collector 	<ul style="list-style-type: none"> 1 RS-485 1 CAN expansion bus 	Built-in display	TM171PDM27R	0.385/ 0.850
				Built-in display 128x64 LCD with backlight	TM171PDM27S	0.385/ 0.850



TM171PBM27R



TM171PDM27R



TM171PDM27S

Flush mounting (to be used with the wall bracket accessory – see below)

No. of I/O	Number and type of channels	Embedded communication ports	Display	Reference	Weight kg/lb	
	Inputs	Outputs				
3	3 configurable analog inputs: <ul style="list-style-type: none"> 1x built-in NTC 1x NTC or digital input 1x 4-20 mA or 0-10 V 	–		Built-in display	TM171PFE03	0.320/ 0.710



TM171PFE03

Accessories for M171 Performance logic controllers to be ordered separately

Designation	Use	Reference	Weight kg/lb
Screw terminal blocks	For TM171PBM27R , TM171PDM27R , and TM171PDM27S	TM171ASCTB27	0.100/ 0.220
Wall bracket for flush mounting Performance logic controllers	For TM171PFE03	TM171ABKPB	0.015/ 0.030



TM171ASCTB27



TM171ABKPB

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

I/O expansion modules

I/O expansion modules

Two I/O expansion modules are available to increase the number of I/O:

- up to 351 on M171 Performance logic controllers
- up to 366 on M172 logic controllers
- up to 106 on M173 logic controllers,

- Expanded I/O types are digital and analog
- They are connected via the CAN expansion bus on M171 Performance, M172 and M173 Optimized logic controllers
- I/O expansion modules compatibility:

Logic controllers	Compatible I/O expansion module (reference)
M173 Optimized (TM173O●●●●)	TM171EP14R, TM171EP27R
M172 Optimized (TM172O●●●●)	
M172 Performance (TM172P●●●●)	
M171 Performance (TM171P●●●●)	

- They are certified CE, UL, CSA, EAC, RoHS China

35 mm/1.38 in rail mounting I/O expansion modules


TM171EP27R expansion module (1)

- 1 Connector for removable terminal block for digital inputs
- 2 Connector for removable terminal block for analog inputs
- 3 Connector for removable terminal block for Modbus SL
- 4 Connector for removable terminal block for CAN expansion bus
- 5 4-position DIP switches for address selection
- 6 Connector for removable terminal block for power supply (24 VAC/DC, 48 VDC)
- 7 Connector for removable terminal block for fast digital inputs
- 8 Connector for removable terminal block for digital outputs
- 9 Connector for removable terminal block for analog outputs
- 10 Clip-on lock for 35 mm/1.38 in rail mounting
- 11 6- and 10-position DIP switches for address selection
- 12 3 status LEDs

TM171EP14R expansion module (1)

- 1 4-position DIP switches
- 2 Connector for removable terminal block for CAN expansion bus
- 3 Removable terminal block for digital outputs
- 4 Behind the removable protective cover: Service port (TTL)
- 5 Connector for low voltage I/O
- 6 Clip-on lock for 35 mm/1.38 in rail mounting
- 7 Connector for removable terminal block for power supply (24 VAC/DC)

(1) Removable terminal blocks to be ordered separately, see page 39.






TM171EP14R



TM171EP27R




TM171ASCTB14

TM171ASCTB27

I/O expansion modules						
35 mm/1.38 in rail mounting						
No. of I/O	Number and type of channels		Compatibility with logic controller	Embedded communication ports	Reference	Weight kg/lb
	Inputs	Outputs				
14	4 digital inputs: 4x 24 VAC or 24VDC (1) 4 analog inputs: (configurable in pairs) 4x NTC, or PT1000, or PTC, or 4-20 mA, or 0-5 V, or 0-10 V, or digital inputs	4 digital outputs: ■ 1x SPDT (5 A, 230 VAC) with independent common ■ 3x SPST (3 A, 230 VAC) with independent common 2 analog outputs: ■ 2x 0-10 V (1)	TM171P●●●● TM172●●●● TM173O●●●●	● 1 CAN expansion bus	TM171EP14R	0.190/ 0.420
27	9 digital inputs (8 + 1): ■ 2 groups of 4 digital inputs, 24 VAC/DC or 48 VDC ■ 1x fast digital input or high speed counter, volt-free 6 analog inputs: ■ 2x NTC or digital inputs ■ 4x NTC, or 4-20 mA, or 0-10 V, or digital inputs	7 digital outputs: ■ 2x SPDT (8 A, 230 VAC) with independent common ■ 5x SPST (5 A, 230 VAC) with independent common 5 analog outputs: ■ 5x 0-10 V, or 4-20 mA	TM171P●●●● TM172●●●● TM173O●●●●	● 1 CAN expansion bus	TM171EP27R	0.385/ 0.850


Accessories for I/O expansion modules to be ordered separately			
Designation	Description	Unit reference	Weight kg/lb
Screw terminal blocks (inputs, outputs, and communication bus)	14 I/O – For TM171EP14R	TM171ASCTB14	0.050/ 0.110
	27 I/O – For TM171EP27R	TM171ASCTB27	0.100/ 0.220

(1) On the same channel: 2 digital inputs or 2 analog outputs (depending on the configuration).
 (2) Minimum set for operating controllers.




M173 Optimized logic controller and Plug-in Interface for secure Ethernet communication:

- Secure connection via HTTPs (TLS1.2) to the webserver
- Secure email SMTPs (TLS1.2)
- Secure file transport protocol FTPs (TLS1.2)



M172 Performance logic controller and Plug-in Interface for:

- Secure connection via HTTPs (TLS1.2) to the webserver
- Secure email SMTPs (TLS1.2)
- Secure file transport protocol FTPs (TLS1.2)



M171 Optimized / M172 Performance logic controllers and Gateway Interface for cybersecure connection to the cloud for machine monitoring

Secure Interfaces

TM172SI● Secure Interfaces are designed to establish a secure Internet connection, and to connect unsafe devices to a secure Ethernet network.

Two versions are available to perform different types of secured operations, and compatible with existing machines or installations.

- TM172SIP, Plug-in version for M173 Optimized (Din rail mounting version) and M172 logic controllers:
 - to send files to an FTPs server (when related to Secure Interfaces only),
 - to reply to an FTPs client (having an FTPs server),
 - to send e-mails to providers using secure encryption algorithms,
 - to manage SNMP protocol, that allows to exchange Object ID information relating to SNMP protocol in an Ethernet network,
 - to access the machine via a secure webserver.
- TM172SIG, Gateway version ensure a cybersecure connection on M173 Optimized and M172 logic controllers, and on M171 Optimized logic controllers via the Modbus communication module.


■ It is possible to create programs within TM172SI● Secure Interfaces that enable the PLC to locate variables or parameters in connected devices, and to save files on a micro SD, USB memory key, or in the NAND flash memory of TM172SI● Secure Interfaces.

■ Secure Interfaces compatibility:


Logic controller type	Compatible Secure Interface (reference)
M173 Optimized (TM173O●●●●)	TM172SIG
M172 Optimized (TM172O●●●●)	TM172SIP (1)
M172 Performance (TM172P●●●●)	
M171 Optimized (TM171O●●●●)	TM172SIG
M171 Optimized	TM172SIG (2)

- EcoStruxure Machine Expert - HVAC programming software is available to program and customize applications in association with M171, M172 and M173 logic controllers.
- The Secure Interfaces are certified CE, UL, CSA, EAC, RCM, UKCA.
- Secure Interface Security
 - The TM172SI● Secure Interfaces are designed to meet cybersecurity requirements in accordance with the standard IEC 62443-4-1 (2020 edition).
 - Within the TM172SI● interface, you can enhance cybersecurity by the following methods:
 - Configure user rights
 - Disable unused services (for example, FTP, HTTP)
 - Use secure communication to connect to the web server.
 - Follow the Recommended Cybersecurity Best Practices | Schneider Electric.

(1) The TM172SIP module can only be connected to the TM173OD●●●● in DIN rail mounting version.
 (2) When the controller is associated to TM171AMB Modbus communication module.



TM172SIP



TM172SIG

Secure Interfaces

35 mm/1.38 in rail mounting Secure Interfaces (1)

- 1 Connector for removable terminal block for power supply (24 VAC/DC)
- 2 TTL communication port to logic controller (Only on TM172SIP)
- 3 Memory card slot (Micro SD)
- 4 Programmable LEDs (red, yellow, green)
- 5 Power LED (green)
- 6 USB-B port
- 7 USB A port
- 8 Ethernet ports (2x RJ45)
- 9 Serial line port (RS-485) (Only on TM172SIG)

Designation	Description	Reference	Weight kg/lb
Secure Interface Plug-in (1)	Size: 4 DIN (2)	TM172SIP	0.165
	<ul style="list-style-type: none"> ● Double Ethernet port with switch capabilities ● Equipped with a intergrated TTL communication port, to communicate with the controller 		0.363
Secure Interface Gateway (1)	Size: 4 DIN (2)	TM172SIG	0.165
	<ul style="list-style-type: none"> ● Double Ethernet port with switch capabilities ● Equipped with a RS-485 serial port used to communicate with a controller via a Modbus RTU connection 		0.363

(1) Removable screw terminal blocks are included with TM172SIP.

(2) 4 DIN: Interface width is 72 mm (2.83 in).

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Communication modules

Communication modules

The communication module offer is dedicated to M171 Performance, and M172 logic controllers (1).

The 8 optional modules provide specific connections:

- To fieldbuses, including:
 - CAN bus
 - Modbus TCP
 - Profibus (only with M171 Performance)
 - Modbus SL (RS-485)
 - BACnet MS/TP (B-AAC profile)
 - BACnet IP (B-AAC profile)
 - RS 232 serial link
 - LonWorks (FFT-10)
 - Konnex (KNX) via Schneider Electric' spacELynk gateway (1)
- To services, including:
 - Ethernet
 - WebVisu and remote download functions
- They are mounted by simply interlocking on the left-hand side of M171 Performance or M172 logic controllers (1). Only one communication module can be added to a logic controller.
- The communication module is powered by the controller.
- Each communication module has its own type of connector, adapted to the bus or communication network, see page 43.
- Communication modules compatibility:



Logic controllers	Compatible communication modules (reference)
M172 Optimized (TM172O●●●●)	TM171ACAN, TM171AMB, TM171ARS485, TM171ARS232, TM171ALON, TM171AETH, TM171AETHRS485
M172 Performance (TM172P●●●●)	TM171ACAN, TM171AMB, TM171ARS485, TM171ARS232, TM171ALON
M171 Optimized (TM171O●●●●)	-
M171 Performance (TM171P●●●●)	TM171ACAN, TM171AETH, TM171APBUS, TM171AMB, TM171ARS485, TM171ARS232, TM171AETHRS485, TM171ALON

TM171A●●● communication modules

- 1 Communication connector (2)
- 2 Locking device
- 3 Expansion connector to the controller
- 4 Clip-on lock for 35 mm/1.38 in rail mounting

(1) spacELynk offer: please consult the offer on our [website](#).

(2) The communication connector type depends on the communication modules, see page 43.



Communication modules

35 mm/1.38 in rail mounting

Fieldbus, services access	Communication ports	Compatibility with logic controller	Reference (1)	Weight kg/lb
<ul style="list-style-type: none"> ● CAN 	<ul style="list-style-type: none"> ● 2 screw terminal blocks (1) 	M172 Optimized, M172 Performance, M171 Performance	TM171ACAN	0.077/ 0.170
<ul style="list-style-type: none"> ● Modbus TCP ● Ethernet ● BACnet IP (B-AAC profile) ● WebVisu and remote download functions 	<ul style="list-style-type: none"> ● 1 RJ45 	M171 Performance, M172 Optimized,	TM171AETH	0.077/ 0.170
<ul style="list-style-type: none"> ● Profibus 	<ul style="list-style-type: none"> ● 1 SUB-D 9 	M171 Performance,	TM171APBUS	0.077/ 0.170
<ul style="list-style-type: none"> ● Modbus SL (RS-485) 	<ul style="list-style-type: none"> ● 2 screw terminal blocks (1) 	M172 Optimized, M172 Performance, M171 Performance	TM171AMB	0.077/ 0.170
<ul style="list-style-type: none"> ● Modbus SL or BACnet MS/TP (B-AAC profile) 	<ul style="list-style-type: none"> ● 2 screw terminal blocks (1) 	M172 Optimized, M172 Performance, M171 Performance	TM171ARS485	0.077/ 0.170
<ul style="list-style-type: none"> ● RS 232 serial link ● Relay output 	<ul style="list-style-type: none"> ● 1 SUB-D 9 for RS 232 ● 1 screw terminal block for relay output (1) 	M172 Optimized, M172 Performance, M171 Performance	TM171ARS232	0.077/ 0.170
<ul style="list-style-type: none"> ● Modbus TCP and BACnet/IP ● Modbus SL or BACnet MS/TP (B-AAC profile) ● WebVisu and remote download functions ● Ethernet 	<ul style="list-style-type: none"> ● 1 RJ45 for Ethernet ● 2 screw terminal blocks for RS-485 (1) 	M171 Performance, M172 Optimized	TM171AETHRS485	0.077/ 0.170
<ul style="list-style-type: none"> ● LonWorks (FFT-10) 	<ul style="list-style-type: none"> ● 1 screw terminal block for LON bus 	M172 Optimized, M172 Performance, M171 Performance	TM171ALON	0.077/ 0.170

(1) Removable terminal blocks supplied with communication modules.



TM171ACAN



TM171AETH



TM171APBUS



TM171AMB



TM171ARS485



TM171ARS232



TM171AETHRS485



TM171ALON

Modicon M171/M172/M173

Logic controllers for HVAC and Pumping applications

Electronic expansion valve drivers

Electronic expansion valve drivers

Electronic expansion valves drivers are specifically designed to control electronic expansion valves used in various types of refrigeration systems. They regulate the superheat level by modulating the valve position and can be used with various type of refrigerants and for many applications, from small residential unit to large HVAC systems. The control system optimizes the superheat control and increase the energy savings of the unit.

Two versions of drivers:

- **TM172EVEV1●**: Electronic Expansion Valve Drivers that are used in combination with M172 and M173 logic controllers (1). The pressure and temperatures sensors are wired to the controller which manages the control algorithm. The user has the choice to use preprogrammed superheat functions or to create his own control algorithm. This provides a very optimized and flexible solution. Several versions are available depending of the valve technology (unipolar or bipolar) and the number of valves to control (single or dual valves). Those drivers are compatible with the battery backup which provides energy to close the valve in case of power failure.
- **TM171VEVM4**: Superheat Electronic Expansion Valve Driver that can be used independently to any other controller. The temperature and pressure sensors are directly wired to the driver and the embedded control algorithm regulates the superheat. This driver is equipped with Modbus SL communication which allows to communicate with the M171 and M172 logic controllers or third party Modbus devices for remote monitoring and setting configuration.
- Electronic expansion valve drivers compatibility:

Logic controller	Compatible EEVD	
M173 Optimized (Except TM173OFM22S and TM173OFM22R)	TM172EVEV1U TM172EVEV1B TM172EVEV2B	–
M172 Optimized (TM172O●●●●)	TM172EVEV1U TM172EVEV1B TM172EVEV2B	TM171VEVM4
M172 Performance (TM172P●●●●)		
M171 Optimized (TM171O●●●●)	–	
M171 Performance (TM171P●●●●)		

- They are certified CE, UL, CSA, EAC, RoHS China

35 mm/1.38 in rail mounting

TM172EVEV1U, TM172EVEV1B, TM172EVEV2B (2)

- 1 Valve Outputs terminal block - CN2, CN3
- 2 Power supply terminal block - CN4
- 3 Battery backup connector
- 4 CAN Expansion bus port terminal block - CN1
- 5 Clip-on lock for 35 mm/1.38 in rail
- 6 Dip switch
- 7 TTL programming port
- 8 Status LEDs

TM171VEVM4 (1)

- 1 Output terminal block and power supply connector (24 VAC/DC)
 - 2 Protective cover
 - 3 Status LEDs
- Behind the removable protective cover:
- 4 6-position DIP switches
 - 5 Status LED (for operation with TM171AMFK programming stick)
 - 6 LAN serial port for connecting TM171DLED remote display
 - 7 Terminal block for analog/digital inputs
 - 8 Clip-on lock for 35 mm/1.38 in rail mounting
 - 9 Modbus (RS-485) port
 - 10 TTL programming port

(1) Depending on model.


(2) Screw terminal blocks are delivered with electronic expansion valve drivers.




M172 EEVD




M171 EEVD



TM172EVEV1U, TM172EVEV1B



TM172EVEV2B



TM171VEVM4



TM172EEV1U



TM172EEV1B



TM172EEV2B



TM171EVM4



TM172EEVBAT

Electronic expansion valve drivers

M172 EEVD

Application	Communication ports	Size (3)	Reference	Weight kg/lb
EEVD for single valve unipolar (1) (2)	● 1 CAN expansion Bus	2 DIN	TM172EEV1U	0.087/ 0.191
EEVD for single valve bipolar (1) (2)	● 1 CAN expansion Bus	2 DIN	TM172EEV1B	0.089/ 0.196
EEVD for dual valves bipolar (1) (2)	● 1 CAN expansion Bus	4 DIN	TM172EEV2B	0.119/ 0.262

M171 EEVD

Application	Number and type of channels		Reference	Weight kg/lb
	Inputs	Outputs		
Superheat EEVD RS-485 for Modbus SL, for single valve Size: 4 DIN (2) (3)	2 digital inputs: <ul style="list-style-type: none"> ■ 2x volt-free 4 analog inputs: <ul style="list-style-type: none"> ■ 2x NTC ■ 2x PT1000, 4-20 mA, or 0-5 V, or 0-10 V 	2 digital outputs: <ul style="list-style-type: none"> ■ 1x open collector (100 mA, 12 VDC) ■ 1x SPST NO relay contact, 5 A, 250 VAC 	TM171EVM4	0.190/ 0.420













Accessories for electronic expansion valve drivers: to be ordered separately

Designation	Use	To use with	Reference	Weight kg/lb
Battery backup	To provide power when the primary source of power is unavailable.	TM172EEV1U TM172EEV1B TM172EEV2B	TM172EEVBAT	0.157/ 0.346

(1) Compatible with Battery backup TM172EEVBAT.

(2) Removable screw terminal blocks are included with M172/M171 EEVD.

(3) in 2 DIN: controller width is 36 mm (1.41 in) in 4 DIN: controller width is 72 mm /2.83 in).

Temperature and Humidity control						
Designation	Use	Description	Cable length m (ft)	Unit reference	Sold in lots of (1)	Weight kg/lb
NTC probes	 Multi-purpose ■ Applications ■ Temperature control: -50...+110 °C (-122...230 °F)	- IP 68	1.5 (4.92)	TM1STNTCRN52015	8	0.144/0.320
		- Grey	3 (9.84)	TM1STNTCRN5201P	100	0.144/0.320
		- Equipped with 2 conductor cables for controller side	5 (16.40)	TM1STNTCRN52030	5	0.180/0.400
				TM1STNTCRN5203P	50	0.180/0.400
	 Multi-purpose ■ Temperature control: -50...+110 °C (-122...230 °F)	- IP 67	1.5 (4.92)	TM1STNTCRN61515	8	0.104/0.230
		- Black	3 (9.84)	TM1STNTCRN6151P	100	0.104/0.230
		- Equipped with 2 conductor cables for controller side	5 (16.40)	TM1STNTCRN61530	5	0.125/0.280
				TM1STNTCRN6153P	50	0.125/0.280
	 Multi-purpose ■ Temperature control: -50...+110 °C (-122...230 °F)	- FAST	1.5 (4.92)	TM1STNTCSF44015	8	0.144/0.320
		- IP 67	3 (9.84)	TM1STNTCSF44030	5	0.175/0.390
		- Grey		TM1STNTCSF4403P	50	0.175/0.390
	 Multi-purpose ■ Temperature control: -50...+110 °C (-122...230 °F)	- IP 68	1.5 (4.92)	TM1STNTCSN62015	8	0.144/0.320
- Grey		3 (9.84)	TM1STNTCSN6201P	100	0.144/0.320	
- Equipped with 2 conductor cables for controller side		5 (16.40)	TM1STNTCSN62030	5	0.175/0.390	
			TM1STNTCSN6203P	50	0.175/0.390	
 Multi-purpose ■ Temperature control: -50...+110 °C (-122...230 °F)	- IP 68	1.5 (4.92)	TM1STNTCSN62050	4	0.232/0.510	
	- Grey	3 (9.84)	TM1STNTCSN6205P	100	0.232/0.510	
	- Equipped with 2 conductor cables for controller side		TM1STNTCSN62030	5	0.180/0.400	
NTC probes with a strap	 Pipe ■ Temperature control: -50...+110 °C (-122...230 °F)	- IP 68	1.5 (4.92)	TM1STNTCTN62015	8	0.152/0.340
		- Grey	3 (9.84)	TM1STNTCTN6201P	100	0.152/0.340
		- Equipped with 2 conductor cables for controller side		TM1STNTCTN62030	5	0.180/0.400
PT1000 probes	 Multi-purpose ■ Temperature control: -50...+110 °C (-122...230 °F)	- IP 68	1.5 (4.92)	TM1STPTTSN62015	8	0.144/0.320
		- Green	3 (9.84)	TM1STPTTSN6201P	100	0.144/0.320
		- Equipped with 2 conductor cables for controller side	5 (16.40)	TM1STPTTSN62030	5	0.175/0.390
	 Multi-purpose ■ Temperature control: -50...+110 °C (-122...230 °F)	- IP 68	1.5 (4.92)	TM1STPTTSN52015	8	0.136/0.300
		- Green	3 (9.84)	TM1STPTTSN5201P	100	0.136/0.300
		- Equipped with 2 conductor cables for controller side	5 (16.40)	TM1STPTTSN52030	5	0.175/0.390
NTC probe	 Outside air ■ Temperature control: -50...+100 °C (-58...212 °F)	- IP 65		TM1STNTCW69755		0.050/0.110
		- Wall mounting				
	 Inside air (room) ■ Temperature control: -25...+40 °C (-13...104 °F)	- IP 30		TM1STNTCWN75750		0.050/0.110
		- Indoor wall mounting				
		- NTC 10kOhm /25°C				
Humidity probe	 Multi-purpose ■ Humidity control: 0...100%	- IP 65		TM1SHC4		0.140/0.308
		- Wall mounting				
Humidity & temperature probes	 Multi-purpose ■ Humidity control: 0...100% ■ Temperature control: -40...+60 °C (-40...140 °F)	- IP 65		TM1SHTCN4		0.140/0.308
		- Wall mounting				
	- 4-20 mA, NTC 10kOhm /25°C		TM1SHTCC4		0.140/0.308	
	- IP 65		TM1SHTM4		0.140/0.308	
- Wall mounting						
- 2x 4-20 mA						
- IP 65						
- Wall mounting						
- 2x Modbus ports embedded (RS-485 / Modbus RTU)						

(1) The given value is the number of products delivered for one ordered reference.

Application	Type of machine controlled	Compressor			
	Number of phases	3			
	Type of motor	Asynchronous	Asynchronous and Synchronous		Asynchronous and Synchronous for scroll
Compressor size	0.18 kW (0.25 HP)	Altivar 12 Consult catalog Ref. DIA2ED2130101EN	Altivar 320 Consult catalog Ref. DIA2ED2160311EN	Altivar Process ATV600 Consult catalog Ref. DIA2ED2140502EN	Altivar 212 Consult catalog Ref. DIA2ED2101102EN
	0.37 kW (0.5 HP)				
	0.75 kW (1 HP)				
	2.2 kW (0.25 HP)				
	4.0 kW (5 HP)				
	7.5 kW (10 HP)				
	15 kW (20 HP)				
	18.5 kW (25 HP)				
	22 kW (30 HP)				
	30 kW (40 HP)				
	37 kW (50 HP)				
	45 kW (60 HP)				
	55 kW (67 HP)				
	75 kW (100 HP)				
	90 kW (120 HP)				
	110 kW (150 HP)				
	315 kW (422 HP)				
	355 kW (480 HP)				
	400 kW (540 HP)				
	450 kW (603 HP)				
500 kW (670 HP)					
560 kW (750 HP)					
630 kW (850 HP)					
710 kW (950 HP)					
800 kW (1100 HP)					

Application	Type of machine controlled	Fan		
	Number of phases	3		
Fan size	0.18 kW (0.25 HP)	Altivar 12 Consult catalog Ref. DIA2ED2130101EN	Altivar 212 Consult catalog Ref. DIA2ED2101102EN	Altivar Process Drive ATV600 Consult catalog Ref. DIA2ED2140502EN
	0.37 kW (0.5 HP)			
	0.75 kW (1 HP)			
	2.2 kW (0.25 HP)			
	4.0 kW (5 HP)			
	7.5 kW (10 HP)			
	15 kW (20 HP)			
	75 kW (100 HP)			
	> 75 kW (> 100 HP)			

Compatible range of variable speed drives

Software solution



EcoStruxure Machine Expert - HVAC programming software

EcoStruxure Machine Expert - HVAC programming software is compliant with IEC 61131-3. It can be used to develop, configure, and commission HVAC solution systems.

It includes:

- Programming M171, M172 and M173 logic controllers, remote display units and Secure Interfaces
- Setting up expansion buses and networks
- Creating the screen of the displays (built-in and displays of M171, M172 and M173 logic controller offer)
- Configuring BMS communication modules on BACnet MS/TP (B-AAC profile), Modbus SL, Modbus TCP, BACnet MS/TP, BACnet IP (B-AAC profile), and LonWorks (FFT-10)
- Dedicated libraries such as:
 - a library of application function blocks
 - a library of Tested, Validated, and Documented Applications (TVDA)
- Full simulation mode

General characteristics

Programming languages	<ul style="list-style-type: none"> ■ ST (Structured Text) ■ FBD (Function Block Diagram) ■ LD (Ladder) ■ IL (Instruction List) ■ SFC (Sequential Function Chart)
Applications	<ul style="list-style-type: none"> ■ Graphical and text-based languages: <ul style="list-style-type: none"> - Adaptation to each developer background - Library management - Code debugging - Parameter definition - Simulation mode ■ Advanced programming: <ul style="list-style-type: none"> - Vectors - Pointers
System solutions management	<ul style="list-style-type: none"> ■ Multi-target project ■ Management of Modbus data ■ Data exchange between several M171, M172 Performance, and M173 logic controllers
Graphical user interface	<ul style="list-style-type: none"> ■ Graphic display: <ul style="list-style-type: none"> - Multipage - Buttons - Edit box - Static text - Images - Animations - Bars - Lists of data (parameters/variables/alarms) ■ Configurable buttons ■ Multilanguage ■ Automatic documentation
Communication bus configurators	<ul style="list-style-type: none"> ■ Control networks: Modbus TCP, Modbus SL, Profibus ■ Expansion bus fieldbus: CAN expansion bus ■ BMS connectivity: BACnet MS/TP (B-AAC profile), BACnet IP (B-AAC profile), LonWorks (FFT-10), MQTT, SNMP
Advanced simulation options	<ul style="list-style-type: none"> ■ Full simulation <ul style="list-style-type: none"> - I/O emulation - HMI - IEC code - Live debug - Triggers - Oscilloscope
Advanced debugging and simulation options	<ul style="list-style-type: none"> ■ Remote control/download: <ul style="list-style-type: none"> - Modbus SL & TCP - CAN - Modem ■ Parameter management ■ Status monitoring ■ Field test: <ul style="list-style-type: none"> - Oscilloscope - Debug window - Export to Excel

Modicon M171/M172/M173

Logic controllers for HVAC and pumping applications

EcoStruxure Machine Expert - HVAC programming software



EcoStruxure Machine Expert - HVAC programming software

Programming software

EcoStruxure Machine Expert - HVAC software is supplied by downloading from our [website](#)

The product version concerned offers the EcoStruxure Machine Expert - HVAC functions associated with logic controllers.

Operating system

- Windows 10, 64 bit, Windows 11, 64 bit
- Architecture x64
- RAM: 2 GB (4 GB preferred)
- CPU: Intel Core i3 1,6 GHz or later
- Hard Disk: 1 GB free space
- Peripherals: USB, Monitor (1563x864 min/ 1920x1080 recommended), Mouse and Keyboard

Designation	Application	Reference
EcoStruxure Machine Expert - HVAC programming software	Logic controllers, remote display units and Secure Interfaces	Only available as a download from our website

Programming accessories


The USB cable is recommended for local programming.

An Ethernet port is recommended for remote download or remote programming.


Description	Characteristics and use	Length	Reference	Weight kg/lb
Ethernet connection cable (1)	Shielded twisted pair straight cord	2 m/6.56 ft	490NTW00002	–
	Equipped with 1 RJ45 connector at each end	5 m/16.40 ft	490NTW00005	–
	From the PC RJ45 port to the RJ45 port on TM171AETH Communication module and M172 logic controller	12 m/39.37 ft	490NTW00012	–
	CE compatible	40 m/131.23 ft	490NTW00040	–

Programming cable (2)	Between a PC and the TTL programming port of M171 Optimized logic controllers	TM171ADMI	0.157/ 0.350
---------------------------------	---	---------------------------	-----------------

Programming stick (3)	To transfer parameters from one M171 Optimized or M173 Optimized logic controller to another, or to download the program	TM171AMFK	0.010/ 0.020
---------------------------------	--	---------------------------	-----------------




Local programming, download via USB-B port on M171 Performance or M172 logic controllers: any USB-A/USB-B cable can be used



Local programming, download via USB-C port on M173 Optimized logic controllers: any smart-phone cable can be used



Remote programming via USB port on TM171AETH Communication module + M172 Performance logic controller



Local programming, download via TTL port on M171 Optimized logic controllers

#			
490NTW00002	49	TM171PDM27S	37
490NTW00005	49	TM171PFE03	37
490NTW00012	49	TM171VEVM4	45
490NTW00040	49	TM172ABKPG	29
T		TM172ABKPW	29
TM171ABKPB	37	TM172AP12PM	24
TM171ABKPG	29		27
TM171ACAN	43	TM172ASCTB07	24
TM171ACB4OAO1M	31	TM172ASCTB12E	27
	34	TM172ASCTB18	24
	35	TM172ASCTB28	24
TM171ACB4OAO2M	31	TM172ASCTB28E	27
	34	TM172ASCTB42	24
	35	TM172DCLFG	29
TM171ACB4OI1M	31		31
	34	TM172DCLFW	29
	35		31
TM171ACB4OI2M	31	TM172DCLWT	29
	34		31
	35	TM172DCLWTH	29
TM171ACB4OLAN	31		31
	34	TM172DCLWTHP	29
	35		31
TM171ACB4ORS485	31	TM172DGRP	29
	35	TM172E12R	27
TM171ADMI	49	TM172E28R	27
TM171AETH	43	TM172EVEV1B	45
TM171AETHRS485	43	TM172EVEV1U	45
TM171ALAN	35	TM172EVEV2B	45
TM171ALON	43	TM172EVEVBAT	45
TM171AMB	43	TM172OBM18R	24
TM171AMFK	49	TM172OBM28R	24
TM171APBUS	43	TM172OBM42R	24
TM171ARS232	43	TM172ODM18R	24
TM171ARS485	43	TM172ODM28R	24
TM171ASCTB14	39	TM172ODM42R	24
TM171ASCTB27	37	TM172PBG07R	25
	39	TM172PBG18R	25
TM171DLCD2U	31	TM172PBG28R	25
	35	TM172PBG28RI	25
TM171DLED	31	TM172PBG42R	25
	35	TM172PBG42RI	25
TM171DWAL2L	31	TM172PDG07R	25
	35	TM172PDG18R	25
TM171DWAL2U	31	TM172PDG18S	25
	35	TM172PDG28R	25
TM171EO14R	31	TM172PDG28RI	25
	34	TM172PDG28SI	25
	35	TM172PDG42R	25
TM171EO15R	31	TM172PDG42RI	25
	34	TM172PDG42S	25
TM171EO22R	31	TM172PDG42SI	25
	34	TM172SIG	31
TM171EP14R	39		41
TM171EP27R	39	TM172SIP	41
TM171OBM14R	31	TM173ACB1M	19
	33	TM173ACB2M	19
TM171OBM22R	33	TM173DLED	19
TM171OD14R	31	TM173OBM22R	17
	33		19
TM171OD22R	33	TM173OBM22RH	17
TM171ODM14R	31		19
	33	TM173ODEM22R	17
TM171ODM22R	33		19
TM171ODM22S	33	TM173ODM15R	17
TM171OF22R	33		19
TM171OFM22R	33		
TM171PBM27R	37		
TM171PDM27R	37		
		TM173ODM22R	17
			19
		TM173ODM22RH	17
			19
		TM173ODM22S	17
			19
		TM173ODM22SH	17
			19
		TM173OFM22R	17
			19
		TM173OFM22S	17
			19
		TM1SHC4	46
		TM1SHTCC4	46
		TM1SHTCN4	46
		TM1SHTM4	46
		TM1STNTCRN52015	46
		TM1STNTCRN5201P	46
		TM1STNTCRN52030	46
		TM1STNTCRN5203P	46
		TM1STNTCRN52050	46
		TM1STNTCRN61515	46
		TM1STNTCRN6151P	46
		TM1STNTCRN61530	46
		TM1STNTCRN6153P	46
		TM1STNTCRN61550	46
		TM1STNTCRN6155P	46
		TM1STNTCSF44015	46
		TM1STNTCSF44030	46
		TM1STNTCSF4403P	46
		TM1STNTCSN62015	46
		TM1STNTCSN6201P	46
		TM1STNTCSN62030	46
		TM1STNTCSN6203P	46
		TM1STNTCSN62050	46
		TM1STNTCTN62015	46
		TM1STNTCTN6201P	46
		TM1STNTCTN62030	46
		TM1STNTCW69755	46
		TM1STNTCWN75750	46
		TM1STPTTSN52015	46
		TM1STPTTSN5201P	46
		TM1STPTTSN52030	46
		TM1STPTTSN5203P	46
		TM1STPTTSN52050	46
		TM1STPTTSN5205P	46
		TM1STPTTSN62015	46
		TM1STPTTSN6201P	46
		TM1STPTTSN62030	46
		TM1STPTTSN6203P	46
		TM1STPTTSN62050	46

mySchneider, your personalized digital experience

Access an all-in-one customized online experience and benefit from tailored business services, resources, and tools to efficiently support your business operations.

- **Efficiency:** In just a few clicks, find all the information and support you need to get the job done.
- **Simplicity:** Use a single login to access all business services, in one place, available 24/7. You no longer need to log in to multiple platforms.
- **Personalization:** Benefit from content, tools, and business services tailored to your activity, and customize your landing page based on your preferences.

Watch the How-to Videos



Order management

- > [Select Products and Add to Cart](#)
- > [Check for Products' Price and Availability](#)
- > [Order Products with Generic Commercial References](#)




Product information

- > [Find a Product Data Sheet and Related Documents](#)
- > [Select Products and Add to Cart](#)
- > [Stay Up to Date on the Status of My Products](#)



Support

- > [Get Quicker Answers Thanks to Online Support](#)



Training

- > [Access Trainings Dedicated to My Activity](#)

[Create your account](#)

Life Is 

Schneider
Electric

Legal information

The information provided in this Catalog contains description of Schneider Electric products, solutions and services ("Offer") with technical specifications and technical characteristics of the performance of the corresponding Offer.

The content of this document is subject to revision at any time without notice due to continued progress in methodology, design and manufacturing.

To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any type of damages arising out of or in connection with (i) informational content of this Catalog not conforming with or exceeding the technical specifications, or (ii) any error contained in this Catalog, or (iii) any use, decision, act or omission made or taken on basis of or in reliance on any information contained or referred to in this Catalog.


SCHNEIDER ELECTRIC MAKES NO WARRANTY OR REPRESENTATION OF ANY KIND, WHETHER EXPRESS OR IMPLIED, AS TO WHETHER THIS CATALOG OR ANY INFORMATION CONTAINED THEREIN SUCH AS PRODUCTS AND SERVICES WILL MEET REQUIREMENTS, EXPECTATIONS OR PURPOSE OF ANY PERSON MAKING USE THEREOF.

Schneider Electric brand and any trademarks of Schneider Electric and its subsidiaries referred to in this Catalog are property of Schneider Electric or its subsidiaries. All other brands are trademarks of their respective owners.

This Catalog and its content are protected under applicable copyright laws and provided for informative use only. No part of this Catalog may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Copyright, intellectual, and all other proprietary rights in the content of this Catalog (including but not limited to software, audio, video, text, and photographs) rests with Schneider Electric or its licensors. All rights in such content not expressly granted herein are reserved. No rights of any kind are licensed or assigned or shall otherwise pass to persons accessing this information.

Life Is On



Learn more about our products at
www.se.com

Design: Schneider Electric
Photos: Schneider Electric

Schneider Electric Industries SAS

Head Office
35, rue Joseph Monier - CS 30323
F-92500 Rueil-Malmaison Cedex
France

DIA3ED2151001EN
February 2026 - V9.1