



OUTPUT SWITCH SPECIFICATIONS:	
RATED OPERATIONAL CURRENT	80A
RATED OPERATIONAL VOLTAGE	400 V
FREQUENCY	50 / 60 Hz
POLE DESCRIPTION	3P
SHORT CIRCUIT CAPACITY (Isc)	20 kA

- NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL ELECTRICAL REGULATIONS.
 2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
 3. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
 4. ALL DIMENSIONS EXCLUDES SCREW PROJECTIONS OUTSIDE THE ENCLOSURE.
 5. OPERATING TEMPERATURE: 32°F TO 104°F [0°C TO 40°C].
 6. PROTECTION CLASS IP20.
 7. COLOR: RAL 9003, GLOSS LEVEL 85%.
 8. WEIGHT OF THE UNIT IS 31 lbs (14 kg).
 9. REFER TO SYSTEM ONE LINE DIAGRAM GVSUPS20K100B3H-SD FOR CONNECTION DETAILS.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

Schneider Electric

TITLE: Galaxy VS Output Switch Box
GENERAL ARRANGEMENT

PROJECT: SUBMITTAL DRAWINGS SHEET 1 OF 1

DWG NO: GVSOPT037 REV. 0

DRAWN BY: RANJITHA 17-SEP-21 THIRD ANGLE PROJECTION

ENGINEER: NILESH 04-OCT-21

APPROVED BY: PRASANNA 04-OCT-21