

#### NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
3. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].
4. FRONT/REAR/SIDE SERVICE, VENTILATION CLEARANCE REQUIRED. CONSULT WITH THE LOCAL SAFETY CODES AND STANDARDS FOR ANY ADDITIONAL REQUIREMENTS OF LOCAL AREA.
5. COLOR: RAL 9003.
6. PROTECTION CLASS: IP20.
7. OPERATING TEMPERATURE: 0°C TO 40°C [32°F TO 104°F].

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.


**Schneider Electric**

TITLE:  
EASY UPS 3S PRO  
10 - 20kVA, 400V, 3:3 UPS  
FOR INTERNAL BATTERIES  
GENERAL ARRANGEMENT


PROJECT: SUBMITTAL DRAWINGS SHEET 1 OF 4

DWG NO:		E3SP10K20HB		REV.
DRAWN:	KARTHIKEYAN K	19-SEP-25	FIRST	ANGLE
ENGINEER:	YAPING YANG	19-SEP-25	19-SEP-25	PROJECTION
APPROVED:	DAVE DONG	19-SEP-25		

SKU NUMBER	NET WEIGHT IN kg [lb]	CENTER OF GRAVITY IN mm [inches]		
		X-Distance	Y-Distance	Z-Distance
E3SP10KHB	119 [262.3]	183 [7.20]	767 [30.20]	406 [16.00]
E3SP15KHB	119 [262.3]			
E3SP20KHB	119 [262.3]			



TOP VIEW



BOTTOM VIEW

- NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
  2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
  3. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

**Schneider Electric**

TITLE:  
EASY UPS 3S PRO  
10 - 20KVA, 400V, 3:3 UPS  
FOR INTERNAL BATTERIES  
TOP & BOTTOM VIEWS

PROJECT: SUBMITTAL DRAWINGS SHEET 2 OF 4

DWG NO: E3SP10K20HB




DRAWN: KARTHIKEYAN K 19-SEP-25

ENGINEER: YAPING YANG 19-SEP-25

APPROVED: DAVE DONG 19-SEP-25


REV. 0

FIRST ANGLE PROJECTION




NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
3. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].



4 PARALLEL BOARD



PARALLEL CONNECTION

NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
  2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
  3. UP TO 4 NUMBERS OF UPS CAN BE CONNECTED IN PARALLEL. MAXIMUM COMMUNICATION CABLE LENGTH IS 15 Meters.
- ▲ PARALLEL BOARD SETTINGS:
- REMOVE JUMPERS FROM THE PARALLEL BOARD ACCORDING TO YOUR SYSTEM:
- a. IN PARALLEL SYSTEM WITH TWO UPSs, REMOVE JUMPERS FROM J34, J36, J38, J40 AND 42 ON BOTH BOARDS
  - b. IN PARALLEL SYSTEMS WITH THREE OR FOUR UPS, REMOVE THE JUMPERS FROM J33, J34, J35, J36, J37, J38, J39, J40, J41, J42 ON ALL PARALLEL BOARDS.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE:  
EASY UPS 3S PRO  
10 - 20kVA, 400V, 3:3 UPS  
FOR INTERNAL BATTERIES  
PARALLEL CONNECTION  
PROJECT: SUBMITTAL DRAWINGS SHEET 4 OF 4

DWG NO:	E3SP10K20HB	REV.	0
DRAWN:	KARTHIKEYAN K	19-SEP-25	FIRST
ENGINEER:	YAPING YANG	19-SEP-25	ANGLE
APPROVED:	DAVE DONG	19-SEP-25	PROJECTION