




Ref. Certif. No.

DK-154305-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Cam Switches
Name and address of the applicant	Schneider Electric Industries SAS 35 Rue Joseph Monier Rueil Malmaison 92500 France
Name and address of the manufacturer	Schneider Electric / DBA Telemecanique Zone Industrielle BP660 L'Isle D'Espagnac 16340 France
Name and address of the factory	SCHNEIDER ELECTRIC a.s. CIZOVSKA 447 PISEK 397 01 Czech Republic <input type="checkbox"/> Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	- degree of protection : IP40 front plate fixing, IP65 diameter 22 mm hole fixing, IP20 contact block <input checked="" type="checkbox"/> Additional Information on page 2
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	K1 Series: K1A001BCH, K1D023MXH, K1C002DLH, K1H008AXH, K1F006ACH, K1C003ALH, K1A001ALH. K2 Series: K2C003ALH, K2A001ALH, K2F006ACH
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60947-3:2020, IEC 60947-1:2020
As shown in the Test Report Ref. No. which forms part of this Certificate	4790788174.2 issued on 2024-06-17

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/hcbnames

Date: 2024-06-20

Signature: Thomas Wilson



Ref. Certif. No.

DK-154305-UL

Additional Ratings:

- number of poles : 2P, 3P, 4P
- kind of current : AC
- number of phases and rated frequency :3-phase 50/60Hz
- Rated and limiting values, main circuit:
 - rated operational voltage Ue (V) : AC 230V, 400V, 690V
 - rated insulation voltage Ui (V) : 690V
 - rated impulse withstand voltage Uimp (kV) : 6kV
 - conventional free air thermal current Ith (A) :12A(K1 type), 20A(K2 type)
 - conventional enclosed thermal current Ithe (A) :10A(K1 type), 16A(K2 type)
 - rated operational current Ie (A) :
12A (K1 type), 20A (K2 type)
10A (K1 type), 16A (K2 type)
- AC-15: 230V/3A, 400V/2A, 690V/1A (K1 type)
- AC-15: 230V/4A, 400V/3A, 690V/2A (K2 type)
- utilization category : AC-3, AC-21A, AC-23A

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2024-06-20

Signature:

Thomas Wilson