Schneider Back-UPS[™] SX3800CI/SX31K1CI User Guide

Place and Power On

Place the Back-UPS to avoid:Direct sunlight

Direct sunlight
 Excessive heat

 $(\mathbf{4})$


- Excessive heat Excessive moisture
- 2 Connect the battery by pulling the battery connector handle down, and then pushing it into the unit.

Plug the Back-UPS SX3800CI/SX31K1CI power cord directly into a wall outlet; not into a surge protector or power strip.

Press the ON/OFF button to turn on the unit.

The green "On Line" indicator confirms that the Back-UPS is on and ready to provide protection.

The Back-UPS should charge for at least 10 hours to ensure sufficient runtime. The unit is being charged whenever it is connected to AC power, whether the unit is turned ON or OFF.



Status Indicators

| Status | LED Indicator | Audible Alarm | Audible Alarm Terminates | |
|--|---|---|--|--|
| Power On The Back-UPS is supplying AC power to connected equipment. | The On Line LED illuminates green. | None | N/A | |
| On Battery The Back-UPS is supplying battery power to battery backup outlets. | The On Line LED illuminates green. The LED is not illuminated during the beeps. | Back-UPS beeps 4 times every 30 seconds. | The beeping stops when AC power is restored or the Back-UPS is turned off. | |
| Low Battery warning The Back-UPS is supplying battery power to the battery backup outlets and the battery is near a total discharge state. | The On Line LED flashes green. | The Back-UPS emits rapid beeping. (once every second) | The beeping stops when AC power is restored or the Back-UPS is turned off. | |
| Replace Battery The battery is disconnected. The battery needs to be charged or replaced. | The Battery LED flashes red. Battery and On Line LEDs flash alternately. | Constant tone | The Back-UPS is turned off. | |
| Overload Shutdown While operating on battery power an overload condition has occurred in one or more of the battery backup outlets. | None | Constant tone | The Back-UPS is turned off. | |
| Sleep Mode While operating on battery power the battery is completely discharged. The Back-UPS will awaken once AC power is restored. | None | The Back-UPS beeps once every four seconds. | AC power is restored AC power is not restored within 32 seconds The Back-UPS is turned off | |
| Overload Alarm The equipment connected to the Back-UPS is drawing more power than the voltage rating allows. | The Battery LED illuminates red. | Constant tone | Alarm stops when nonessential equipment is disconnected from the Battery Backup outlets. | |

Adjust Transfer Voltage and Sensitivity Settings

Automatic Voltage Regulation boosts the AC voltage when it drops below safe levels. This allows the equipment plugged into the unit to operate during low voltage conditions, conserving the battery power in the event of a power cut.

The Back-UPS will switch to battery power if the input voltage level becomes too low for the Automatic Voltage Regulation to compensate, or if the AC power is distorted.

If the Back-UPS switches to battery power too frequently or too infrequently, adjust the transfer voltage and sensitivity settings:

- 1. Verify that the Back-UPS battery is connected. Connect the Back-UPS to a wall outlet. The Back-UPS should be turned off.
- 2. Press and hold the ON/OFF button for 10 seconds. The LEDs will illuminate green and red alternately, to indicate that the Back-UPS is in **Program** mode.
- 3. The LEDs will flash either green, red or green and red alternately to indicate the current sensitivity level. The Back-UPS will beep to indicate that No-load Shutdown is enabled. Refer to the table for an explanation of the transfer voltage sensitivity levels.
- 4. To select LOW sensitivity, press the ON/OFF button until the **On Line** LED flashes green.
- 5. To select MEDIUM sensitivity, press the ON/OFF button until the **Battery** LED flashes red.
 6. To select HIGH sensitivity, press the ON/OFF button until the **On Line** and **Battery** LEDs
- 6. To select HIGH sensitivity, press the ON/OFF button until the **On Line** and **Battery** LEDs flash green and red alternately. 7. To avit **Program** mode wait for five seconds and both LEDs will extinguish **Program** mode
- 7. To exit **Program** mode wait for five seconds and both LEDs will extinguish. **Program** mode is no longer active..

No-load Shutdown

The UPS will shut down to conserve energy if while operating on battery power the UPS detects that connected equipment is using less than 15 W of energy for more than 15 minutes. No load shutdown can be enabled or disabled through **Program** mode.

| LED Flashes | Audible Indicator | Voltage Sensitivity Setting | Input Voltage Range | No-load Shutdown | Description |
|------------------|-----------------------|-----------------------------------|---------------------------|---------------------|--|
| Green | None | Low | 150-280 | Disabled | Use this setting with equipment that is less sensitive to fluctuations in voltage or waveform distortions. |
| Green | 4 beeps per second | Low | 150-280 | Enabled | Use this setting with equipment that is less sensitive to fluctuations in voltage or waveform distortions. |
| Red | None | Medium | 155-280 | Disabled | Use this setting for normal operation conditions. |
| Red | 4 beeps per second | Medium (factory default) | 155-280 | Enabled | Use this setting for normal operation conditions. |
| Green and Red | None | High | 160-280 | Disabled | Use this setting when connected equipment is sensitive to voltage fluctuations or waveform distortions. |
| Green and Red | 4 beeps per second | High | 160-280 | Enabled | Use this setting when connected equipment is sensitive to voltage fluctuations or waveform distortions. |

Specifications

| Specification | | SX3800CI | SX31K1CI | |
|------------------|-------------------------|---|-----------------------------|--|
| | Voltage | 230 Vac, nominal | | |
| Input | Frequency | 50 Hz ±3 Hz, 60 Hz ±3 Hz | | |
| | Brownout Transfer | 155 Vac, typical | | |
| | Over-voltage Transfer | 280 Vac, typical | | |
| Output | UPS Capacity (total) | 800 VA / 480 W | 1100 VA / 660 W | |
| | Voltage On Battery | 230 Vac rms (step-approximated sinewave) | | |
| | Frequency on Battery | 50 Hz ±1 Hz, 60 Hz ±1 Hz | | |
| | Transfer Time | 8 ms typical | | |
| Protection | AC Surge Protection | Full time, 273 Joules | | |
| and Filtering | AC Input | Resettable circuit breaker | | |
| | Type (maintenance free) | 12 V 9 Ah | Each battery 12 V 7.2 Ah | |
| Battery | Average Life | 2 - 5 years depending on the number of discharge cycles and environmental temperature | | |
| | Typical Recharge Time | 8 Hours | | |
| Physical | Net Weight | 8 kg | 12 kg | |

Troubleshooting and Service

1. Consult the Troubleshooting from the Schneider Electric Web site, www.apc.com.

- 2.If the problem persists, contact Schneider Electric IT (SEIT) Customer Support through the Schneider Electric Web site, **www.apc.com**.
 - a. Note the model number and serial number and the date of purchase. The model and serial numbers are located on the rear panel of the unit and are available through the LCD display on select models.
 - b. Call SEIT Customer Support and a technician will attempt to solve the problem over the phone. If this is not possible, the technician will issue a Returned Material Authorization Number (RMA#).
 - c. If the unit is under warranty, the repairs are free.
 - d. Service procedures and returns may vary internationally. Refer to the Schneider Electric Web site for country specific instructions.
- 3. Prepare to troubleshoot the problem over the phone. If this is not successful, and the unit is still under warranty, the Technical Support Representative will provide all necessary information to return the unit for replacement.

| Ilysical | Dimensions (H x W x D) | 21.5 cm x 13 c | cm x 33.6 cm |
|----------|------------------------|----------------|--------------|
| | | | |

Battery Replacement

The battery in the Back-UPS 800CI/1100CI is not user-replaceable. Contact SEIT Technical Support for a list of authorized service centers near you.

Warranty

Register your product on-line. http://warranty.apc.com

The standard warranty is two (2) years from the date of purchase. SEIT standard procedure is to replace the original unit with a factory reconditioned unit. Customers who must have the original unit back due to the assignment of asset tags and set depreciation schedules must declare such a need at first contact with an SEIT Technical Support representative. SEIT will ship the replacement unit once the defective unit has been received by the repair department, or cross-ship upon the receipt of a valid credit card number. The customer pays for shipping the unit to SEIT. SEIT pays ground freight transportation costs to ship the replacement unit to the customer.

Schneider Electric IT Customer Support Worldwide

For country specific customer support, go to the Schneider Electric Web site, www.apc.com.

EN 990-5188 07/2013

© 2013 Schneider Electric. APC, the APC logo and APC, the APC logo, and Back-UPS are owned by Schneider Electric Industries S.A.S. or their affiliated companies. All other trademarks are property of their respective owners.