



Certificate of Conformity

Number NMI-CoC-24.11
Project number 3195407
Page 1 of 3

Issued by : NMI Certin B.V.
Thijssseweg 11
2629 JA Delft
The Netherlands

Applicant : Schneider Electric Canada Inc.
2195 Keating Cross Road
Saanichton, BC V8M 2A5
Canada

Submitted : **Static electrical energy meter**

Manufacturer : Schneider Electric
Type : PowerLogic ION7400 (METSEION74xx)
Destined for the measurement of : Electrical active / reactive energy in a
- three-phase four-wire network
- three-phase three-wire network

In accordance with : See page 2

Characteristics : See page 3

The undersigned declares that the described product is tested according to the standards as referred to on page 2 and meet their requirements, based on a non-recurrent examination. The appertaining test data is presented in the type evaluation reports NMI-3195407-01, NMI-3195407-02, NMI-3600522-02, NMI-2528595-01b and NMI-2553437-01 granted by NMI, and including external test reports 12046-1E and 16741-1E issued by LabTest Certification Inc, Canada and E189364-D1000-1/A3/C2-CB issued by UL.

NMI Certin B.V.
26 March 2024

Certification Board

NMI Certin B.V.
Thijssseweg 11
2629 JA Delft
The Netherlands
T +31 88 636 2332
certin@nmi.nl
www.nmi.nl

This document is issued under the provision that no liability is accepted and that the applicant shall indemnify third-party liability.

Reproduction of the complete document only is permitted.

This document is digitally signed and sealed. The digital signature can be verified in the blue ribbon at the top of the electronic version of this certificate.



Certificate of Conformity

Number NMI-CoC-24.11
Project number 3195407
Page 2 of 3

IEC 62052-11: 2020

"Electricity metering equipment - General requirements, tests and test conditions - Part 11: Metering equipment"

IEC 62053-22: 2020

"Electricity metering equipment - Particular requirements - Part 22: Static meters for AC active energy (classes 0,1 S, 0,2 S and 0,5 S)"

IEC 62053-24: 2020

"Electricity metering equipment - Particular requirements - Part 24: Static meters for fundamental component reactive energy (classes 0,5S, 1S, 1, 2 and 3)"

IEC 62052-31: 2015

"Electricity metering equipment (AC)-General requirements, tests and test conditions- Part 31: Product safety requirements and tests"

IEC 61000-4-19: 2014

"Electromagnetic compatibility (EMC) - Part 4-19: Testing and measurement techniques - Test for immunity to conducted, differential mode disturbances and signalling in the frequency range 2 kHz to 150 kHz at a.c. power ports";

Characteristics of the measuring instrument

Model	ION7400 (METSEION74xx)
Accuracy class	0,25 for active energy (IEC 62053-22) 0,55 for reactive energy (IEC 62053-24)
Destined for the measurement of	electrical energy, in a - three-phase four-wire network - three-phase three-wire network
U_{n-min} U_{n-max}	3 x 57/ 100 V 3 x 400/ 690 V
I_n	5 A
I_{max}	10 A
f_{ref}	50 and 60 Hz
Relevant product standards	IEC 62052-31:2015
Classification of installation and use	OVC III / CAT III
Environmental conditions	Operation : -25 °C ... +70 °C Storage : -40 °C ... +85 °C Altitude : up to 3000 m Pollution degree : 2 (indoor) Location : dry
Degree of protection	IP 54 (Panel mount)
Protective class	II
Rated impulse voltage	Up to 6 kV (BI) or 8kV (RI/DI)
Software version	004.xxx.xxx, with x being any number
Hardware version	IO board: MFR3370329 CVM board: MFR3370629 PSU board: MFR3370429 PSU LV-DC-DC board: QGH244130
Aux Power supply	
AC/DC Power supply	90 - 415 VAC / 110 - 415 VDC
LV DC Power supply	20 - 60 VDC
Rated Frequency	50 and 60 Hz