


Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

LR3D340



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Termination Method: Screw Clamp
 UL File/CCN: E164353 / NKCR
 CSA File: LR43364 3211 03
 Meets Standard: IEC 60947-1
 CE: Yes
 RoHS: Yes
 Weight: 0.84 lb (0.38 kg)
 Power Wire Size : #2 - #16 AWG
 Control Wire Size: #12 - #20 AWG
 Power Terminal Torque: 70 lb-in (8 Nm)
 Control Terminal Torque: 15 lb-in (1.7 Nm)
 Mtg. Directly to Contactor: Yes
 Mtg. Separate from Contactor: Panel or DIN

Specification:

Description: TeSys D IEC Overload Relays, Amb. Comp. Bimetallic Class 10 wo Single Phase Sensitivity
 Type: TeSys D IEC Bi-Metallic Overload Relay with Everlink 600V 40A
 Ambient Comp. Bimetallic: Yes
 Solid State: No
 Class 10: Yes
 Class 20: No
 Single Phase Sensitivity: No
 For Use with Contactors: LC1D40A thru LC1D65A
 Current Setting Range: 25A to 40A