


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**LRD086**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Termination Method: Ring-Tongue  
 UL File/CCN: E164353 / NKCR  
 CSA File: LR43364 3211 03  
 Meets Standard: IEC 60947-1  
 CE: Yes  
 RoHS: Yes  
 Weight: 0.12 lb (0.27 kg)  
 Power Wire Size : Lug Size 0.32 in (8mm)  
 Control Wire Size: Lug Size 0.32 in (8mm)  
 Power Terminal Torque: 15 lb-in (1.7 Nm)  
 Control Terminal Torque: 15 lb-in (1.7 Nm)  
 Mtg. Directly to Contactor: Yes  
 Mtg. Separate from Contactor: LAD7B10

**Specification:**

Description: TeSys D IEC Overload Relays, Amb. Comp. Bimetallic Class 10 w Single Phase Sensitivity  
 Type: TeSys D IEC Bi-Metallic Overload Relay 600V 4.0A  
 Ambient Comp. Bimetallic: Yes  
 Solid State: No  
 Class 10: Yes  
 Class 20: No  
 Single Phase Sensitivity: Yes  
 For Use with Contactors: LC1D09 thru LC1D32  
 Current Setting Range: 2.5A to 4.0A