

SpaceLogic Sensors

SLP Series PM Sensors – BACnet and Modbus



Note: A subset of models shown.

Product Description

The SpaceLogic SLP PM (Particulate Matter) Series of air quality sensors for living space is a flexible multisensor platform for use with BAS controllers designed to accept BACnet or Modbus outputs. Housings are available in Medium matte white and Optimum faces available in black and white. All housing types are available with touchscreen and blank user interface options. The SLP PM Series offers an all-in-one sensor with temp, RH, CO₂, VOC, PM1, PM2.5, PM4 and PM10.

Features

- Medium matte white housing or optimum glass panel housing available in white or black
- Laser-scatter type PM sensor featuring innovative contamination resistance technology for highly accurate measurement of particulate matter
- Manual and auto field calibratable non-dispersive infrared CO₂ sensor
- VOC sensor available
- Quick to commission with DIP switch selectable outputs
 - BACnet, Modbus via RS-485
- Selectable BACnet MSTP and Modbus outputs via RS-485
- Temperature output value shown as default main value on touchscreen displays
- 61 mm (2.4") backlit color touchscreen
 - Dedicated screen for all PM values
 - Digital temperature indication (0.1° display resolution of °F or °C)
 - Digital humidity indication (0.1% RH display resolution)
 - Digital CO₂ indication (1 ppm display resolution)
 - Stoptlight feature for visual indication at user-configurable CO₂ and PM threshold levels (touchscreen models only)
 - Selectable temp, RH and fan speed setpoint
 - Configurable screen lock and display timeout
 - Override
- 18-24 AWG screw terminals

Available Products

Model Number	Description	User Interface	Housing Finish
SLPSTCVP2	Sensor, PM, CO ₂ , VOC, RH, Temp, Touch, BAC/MB	Touchscreen	Medium White
SLPBTCVP2	Sensor, PM, CO ₂ , VOC, RH, Temp, Touch, BAC/MB, Optm Bk	Touchscreen	Optimum Black
SLPWTCVP2	Sensor, PM, CO ₂ , VOC, RH, Temp, Touch, BAC/MB, Optm Wh	Touchscreen	Optimum White
SLPSXCVP2	Sensor, PM, CO ₂ , VOC, RH, Temp, BAC/MB	Blank	Medium White
SLPBXCVP2	Sensor, PM, CO ₂ , VOC, RH, Temp, BAC/MB, Optm Bk	Blank	Optimum Black
SLPWXCVP2	Sensor, PM, CO ₂ , VOC, RH, Temp, BAC/MB, Optm Wh	Blank	Optimum White

Replaceable PM Elements

Model Number	Description
SLXPMS	Replaceable Module, PM

USA: +1 888-444-1311
 Europe: +46 10 478 2000
 Asia: +65 6484 7877
www.schneider-electric.com

Life Is On



Specifications

Operating Environment			
Input power	Class 2; 20 to 30 Vdc, 24 Vac, 50 to 60 Hz		
Protocol output	BACnet or Modbus via RS-485, selectable		
Operating temp. range	0 to 50 °C (32 to 122 °F)		
Operating humidity range	0 to 95% RH non-condensing		
Housing material	High impact ABS plastic		
IP rating	IP 30		
Mounting location	For indoor use only. Not suitable for wet locations.		
Surface mount	The device can be surface mounted on Single Gang J-Box, British Standard and CE60 wall boxes		
PM Sensor			
Sensor type	Laser-scatter		
Output range	0 to 1,000 µg/m ³		
Accuracy	PM1 and PM2.5: 0 to 100 µg/m ³ +/-[5µg/m ³ +5% m.v.], 100 to 1,000 µg/m ³ +/-[10% m.v.] PM4 and PM10 ¹ : 0 to 100 µg/m ³ +/-[25µg/m ³], 100 to 1,000 µg/m ³ +/-[25% m.v.] (sensor-to-sensor deviation)		
Resolution	0.1 µg/m ³		
CO ₂ Sensor			
Sensor type	Non-dispersive infrared (NDIR), diffusion sampling		
Output range	0 to 10,000 ppm		
Accuracy	±30 ppm ±3% of measured value		
Resolution	1 ppm		
Repeatability	±20 ppm ±1% of measured value		
Response time	<60 seconds for 90% step change		
VOC Sensor			
Sensor type	Solid state		
Output range	0 to 100% AQI for VOC		
Accuracy	±15% of measured value		
Resolution	1 ppb		
Output scale	0 to 1,000 ppb of total VOC (TVOC)		
AQI table ²	Level	Ventilation Recommendation	TVOC (ppb)
	>61%	Greatly increased	>610
	20 to 61%	Significantly increased	200 to 610
	10 to 20%	Slightly increased	100 to 200
	5 to 10%	Average	50 to 100
	0 to 5%	Target value	0 to 50
RH Sensor			
Sensor type	Solid state capacitive, replaceable		
Output range	0 to 100% RH		
Accuracy (includes Hysteresis) ³	±3.8% RH from 10 to 60% RH @ 25°C (77 °F) ±4.8% RH from 60 to 80% RH @ 25°C (77 °F) ±5.8% RH from 80 to 100% RH @ 25°C (77 °F)		
Resolution	0.1% RH		
Linearity	Included in accuracy specification		
Stability	±1% @ 20°C (68 °F) annually for 2 years		
Temperature coefficient	±0.1% RH/°C above or below 25 °C (77 °F) typical		
Temperature Sensor			
Sensor type	Solid state, integrated circuit		
Output range	0 to 50 °C (32 to 122 °F)		
Accuracy	±0.2 °C (±0.4 °F) typical		
Resolution	0.1 °C (0.1 °F)		
Display Models			
Touchscreen	61 mm (2.4 in), color, backlit, capacitive, 240x300px Setpoint: Temperature, humidity or fan speed selectable Timeout override: Display timeout Lockout override: Touchscreen/button lockout		
Setpoints ⁴			
Temperature setpoint	Scale: 0 to 50 °C (32 to 122 °F) max., adjustable span		
Humidity setpoint	Scale: 0 to 100% RH		
Fan speed setpoint	Off, Low, Medium, High, Auto		
Override			
Override button	Display models feature momentary override button		
Wiring			
Terminal blocks	Screw terminals, 18-24 AWG		
Screw terminal torque	0.2 N-m (2.0 in-lbF) max.		
EBO integration ⁵	Download Modbus Device Type template for Modbus models from the Building Application tool.		
Warranty			
Limited warranty	5 years		

USA: +1 888-444-1311
 Europe: +46 10 478 2000
 Asia: +65 6484 7877
www.schneider-electric.com

Life Is On

Schneider
Electric

Specifications (cont.)

Regulatory Information

Agency approvals	UL 916
	European conformance CE: EN 60730-1, EN 60730-2-9, EN 60730-2-13, EN 61000-6-2, EN 61000-6-3, EN 61000 Series - Industrial Immunity, EN 61326-1
	FCC Part 15 Class B, REACH, RoHS, Green Premium, RCM (Australia), ICES-003 (Canada), UKCA (UK)

1. PM4 and PM10 output values are calculated based on distribution profile of all measured particles.
2. Air Quality Index for VOC aligns with TVOC levels for IAQ as specified by the WHO (World Health Organization).
3. Humidity sensor overall accuracy should include: accuracy, temperature coefficient and stability. Humidity accuracy is shown as an absolute value, so if testing accuracy with a hand-held device, you must check for deviation in its readings instead of calculating the percentual deviation. Additionally, you must consider the overall accuracy of the hand-held device in the comparison.
4. On display models only.
5. See <http://bms-applications.schneider-electric.com/type/MB/download/419> for device import file and instructions.

Note: This product is specified for environments with stable natural airflow. In dynamic airflow conditions, sensor performance may deviate from expected values. In stable elevated airflow, an offset feature can be applied. Refer to ZL0241-xx, *Field Offset Adjustment Procedure for SLA and SLP Temperature and Humidity Outputs* on se.com for further information.


Power Table

Model	Description	Max. VA
SLPxTCPV2	Touch CO2/VOC/Temperature/Humidity/PM	2.520
SLPxCPV2	Blank CO2/VOC/Temperature/Humidity/PM	2.016


Note: Model numbers based on supported product matrix.

Dimensions mm (in.)

Optimum Housing



Medium Housing



Base Hole Measurement

