



Ref. Certif. No.

FR_721591

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Air circuit-breaker

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS
35, rue Joseph Monier, 92500 RUEIL-MALMAISON - FRANCE

Name and address of the manufacturer

SCHNEIDER ELECTRIC INDUSTRIES SAS
35, rue Joseph Monier, 92500 RUEIL-MALMAISON - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

CTF2

Model / Type Ref.

MasterPact MTZ3 type H1,H2
Circuit-breakers equipped with control units :
MicroLogic X: 2.0 X – 5.0 X – 6.0 X
MicroLogic Xi: 5.0 Xi – 6.0 Xi
MicroLogic Active: 2.0 A – 5.0 A – 6.0 A – 2.0 AP – 5.0 AP –
6.0 AP – 2.0 E – 5.0 E – 6.0 E – 2.0 EP – 5.0 EP – 6.0 EP-
6.0Ei
See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_713525/M3 dated 14/10/2024.
Addition of product references
Technical modification

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60947-1:2007 +A1:2010 +A2:2014
IEC 60947-2:2016 +A1:2019

As shown in the Test Report Ref. No. which forms part of this Certificate

25119Y90022

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/05/2025

Signature:

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
S.A.S au capital de 15,745,984 €
RCS Nanterre 348 263 170
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES
Certification Officer

IEC

IECEE

Ref. Certif. No.

FR_721591

ANNEX

Name and address of the factories:

SCHNEIDER ELECTRIC Alpes

Zone d'activités Alpespace, Rue Isaac Newton, 73800 Porte-de-Savoie - FRANCE

Schneider Electric India Pvt Ltd

SURVEY NO 215, GAGILLAPUR VILLAGE, MEDAK ROAD, RANGAREDDY DISTRICT
HYDERABAD, 500 043 (A.P.) - INDIA

SCHNEIDER SHANGHAI POWER DISTRIBUTION ELEC. APP. Co. Ltd

No.833 Kangqiao Road, Kangqiao Industrial Development Zone Pudong District, 201315 SHANGHAI - CHINA



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Date: 09/05/2025

Signature: 
Julien GAUTHIER
Certification Officer



ANNEX

References, ratings and main characteristics:

Models	Rated current (In)	Models	Rated current (In)
MTZ3-40 H1	2000 to 4000A	MTZ3-40 H2	2000 to 4000A
MTZ3-50 H1	2500 ⁽¹⁾ to 5000A	MTZ3-50 H2	2500 ⁽¹⁾ to 5000A
MTZ3-63 H1	3200 ⁽¹⁾ to 6300A	MTZ3-63 H2	3200 ⁽¹⁾ to 6300A

(1) 2000A WITH MICROLOGIC ACTIVE CONTROL UNIT

Selectivity category	B
Interruption medium	Air
Design	Moulded case
Method of controlling the operating mechanism	Stored energy operation
Suitability for isolation	Suitable
Provision for maintenance	Maintainable
Method of installation	Fixed & withdrawable
IP degree of protection	IP40 with escutcheon IP54 with transparent cover
Type of release :	Electronic MicroLogic X: 2.0 X – 5.0 X – 6.0 X MicroLogic Xi: 5.0 Xi – 6.0 Xi MicroLogic Active: 2.0 A – 5.0 A – 6.0 A – 2.0 AP - 5.0 AP - 6.0 AP – 2.0 E – 5.0 E – 6.0 E – 2.0 EP - 5.0 EP - 6.0 EP-6.0Ei
Rated operational voltage U_e : (V)	220V, 415V, 440V, 525V, 690V
Rated insulation voltage U_i : (V)	1000V
Rated impulse withstand voltage U_{imp} : (kV)	12kV
Rated current I_n : (A)	See above table
Conventional free air thermal current I_{th} : (A)	Equal to I_n
Rated current for four pole circuit-breakers : (A)	Equal to I_n
Rated frequency : (Hz)	50/60Hz
Nature of supply :	AC
Total number of poles :	3P,4P
Rated duty	uninterrupted duty
Rated ultimate short-circuit breaking capacity I_{cu} : (kA)	H1: 100kA – 220/415/440/525/690V H2: 150kA – 220/415/440V 130kA – 525V, 100kA – 690V
Rated service short-circuit breaking capacity I_{cs} : (A)	H1: 100kA – 220/415/440/525/690V H2: 150kA – 220/415/440V 130kA – 525V, 100kA – 690V
Rated short-time withstand current I_{cw} : (A)	100kA/3s
Electromagnetic compatibility	A
Circuit-breaker for use in IT systems	$I_{IT} = 50kA – 690V$
Special tests according Annex Q – IEC60947-1 : Tests for environmental categories	Category D


 LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/05/2025

 Signature: 
 Certification Officer


ANNEX

Undervoltage release (MN), shunt trip release (MX), closing release (XF)

References	Voltage - Type - Frequency	References	Voltage - Type - Frequency		
MN		MN Diag.			
LV833668 LV833668SP	24-30V DC ; 24V AC 50/60 Hz	LV836668 LV836668SP	24-30V DC ; 24V AC 50/60 Hz		
LV833669 LV833669SP	48-60V DC ; 48V AC 50/60 Hz	LV836669 LV836669SP	48-60V DC ; 48V AC 50/60 Hz		
LV833670 LV833670SP	100-130V DC ; 100-130V AC 50/60 Hz	LV836670 LV836670SP	100-130V DC ; 100-130V AC 50/60 Hz		
LV833671 LV833671SP	200-250V DC ; 200-250V AC 50/60 Hz	LV836671 LV836671SP	200-250V DC ; 200-250V AC 50/60 Hz		
LV833673 LV833673SP	380-480V AC 50/60 Hz	LV836673 LV836673SP	380-480V AC 50/60 Hz		
33668 LV933668SP	24-30V DC ; 24V AC 50/60 Hz				
33669 LV933669SP	48-60V DC ; 48V AC 50/60 Hz				
33670 LV933670SP	100-130V DC ; 100-130V AC 50/60 Hz				
33671 LV933671SP	200-250V DC ; 200-250V AC 50/60 Hz				
33673 LV933673SP	380-480V AC 50/60 Hz				
MX/XF				MX/XF Diag. and COM	
LV833659 LV833659SP	24-30V DC ; 24V AC 50/60 Hz			LV833033 LV833033SP	24-30V DC ; 24V AC 50/60 Hz
LV833660 LV833660SP	48-60V DC ; 48V AC 50/60 Hz	LV833034 LV833034SP	48-60V DC ; 48V AC 50/60 Hz		
LV833661 LV833661SP	100-130V DC ; 100-130V AC 50/60 Hz	LV833035 LV833035SP	100-130V DC ; 100-130V AC 50/60 Hz		
LV833662 LV833662SP	200-250V DC ; 200-250V AC 50/60 Hz	LV833036 LV833036SP	200-250V DC ; 200-250V AC 50/60 Hz		
LV833663 LV833663SP	277V AC 50/60 Hz	LV833037 LV833037SP	277V AC 50/60 Hz		
LV833664 LV833664SP	380-480V AC 50/60 Hz	LV833038 LV833038SP	380-480V AC 50/60 Hz		
33659 LV933659SP	24-30V DC ; 24V AC 50/60 Hz				
33660 LV933660SP	48-60V DC ; 48V AC 50/60 Hz				
33661 LV933661SP	100-130V DC ; 100-130V AC 50/60 Hz				
33662 LV933662SP	200-250V DC ; 200-250V AC 50/60 Hz				
33663 LV933663SP	277V AC 50/60 Hz				
33664 LV933664SP	380-480V AC 50/60 Hz				



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/05/2025

Signature:



LABORATOIRE CENTRAL DES
 INDUSTRIES ELECTRIQUES
 S.A.S au capital de 15.745.984 €
 RCS Nanterre B 408 363 174
 33 avenue du Général Leclerc
 F - 92260 FONTENAY AUX ROSES

Julien GAUTHIER
 Certification Officer

ANNEX

Electric motor (MCH)

References	Voltage - Type - Frequency	
47889 LV847889SP	48 V	AC 50/60 Hz
47893 LV847893SP	100-130 V	
47894 LV847894SP	200-240 V	
47895 LV847895SP	250-277 V	
47896 LV847896SP	380-415 V	
47897 LV847897SP	440-480 V	
47888 LV847888SP	24-30 V	
47889 LV847889SP	48-60 V	
47890 LV847890SP	100-125 V	
47891 LV847891SP	200-250 V	

Others:

Embedded Ethernet InterFace (EIFE): LV851001, LV851001SP, LV851200SP
 ULP interface module: LV836385, LV850061SP, LV836387, LV850062SP
 M2C - Programmable contacts: LV847086, LV847086SP
 ESM - ERMS Switch Module: LV836300, LV836300SP
 Electrical reset (RES): 47901, LV848202SP, 47902, LV848203SP



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/05/2025

Signature: 

 Certification Officer