



Main

For connecting 8 conventional devices with AC/DC 24 V outputs to KNX.

Complementary

With integrated bus coupler and plug-in screw terminals. For installation on DIN rails EN 50022. The bus is connected using a bus connecting terminal; a data rail is not necessary.

The input voltage level is displayed at each input with a yellow LED. A green LED indicates that the device is ready for operation once the application has been loaded.

KNX software functions:

Switching, dimming or blind control via 1 or 2 inputs. Positioning values for blind control (8-bit). Pulse edges with 1-, 2-, 4-, or 8-bit telegrams. Differentiation between short/long operation. Initialisation telegram. Cyclical sending. Pulse edges with 2-byte telegrams. 8-bit linear regulator. Disable function. Break/make contact. Debounce time.

Input voltage: AC/DC 24V

Inputs: 8

Input current: DC approx. 15 mA/AC approx. 6 mA

Line length: max. 100 m

Device width: 4 modules = approx. 72 mm

Contents: With bus connecting terminal and cable cover.

Colour: light grey

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.