

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

## Product

Switch-disconnector (Changeover switch)

## Name and address of the applicant

Schneider Electric India Private Limited  
Switchgear Design and Development centre, Prima Bay, TC-2, Tower B, 4th Floor, Gate 5, Saki Vihar Road, Powai, 400072 Mumbai, Maharashtra, India

## Name and address of the manufacturer

Schneider Electric India Private Limited  
ESP Ahmednagar Mfg. Plant, A9, MIDC, 414111 Ahmednagar, Maharashtra, India

## Name and address of the factory

Schneider Electric India Private Limited  
ESP Ahmednagar Mfg. Plant, A9, MIDC, 414111 Ahmednagar, Maharashtra, India*Note: When more than one factory, please report on page 2* [Additional information on page 2](#)

## Ratings and principal characteristics

1P, 2P, 3P, 4P  
Ue: 230/240 Vac for 1P, 400/415 Vac for 2P, 3P, 4P  
Ui: 690 Vac; Uimp: 6 kV; 50/60 Hz  
Ie:63 A; AC-22A  
Icw: 20 Ie - 1 s; Icm: 20 Ie (peak)  
See annex for further ratings

## Trademark / Brand (if any)

Schneider Electric

## Customer's Testing Facility (CTF) Stage used

CTF Stage 2

## Model / Type Ref.

Acti9

## Additional information (if necessary may also be reported on page 2)

 [Additional information on page 2](#)

## A sample of the product was tested and found to be in conformity with

IEC 60947-3:2020

## National differences:

AU, NZ

## As shown in the Test Report Ref. No. which forms part of this Certificate

3325083.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.  
Meander 1051  
Arnhem, 6825 MJ  
Netherlands

Date: 2023-03-13

Signature: F.S.Strikwerda

**Rating**

product	: Switch-disconnector (Changeover switch)
trade name(s)	: Schneider Electric
type(s)	: Acti9
number of poles	: 1P, 2P, 3P, 4P
kind of current	: AC
rated operational voltage (Ue)	: 230/240 Vac for 1P, 400/415 Vac for 2P, 3P, 4P
rated insulation voltage (Ui)	: 690 V
rated impulse withstand voltage (Uimp)	: 6 kV
rated frequency	: 50/60 Hz
rated operational currents (Ie)	: 63 A
conventional free air thermal current (Ith)	: Equal to Ie
rated uninterrupted current (Iu)	: Equal to Ie
rated short-time withstand current (Icw)	: 1260 A - 1 s
rated short-time making capacity (Icm)	: 1260 A (peak)
suitable for isolation	: Suitable
utilization category	: AC-22A
degree of protection	: IP20 (only front side)
ambient air temperature	: - 5 °C to 40 °C
method of mounting	: Fixed
EMC Environment	: A and B
tightening torque for terminals	: 4 Nm / M5
line/load terminal connection	: Not marked (double break contact system) : Copper conductor with unprepared cable: 6 mm <sup>2</sup> to 16 mm <sup>2</sup>