

National Measurement Institute

Certificate of Approval NMI 14/2/88

Issued by the Chief Metrologist under Regulation 60 of the
National Measurement Regulations 1999

This is to certify that an approval for use for trade has been granted in respect of the instruments herein described.

Schneider Electric Model iEM3255 Class 0.5 Electricity Meter

submitted by Schneider Electric (Australia) Pty Ltd

78 Waterloo Road

Macquarie Park NSW 2113

NOTE: This Certificate relates to the suitability of the pattern of the instrument for use for trade only in respect of its metrological characteristics. This Certificate does not constitute or imply any guarantee of compliance by the manufacturer or any other person with any requirements regarding safety.

This approval has been granted with reference to document NMI M 6-1 *Electricity Meters. Part 1: Metrological and Technical Requirements*, July 2012.

DOCUMENT HISTORY

Rev	Reason/Details	Date
0	Pattern & variant 1 approved – interim certificate issued	29/07/15
1	Pattern & variant 1 approved – certificate issued	21/01/16
2	Pattern & variant 1 approved – amended Test procedure reference to MPEs	10/02/17
3	Pattern amended – certificate issued	28/07/20
4	Variant 2 approved – certificate issued	18/08/20

CONDITIONS OF APPROVAL

General

Instruments purporting to comply with this approval shall be marked with pattern approval number 'NMI 14/2/88' and only by persons authorised by the submittor.

It is the submittor's responsibility to ensure that all instruments marked with this approval number are constructed as described in the documentation lodged with the National Measurement Institute (NMI) and with the relevant Certificate of Approval and Technical Schedule. Failure to comply with this Condition may attract penalties under Section 19B of the National Measurement Act and may result in cancellation or withdrawal of the approval, in accordance with document NMI P 106.

Auxiliary devices used with this instrument shall comply with the requirements of

General Supplementary Certificate No S1/0B.

Signed by a person authorised by the Chief Metrologist to exercise their powers under Regulation 60 of the *National Measurement Regulations 1999*.

Darryl Hines Manager

Policy and Regulatory Services

TECHNICAL SCHEDULE No 14/2/88

1. Description of Pattern

approved on 29/07/15

amended on 28/07/20

A Schneider Electric model iEM3255 class 0.5 electronic current transformer (CT) operated static watt hour meter (Figure 1) used to measure electrical energy.

1.1 Field of Operation

The field of operation of the measuring system is determined by the following characteristics:

Number of phases
Number of wires
Reference frequency
3 or 4
50 Hz

• Reference ambient temperature ranges:

specified range of operation -25 to 55°C limit range of operation -25 to 60°C

Reference voltage 3x100/173 277/480 V AC

Rated currents: Rated current, I_n 5 A
 Maximum current, I_{max} 6 A

Meter constant 5000 imp/kWh

Accuracy class
 0.5

1.2 Features/Functions

- Electronic (LCD) digital indicator
- Internal crystal clock
- One (1) × three-phase or three (3) × single phase configuration
- Measurement in positive and negative direction

1.3 Descriptive Markings

Instruments are marked with the following data, together in one location, in the form shown at right:

Manufacturer's name or mark ...

Model designation ...

Serial number ...

Pattern approval mark NMI 14/2/88

Class 0.5

Accuracy index Class 0.5

1.4 Verification Provision

Provision is made for the application of a verification mark.

1.5 Sealing Provision

Provision is made for the instrument to be sealed by the application of one or more destructible adhesive labels (Figure 2).

2. Description of Variant 1

approved on 29/07/15

Certain other models of the iEM3200 series as listed below:

- iEM3200 basic energy meter
- iEM3210 energy meter with pulse output
- iEM3215 multi-tariff energy meter
- iEM3250 energy meter & electrical parameter plus RS485 comm port
- iEM3255 (the pattern) advanced multi-tariff energy meter & electrical parameter plus RS485 comm port.
- iEM3265 advanced multi-tariff energy meter & electrical parameter plus BACnet MS/TP comm port
- iEM3275 advanced multi-tariff energy meter & electrical parameter plus LON TP/FT-10 comm port

All of the models have the same field of operation. The differences relate to features and functions.

3. Description of Variant 2

approved on 18/08/20

The pattern, or any of the models listed under variant 1, configured for use as three single-phase meters.

TEST PROCEDURE

Instruments tested for initial verification shall comply with the certificate of approval and technical schedule, and the maximum permissible errors for verifications at the operating conditions in effect at the time of verification.

The maximum permissible errors are specified in the *National Trade Measurement Regulations 2009* (Cth).

Meters shall be verified in accordance with NITP 14 National Instrument Test Procedures for Utility Meters.

Evidence of verification shall be confirmed via the meter serial number and certificate of verification issued by a utility meter verifier in accordance with NITP 14.

NOTE: NMI reserves the right to vary this procedure. Any such variation shall be notified in writing by NMI.

FIGURE 14/2/88 - 1



Schneider Electric Model iEM3255 Electricity Meter





Showing Typical Mechanical Sealing