


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**LC1D115M7**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Rating: 600V / 115A  
 UL File/CCN: E164862 / NLDX  
 CSA File: LR43364 3211 04  
 Meets Standards: IEC 60647-4  
 Weight: 2.5 lb (1.13 kg)  
 Termination Method: Screw Clamp  
 Wire Size: Power: #8 AWG - 250MCM  
 Control: #14 - #18 AWG  
 Terminal torque: Power: 100 lb-in (12 Nm)  
 Control: 10 lb-in (1.2 Nm)  
 Mounting Hwd.: 2 x 35mm DIN Rail, M6 screw

**Specification:**

Description: TeSys D IEC Contactor - 115A - Vac Coil  
 Type: TeSys D IEC Contactor - 115A - 220Vac Coil  
 Voltages Code: M7 at 220Vac 50/60 Hz

Coil Consumption: Inrush 280 - 350 VA  
 Sealed 2 - 18 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
N/A	N/A	30 HP	40 HP	75 HP	100 HP