




Note:  
- Drawings Not To Scale  
- Drawings Subject to Change Without Notice  
- Dimensions are inches next to [Millimeters]

Part No.:  
**LC1D12J7**

**Schneider Electric**  
Schneider Electric United States  
North American Division  
Boston One Campus  
800 Federal Street  
Andover, MA 01810, USA  
Phone: +1 8773425173  
Email: CCC@us.schneider-electric.com

Rating: 600V / 12A  
UL File/CCN: E164862 / NLDX  
CSA File: LR43364 3211 04  
Meets Standards: IEC 60647-4  
Weight: 0.72 lb (0.325 kg)  
Termination Method: Screw Clamp  
Wire Size: Power: #10 - #18 AWG  
Control: #10 - #18 AWG  
Terminal torque: Power: 15 lb-in (1.7 Nm)  
Control: 15 lb-in (1.7 Nm)  
Mounting Hwd.: 35mm DIN Rail, #8 screw

Technical Information:

Description: TeSys D IEC Contactor - 12A - Vac Coil  
Type: TeSys D IEC Contactor - 12A - 12Vac Coil  
Voltages Code: J7 at IEC Contactor - 12A - 12Vac Coil

Coil Consumption: Inrush 70 VA  
Sealed 7.5 VA

| Single Phase |      |      | Three Phase |        |       |
|--------------|------|------|-------------|--------|-------|
| 115V         | 230V | 200V | 230V        | 460V   | 575V  |
| 1 HP         | 2 HP | 3 HP | 3 HP        | 7.5 HP | 10 HP |