Ultrasonic Sensor M30 - Straight or 90° angled version

Plastic XX•30P2•M12

Ni-plated Brass: XXe30B2eM12 Stainless steel · XX•30S2•M12





▲ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not use this product to detect objects within the deadband (blind zone) or outside the sensing window.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

http://qr.tesensors.com/XX0003

Dimensions XXA30P2•M12 XXA30B2•M12






LEDs




Connectors wiring


XXA30S2eM12





Pin Number	Wire Color	Description
1	BN: Brown	+1224 Vdc
2	WH: White	Input teach
3	BU: Blue	0 Vdc
4	BK: Black	Output
(5)	GY: Grey	Synchronization




Note: (1): See synchronization section








Wiring diagrams






4–20 mA:
- For 12 Vdc, Load ≤ 250 Ω
- For 24 Vdc, Load ≤ 850 Ω

Sensor type	4-20 mA	0-10 V
Rated supply voltage	1224 Vdc Min = 10 Vdc Max = 30 Vdc	24 Vdc Min = 14 Vdc Max = 30 Vdc
	with reverse polarity protection	

Synchronization (side by side application)




Synchronization operation

Up to 8 sensors can be synchronized to operate side by side by electrically connecting all pin no.5 (grey) wires together. To synchronize more than 8 sensors a PLC output can be used (the pins no.5 must be simultaneously driven by the rising edge of a pulse).

NOTE (1): The pulse must be at a high level of 12 to 24 Vdc and a low level of 0 to 2Vdc. All sensors should be the same model and have the same cycle time setting. The high pulse width should be 1 ms, and the low should be at be at least as long as the sensor cycle time setting (default cycle times: 2m sn= 30 ms).

NOTE (2): When the pin no.5 is at low level or at high level, object sensing is suspended and the sensor output holds the last valid output state before suspension.


Multiplexing (face to face application)



This function can be used to avoid disturbances when operating sensors face to face. A unique address must be assigned to each sensor (or group of sensors) with the use of the XX Configuration Software (prior to wiring the sensors), and all pin no.5 (grey) wires must be connected together. For sequencing with a PLC, please contact your local Telemecanique Sensors Technical Support Group.


Electrical equipment should be installed, operated, serviced, and maintained only by qualified personnel. No responsibility is assumed by Schneider Electric for any consequences arising out of the use of this material.

© 2019 Schneider Electric. "All Rights Reserved."




Detection curves for different objects

Detection curve with 100 x 100 mm square target




Detection curve with round bar



Wiring accessory






M12 connectors








Mounting accessory



Recommended to use for sensor applications at operating temperatures -25 \dots 0 °C (-13...32 °F)







Scan the Qr-code to access this Instruction Sheet in different languages.



Note:
You can download this Instruction Sheet in different languages from our website at: www.tesensors.com
We welcome your comments about this document. You can reach us by e-mail at: customer-support@tesensors.com

http://qr.tesensors.com/XX0003