


SECTION 1: IDENTIFICATION

Product identifier:

Product name:	LI-ION BATTERY – CP12010LI, CP12044LI Network UPS
Other names:	UPS PowerBank Containing Lithium Ion Batteries, Lithium Ion Battery pack less than 100 WH
Model Numbers:	CP12010LI, CP12044LI
Country:	USA/Canada/Worldwide Distribution
Product type:	Solid
Picture: CP12010LI, CP12044LI	

Identified uses

Lithium-Ion battery pack, less than 100 WH

Manufacturer

Supplier/Manufacturer:	Schneider Electric IT USA (formerly APC by Schneider Electric, APC Sales and Service Corp.)
Address:	132 Fairgrounds Road West Kingston, RI 02892, USA / SEIT- CA, c/o 210080, PO Box 11728, SUCC. Centre-Ville, Montreal, QC, H3C 6P7132
Telephone:	+1 800-788-2208 or +1 401-789-5735
E-mail:	http://nam-en.apc.com/app/ask
Website:	www.APC.com
Telecopy:	Not available.

Emergency telephone number (with hours of operation)

For all Service, Technical Support and Emergency Inquires.
800-255-3924 USA and 1-813-248-0585 International

SECTION 2: HAZARDS IDENTIFICATION

OSHA/HCS status:

OSHA Hazard Communication: This material is not considered hazardous by the OSHA Hazard Communication Standard 29CFR 1910.1200.

Carcinogenicity (NTP): Not listed

Carcinogenicity (IARC): Not listed

Carcinogenicity (OSHA): Not listed

Classification of the substance or mixture:

Not classified.

GHS label elements:

Signal word: No signal word.

Hazard statements: No known significant effects or critical hazards.

Precautionary statements

Prevention:	Not applicable
Response	Not applicable
Storage	Not applicable
Disposal	Not applicable

Hazards not otherwise classified (HNOC)

Physical hazards not otherwise classified (PHNOC): None known.

Health hazards not otherwise classified (HHNOC): In case of cell damage, possible release of dangerous substances and a flammable gas mixture

SECTION 3: COMPOSITION / INFORMATION ON INGREDIENTS

Substance/Mixture: Mixture.

Other means of identification: Not available.

CAS number/other identifiers

Product/ingredient name	Identifiers	%	Classification OSHA HCS 2015
Lithium Cobalt Oxide(LiCoO ₂)	CAS: 12190-79-3 EINECS: 235-362-0	50	Eye, Skin, Respiratory Irritant
Carbon, as Graphite	CAS: 7440-44-0 EINECS : 231-955-3	10	Eye, Skin, Respiratory Irritant
Dimethyl Carbonate	CAS: 16-38-6 EINECS : 210-478-4	5	Flammable

Ethylene Carbonate	CAS: 96-49-1 EINECS: 202-510-0	5	Risk of serious damage to eyes, Skin & Respiratory Irritant
Lithium hexafluorophosphate (LiPF ₆)	CAS: 21342-40-3 EINECS: 244-334-7	5	Harmful if swallowed, Toxic in contact with skin, Causes severe skin burns and eye damage
CARBOXYMETHYLCELLULOSE SODIUM (CMC)	CAS: 21342-40-3	0.5	Inert
Mixed Plastics (PP, PVDF, PE)	CAS : 9003-07-0, CAS : 24937-79-9, CAS : 9002-88-4	12	Inert
Aluminum Metal	CAS: 7429-90-5 EINECS : 231-072-3	5	Inert
Copper Metal	CAS: 7440-50-8 EINECS : 231-159-6	5	Inert
Nickel Metal	CAS: 7440-50-8 EINECS : 231-111-4	2.5	Inert

Further Information

Directive 2006/66/EC of the European Parliament and of the Council of 6 September 2006 on batteries and accumulators and waste batteries and accumulators (Battery Directive)

Mercury content: Hg < 0.1mg/kg

Cadmium content: Cd < 1mg/kg

Lead content: Pb < 10mg/kg

SECTION 4: FIRST AID MEASURES

General information

The following first aid measures are required only in case of exposure to interior battery components after damage of the external battery casing. Undamaged, closed cells do not represent a danger to the health.

Description of necessary first aid measures

Eye contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Seek medical treatment by eye specialist.
Inhalation	Ensure of fresh air. Consult a physician.
Skin contact	In case of contact with skin wash off immediately with plenty of water. Consult a physician.

Ingestion	Drink plenty of water. Call a physician immediately.
------------------	---

Most important symptoms/effects, acute and delayed

Potential acute health effects

Eye contact	No particular hazards for proper use. It will cause severe irritation or chemical burn when batteries are broken.
Inhalation	No particular hazards for proper use. It will cause skin severe irritation by inhalation of EC and Routes of Entry: DMC or chemical burn when batteries are broken.
Skin contact	It will irritate breath system by being exposed to fumes when batteries are broken.
Ingestion	It is deleterious by swallowing battery. Broken batteries will cause severe chemical burn to mouth, esophagus and gastro enteric system

Indication of immediate medical attention and special treatment needed, if necessary

Notes to physician	none
Specific treatments	No specific treatment
Protection of first-aiders	No action shall be taken involving any personal risk or without suitable training

See toxicological information (Section 11)

SECTION 5: FIRE-FIGHTING MEASURES

Extinguishing media

Suitable extinguishing media	Cold water and dry powder in large amount are applicable. Use metal fire extinction powder or dry sand if only few cells are involved.
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	May form hydrofluoric acid if electrolyte comes into contact with water.
Hazards thermal decomposition products	In case of fire, the formation of the following flue gases cannot be excluded: Hydrogen fluoride (HF), Carbon monoxide and carbon dioxide.
Special protective actions for fire-fighters	If possible, remove cell(s) from firefighting area. If heated above 125°C, cell(s) can explode/vent. Cell is not flammable but internal organic material will burn if the cell is incinerated.
Special protective equipment for fire-fighters	Wear self-contained breathing apparatus and protective suit.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

For non-emergency personnel	Use personal protective clothing. Avoid contact with skin, eyes and clothing. Avoid breathing fume and gas.
For emergency responders	Take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For nonemergency personnel".
Environmental precautions	Do not discharge into the drains/surface waters/groundwater.

Methods and materials for containment and cleaning up

Take up mechanically and send for disposal.

Note: See Section 1 for emergency contact information and Section 13 for waste disposal.

SECTION 7: HANDLING AND STORAGE

Precautions for safe handling

Protective measures	Put on appropriate personal protective equipment (see Section 8).
Advice on safe handling	Avoid short circuiting the cell. Avoid mechanical damage of the cell. Do not open or disassemble. Advice on protection against fire and explosion Keep away from open flames, hot surfaces and sources of ignition.
Conditions for safe storage, including any incompatibilities	Storage at room temperature at approx. 20°C, 60% of the nominal capacity (OCV approx. 3.6 - 3.9 V). Keep in closed original container.

SECTION 8: EXPOSURE CONTROLS / PERSONAL PROTECTION

Control parameters

United States Occupational exposure limits

None

Canada

None

Appropriate engineering controls	No specific precautions necessary.
Environmental exposure controls	No specific precautions necessary.

Individual protection measures

Hygiene measures	When using do not eat, drink or smoke. Wash hands before breaks and after work.
Eye/face protection	No specific precautions necessary.
Hand protection	No specific precautions necessary.
Body protection	No specific precautions necessary.
Other skin protection	No specific precautions necessary.
Respiratory protection	No specific precautions necessary.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Appearance

Physical state	Solid.
Color	Various.
Odor	Odorless.
Odor threshold	Not applicable.
pH	Not applicable.
Melting point	Not applicable.
Boiling point	Not applicable.
Flash point	Not applicable.
Evaporation rate	Not applicable.
Flammability (solid, gas)	Not applicable.
Lower and upper explosive (flammable) limits	Not applicable.
Vapor pressure	Not applicable.
Vapor density	Not applicable.
Relative density	Not applicable.
Solubility in water	Insoluble.
Partition coefficient: n-octanol/water	Not applicable.
Auto-ignition temperature	Not applicable.
Decomposition temperature	Not applicable.
Viscosity	Not applicable.

SECTION 10: STABILITY AND REACTIVITY

Reactivity	No specific test data related to reactivity available for this product or its ingredients.
Chemical stability	The product is stable.

Possibility of hazardous reactions	Hazardous reactions will not occur.
Conditions to avoid	Keep away from open flames, hot surfaces and sources of ignition. Do not puncture, crush or incinerate.
Incompatible materials	No materials to be especially mentioned.
Hazardous decomposition products	In case of open cells, there is the possibility of hydrofluoric acid and carbon monoxide release.
Additional information	No decomposition if stored and applied as directed.

SECTION 11: TOXICOLOGICAL INFORMATION

Information on toxicological effects

Acute toxicity	There is no data available.
Irritation/Corrosion	There is no data available.
Sensitization	There is no data available.
Mutagenicity	There is no data available.
Carcinogenicity	There is no data available.
Reproductive toxicity	There is no data available.
Teratogenicity	There is no data available.
Specific target organ toxicity (single exposure)	There is no data available.
Specific target organ toxicity (repeated exposure)	There is no data available.
Aspiration hazard	There is no data available.

Information on the likely routes of exposure: Dermal contact, Eye contact, Inhalation, Ingestion.

Potential acute health effects

Eye contact	No known significant effects or critical hazards.
Inhalation	No known significant effects or critical hazards.
Skin contact	No known significant effects or critical hazards.
Ingestion	No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

Eye contact	No known significant effects or critical hazards.
Inhalation	No known significant effects or critical hazards.
Skin contact	No known significant effects or critical hazards.
Ingestion	No known significant effects or critical hazards.

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

Potential immediate effects	No known significant effects or critical hazards.
Potential delayed effects	No known significant effects or critical hazards.

Long term exposure

Potential immediate effects	No known significant effects or critical hazards.
Potential delayed effects	No known significant effects or critical hazards.

Potential chronic health effects

General	No known significant effects or critical hazards.
Carcinogenicity	No known significant effects or critical hazards.
Mutagenicity	No known significant effects or critical hazards.
Teratogenicity	No known significant effects or critical hazards.
Developmental effects	No known significant effects or critical hazards.
Fertility effects	No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates: There is no data available.

SECTION 12: ECOLOGICAL INFORMATION

Toxicity	There is no data available.
Persistence and degradability	There is no data available.
Bioaccumulative potential	There is no data available.

Mobility in soil

Soil/water partition coefficient (K_{oc})	No data available.
Other adverse effects	No known significant effects or critical hazards.

Further information

Ecological injuries are not known or expected under normal use. Do not flush into surface water or sanitary sewer system.

SECTION 13: DISPOSAL CONSIDERATIONS

Advice on disposal






For recycling consult manufacturer.

Contaminated packaging

Disposal in accordance with local regulations.

SECTION 14: TRANSPORT INFORMATION

Under IATA Dangerous Goods Regulations 60th Edition effective 1st January 2019 until 31st December 2019 accordance to IATA-Resolution 618 Annex "A" and in consultation with ICAO, Schneider Electric certifies that the referenced products are classified as follows:

	DOT	TDG	IMDG	IATA
UN number	UN3480	UN3480	UN3480	UN3480
UN proper shipping name	LITHIUM ION BATTERIES	LITHIUM ION BATTERIES	LITHIUM ION BATTERIES	LITHIUM ION BATTERIES
Hazard Class	Class 9	Class 9	Class 9	Class 9
Packing Instruction & Label	PI965 - Section II 	PI965 - Section II 	PI965 - Section II 	PI965 - Section II   "Lithium ion batteries in compliance with Section II of PI965" and "CAO"
Additional information	<ul style="list-style-type: none"> Each lithium ion battery pack has a rating less than 100 WH CP12010LI-XX Lithium Battery Weight = 43.5 g, Lithium Battery Rating = 9.63 WH CP12044LI Lithium Battery Weight = 380 g, Lithium Battery Rating = 47.2 WH 			

AERG : 147

Note: Original packaging is strong rigid outer packaging equivalent to its capacity and intended use. UN38.3.5 Test Report Summary on the 914-0001, ZE18017 pack is available upon request.

Special precautions for user	Not available.
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not available.

SECTION 15: REGULATORY INFORMATION

U.S. Federal regulations	TSCA 8(a) CDR Exempt/Partial exemption: All chemical component are listed or exempt from listing United States inventory (TSCA 8b): All components are listed or exempted.
---------------------------------	---

LI-ION BATTERY CP12010LI, CP12044LI Network UPS

Version: 1.1

Date: August 3, 2020

Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs)	Not available.
Clean Air Act Section 602 Class I Substances	Not available.
Clean Air Act Section 602 Class II Substances	Not available.
DEA List I Chemicals (Precursor Chemicals)	Not available.
DEA List II Chemicals (Precursor Chemicals)	Not available.

SARA 302/304

Composition/information on ingredients
Not available.

SARA 304 RQ: Not available.

SARA 311/312

Classification: Not applicable.
Composition/information on ingredients. No products were found.

SARA 311/312

Not applicable

SARA 313

This product contains no toxic chemicals subject to the supplier notification requirements of Section 313.

State regulations

Massachusetts	Not known
New York	Not known
New Jersey	Not known
Pennsylvania	Not known
California	Proposition 65 - No known Proposition 65 substances requiring warning

Canada - Canadian lists

Canadian NPRI	Not known
CEPA Toxic substances	Not known
Canada inventory	Not known.

SECTION 16: OTHER INFORMATION

LI-ION BATTERY CP12010LI, CP12044LI Network UPS

Original release date: August 2, 2018

Review date: August 3, 2020

Version: 1.1

Further Information USA

Data of sections 4 to 8, as well as 10 to 12, do not necessarily refer to the use and the regular handling of the product (in this sense consult package leaflet and expert information), but to release of major amounts in case of accidents and irregularities. The information describes exclusively the safety requirements for the product (s) and is based on the present level of our knowledge. This data does not constitute a guarantee for the characteristics of the product(s) as defined by the legal warranty regulations.

The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.

Notice to reader:

Schneider Electric has prepared this Product Safety Datasheets to provide information on the referenced battery systems. Batteries are defined as articles under the GHS and exempt from GHS classification criteria (Section 1.3.2.1.1 of the GHS). To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

LI-ION BATTERY CP12010LI, CP12044LI Network UPS

Version: 1.1

Date: August 3, 2020

Page 11 to 11