


CATALOG NUMBER	A		B		C	
	IN	MM	IN	MM	IN	MM
NC26SHR	26.12	663	17.70	436	5.19	132
NC32SHR	32.12	816	23.70	602	8.19	208
NC38SHR	38.12	968	29.70	754	11.19	284
NC44SHR	44.12	1121	35.70	907	14.19	360
NC50SHR	50.12	1273	41.70	1059	17.19	437
NC56SHR	56.12	1425	47.70	1212	20.19	513
NC62SHR	62.12	1578	53.70	1364	23.19	589
NC68SHR	68.12	1730	59.70	1516	26.19	665
NC74SHR	74.12	1883	65.70	1669	29.19	741
NC80SHR	80.12	2035	71.70	1821	31.19	792
NC26FHR	27.52	699	17.70	436	5.19	132
NC32FHR	33.52	851	23.70	602	8.19	208
NC38FHR	39.52	1004	29.70	754	11.19	284
NC44FHR	45.52	1156	35.70	907	14.19	360
NC50FHR	51.52	1309	41.70	1059	17.19	437
NC56FHR	57.52	1461	47.70	1212	20.19	513
NC62FHR	63.52	1613	53.70	1364	23.19	589
NC68FHR	69.52	1766	59.70	1516	26.19	665
NC74FHR	75.52	1918	65.70	1669	29.19	741
NC80FHR	81.52	2071	71.70	1821	31.19	792
NC86SHR	86.12	2187	77.70	1974	34.19	868
NC86FHR	87.52	2071	77.70	1974	34.19	868
NC43GEINTEL	43.62	1108	29.70	754	11.19	284
NC55GEINTEL	55.62	1413	41.70	1059	17.19	437



DUAL DIMENSIONS: INCHES
MILLIMETERS

PANELBOARD COVER
TRIM TYPE 1
SURFACE/FLUSH



DWG# PWFDS-SYTI-0165
NO.