


Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

LRD076



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Termination Method: Ring-Tongue
 UL File/CCN: E164353 / NKCR
 CSA File: LR43364 3211 03
 Meets Standard: IEC 60947-1
 CE: Yes
 RoHS: Yes
 Weight: 0.12 lb (0.27 kg)
 Power Wire Size : Lug Size 0.32 in (8mm)
 Control Wire Size: Lug Size 0.32 in (8mm)
 Power Terminal Torque: 15 lb-in (1.7 Nm)
 Control Terminal Torque: 15 lb-in (1.7 Nm)
 Mtg. Directly to Contactor: Yes
 Mtg. Separate from Contactor: LAD7B10

Specification:

Description: TeSys D IEC Overload Relays, Amb. Comp. Bimetallic Class 10 w Single Phase Sensitivity
 Type: TeSys D IEC Bi-Metallic Overload Relay 600V 2.5A
 Ambient Comp. Bimetallic: Yes
 Solid State: No
 Class 10: Yes
 Class 20: No
 Single Phase Sensitivity: Yes
 For Use with Contactors: LC1D09 thru LC1D32
 Current Setting Range: 1.6A to 2.5A