



Certificate of Compliance

Certificate: 2491248

Master Contract: 254977

Project: 70111653

Date Issued: February 6, 2017

Issued to: Telemecanique/Schneider Electric Industries SAS
BP 660, Zone Industrielle No. 3
L'Isle d'Espagnac, 16340
FRANCE
Attention: Jean-Pierre Laidet

The products listed below are eligible to bear the CSA Mark shown



Issued by: *Lizon Deschamps*
Lizon Deschamps

PRODUCTS

CLASS 3211 07 - INDUSTRIAL CONTROL EQUIPMENT - Miscellaneous Apparatus

- Relay sockets, open type, models and ratings as following:

Model RSZ E1S35M, contact rated 300 V ac, 12 A, -40 °C ~ 65 °C surrounding air ambient.

Model RSZ E1S48M, contact rated 300 V ac, 10 A, -40 °C ~ 65 °C surrounding air ambient.

Models RSLZVA1 and RSLZRA1, contact rated 300 V ac, 8 A, control circuit rated 12-24 V dc/ac input, 12-24 V dc output, 55 °C surrounding air ambient.

Models RSLZVA2, RSLZRA2, SSLZVA2 and SSLZRA2, contact rated 300 V ac, 8 A, control circuit rated 48-60 V dc/ac input, 48-60 V dc output, 55 °C surrounding air ambient.

Models RSLZVA3 and RSLZRA3, contact rated 300 V ac, 8 A, control circuit rated 110 V dc/ac input, 60 V dc output, 55 °C surrounding air ambient.

Models RSLZVA4 and RSLZRA4, contact rated 300 V ac, 8 A, control circuit rated 230 V dc/ac input, 60 V dc output, 55 °C surrounding air ambient.



Certificate: 2491248
Project: 70111653

Master Contract: 254977
Date Issued: February 6, 2017

Models SSLZVA1 and SSLZRA1, contact rated 300 V ac, 8A, control circuit rated 5-24 V dc/ac input, 5-24 V dc output, 55°C surrounding air ambient.

Models SSLZVA3 and SSLZRA3, contact rated 300 V ac, 8A, control circuit rated 110 V dc/ac input, 60V dc output, 55°C surrounding air ambient.

Models SSLZVA4 and SSLZRA4, contact rated 300 V ac, 8A, control circuit rated 230 V dc/ac input, 60V dc output, 55°C surrounding air ambient.

Notes:

1. These relay sockets are certified, as components, for use in other certified equipment where the suitability of the combination is to be determined by CSA International.
2. These relay sockets are intended for factory wiring only.

- Relay sockets, DIN-Rail mounted, open type, models and ratings as following:

<u>Model</u>	<u>Ratings</u>	<u>Wire Size</u>	<u>Contacts and Terminals</u>
RXZE2S114S	12 A, 300 V	16 to 20 AWG	8 pins and 8 spring-force connector, for DPDT relay
RXZE2S114S	6 A, 300 V	16 to 20 AWG	14 pins and 14 spring-force connector, for 2DPDT relay

Notes:

1. Open type devices are certified as components for use only in other certified equipment where the suitability of the combination is to be determined by the CSA International.
2. These devices have not been investigated for interrupting current.
3. The wiring terminals are suitable for copper conductors only.

- Relay, open type, models and ratings as follows:

RXG15B7, RXG15E7, RXG15F7, RXG15M7, RXG15P7, RXG15RD, RXG15JD, RXG15BD, RXG15ED, RXG15ND, RXG15FD, and RXG11B7, RXG11E7, RXG11F7, RXG11M7, RXG11P7, RXG11RD, RXG11JD, RXG11BD, RXG11ED, RXG11KD, RXG11ND, RXG11FD, RXG12B7, RXG12E7, RXG12F7, RXG12KD, RXG12M7, RXG12P7, RXG12RD, RXG12JD, RXG12BD, RXG12ED, RXG12ND, RXG12FD, RXG13B7, RXG13E7, RXG13F7, RXG13M7, RXG13P7, RXG13RD, RXG13JD, RXG13BD, RXG13ED, RXG13ND, RXG13FD, RXG21KD, RXG22KD, contact rated 10 A or 16 A, 250 V ac, general purpose, SPST, NO contact, or SPDT, NO/NC contact; 10 A, 30 V dc, resistive, SPST, NO contact, or SPDT, NO/NC contact; 1/3 HP, 240 Vac. Coil rated 3 to 110 V dc or 6 to 240 V ac.

RXG25B7, RXG25E7, RXG25F7, RXG25M7, RXG25P7, XG25RD, RXG25JD, RXG25BD, RXG25ED, RXG25ND, RXG25FD and RXG21B7, RXG21E7, RXG21F7, RXG21M7, RXG21P7, RXG21RD, RXG21JD, RXG21BD, RXG21ED, RXG21ND, RXG21FD, RXG22B7, RXG22E7, RXG22F7, RXG22M7, RXG22P7, RXG22RD, RXG22JD, RXG22BD, RXG22ED, RXG22ND, RXG22FD, RXG23B7, RXG23E7, RXG23F7, RXG23M7, RXG23P7, RXG23RD, RXG23JD, RXG23BD, RXG23ED, RXG23ND, RXG23FD, contact rated 5 A or 8 A, 250 V ac, general purpose, DPST, NO contact, or DPDT, NO/NC contact; 5 A or 8 A, 30 V dc,



Certificate: 2491248
Project: 70111653

Master Contract: 254977
Date Issued: February 6, 2017

resistive, DPST, NO contact, or DPDT, NO/NC contact; 1/6 HP, 240 Vac. Coil rated 3 to 110 V dc or 6 to 240 V ac.

- Accessory Relay Socket, open type, models and ratings as follows:

RGZ E1S35M, contact rated 16 A, 300 V ac, maximum coil voltage 300 V ac, for use with above RXG15B7, RXG15E7, RXG15F7, RXG15M7, RXG15P7, RXG15RD, RXG15JD, RXG15BD, RXG15ED, RXG15ND, RXG15FD, or RXG11B7, RXG11E7, RXG11F7, RXG11M7, RXG11P7, RXG11RD, RXG11JD, RXG11BD, RXG11ED, RXG11ND, RXG11FD, RXG12B7, RXG12E7, RXG12F7, RXG12M7, RXG12P7, RXG12RD, RXG12JD, RXG12BD, RXG12ED, RXG12ND, RXG12FD, RXG13B7, RXG13E7, RXG13F7, RXG13M7, RXG13P7, RXG13RD, RXG13JD, RXG13BD, RXG13ED, RXG13ND, RXG13FD, relays, maximum surrounding ambient temperature 85 °C.

RGZ E1S48M, contact rated 10 A, 300 V ac, maximum coil voltage 300 V ac, for use with above RXG25B7, RXG25E7, RXG25F7, RXG25M7, RXG25P7, XG25RD, RXG25JD, RXG25BD, RXG25ED, RXG25ND, RXG25FD or RXG21B7, RXG21E7, RXG21F7, RXG21M7, RXG21P7, RXG21RD, RXG21JD, RXG21BD, RXG21ED, RXG21ND, RXG21FD, RXG22B7, RXG22E7, RXG22F7, RXG22M7, RXG22P7, RXG22RD, RXG22JD, RXG22BD, RXG22ED, RXG22ND, RXG22FD, RXG23B7, RXG23E7, RXG23F7, RXG23M7, RXG23P7, RXG23RD, RXG23JD, RXG23BD, RXG23ED, RXG23ND, RXG23FD relays, maximum surrounding ambient temperature 85 °C.

Notes:

1. Suffix may be added for features that do not affect the Certification.
2. Open type devices are Certified as components for use only in other Certified equipment where the suitability of the combination is to be determined by the CSA International.
3. These devices have not been investigated for interrupting current.
4. The wiring terminals are suitable for copper conductors only.
5. The accessory relay sockets are intend for use with the manufacturer's relays and are intended for factory wiring only.

- Relay, open type, models and ratings as following:

Contact rated 10 A or 16 A, 250 V ac, general purpose, SPST, NO contact, or SPDT, NO/NC contact; 10 A, 30 V dc, resistive, SPST, NO contact, or SPDT, NO/NC contact; 1/3 HP, 240 Vac. Coil rated 3 to 110 V dc or 6 to 240 V ac., Cat. No.: RXG12K7, RXG12L7, RXG13K7, RXG13L7, RXG13KD, RXG11K7, RXG11L7, RXG15K7, RXG15L7, RXG15KD.

Contact rated 5 A or 8 A, 250 V ac, general purpose, DPST, NO contact, or DPDT, NO/NC contact; 5 A or 8 A, 30 V dc, resistive, DPST, NO contact, or DPDT, NO/NC contact; 1/6 HP, 240 Vac. Coil rated 3 to 110 V dc or 6 to 240 V ac., Cat. No.: RXG22K7, RXG22L7, RXG23K7, RXG23L7, RXG23KD, RXG21K7, RXG21L7, RXG25K7, RXG25L7, RXG25KD.

Notes:

1. Suffix may be added for features that do not affect the Certification.



Certificate: 2491248
Project: 70111653

Master Contract: 254977
Date Issued: February 6, 2017

2. Open type devices are Certified as components for use only in other Certified equipment where the suitability of the combination is to be determined by the CSA International.
3. These devices have not been investigated for interrupting current.
4. The wiring terminals are suitable for copper conductors only.
5. The accessory relay sockets are intended for use with the manufacturer's relays and are intended for factory wiring only.

APPLICABLE REQUIREMENTS

CSA C22.2 No. 14-10 - Industrial control equipment
CSA C22.2 No. 14-13 - Industrial control equipment

MARKINGS

Company's name and/or CSA File No. 254977, model designation, complete electrical ratings, and the CSA Mark appears on an ink-stamped, non-metallic, adhesive-type label, permanently secured on each device.

The mounting and wiring instruction are provided with each device.

Note: Jurisdictions in Canada may require these markings to be also in French. It is the responsibility of the customer to provide bilingual marking, where applicable, in accordance with the requirements of the Provincial Regulatory Authorities. It is the responsibility of the customer to determine this requirement and have bilingual wording added to the "Markings".



Supplement to Certificate of Compliance

Certificate: 2491248

Master Contract: 254977

*The products listed, including the latest revision described below,
are eligible to be marked in accordance with the referenced Certificate.*

Product Certification History

Project	Date	Description				
70111653	February 6, 2017	<u>Original Report</u>	<u>Submittor Model No.</u>	<u>Listee Model No.</u>		
		2685079	RFT-1CO600LT	RXG12K7		
			RFT-1CO700LT	RXG12L7		
			RFT-1CO600L	RXG13K7		
			RFT-1CO700L	RXG13L7		
			RFT-1CO100L	RXG13KD		
			RFT-1CO600T	RXG11K7		
			RFT-1CO700T	RXG11L7		
			JQX-14FT 1C	RXG15K7		
			JQX-14FT 1C	RXG15L7		
			JQX-14FT 1C	RXG15KD		
			RFT-2CO600LT	RXG22K7		
			RFT-2CO700LT	RXG22L7		
			RFT-2CO600L	RXG23K7		
			RFT-2CO700L	RXG23L7		
			RFT-2CO100L	RXG23KD		
			RFT-2CO600T	RXG21K7		
			RFT-2CO700T	RXG21L7		
			JQX-14FT 2C	RXG25K7		
			JQX-14FT 2C	RXG25L7		
			JQX-14FT 2C	RXG25KD		
			RFT-1CO100LT	RXG12KD		
			RFT-1CO100T	RXG11KD		
			RFT-2CO100LT	RXG22KD		
			RFT-2CO100T	RXG21KD		
		2697901	January 27, 2014	<u>Original Report:</u>	<u>Submittor Models:</u>	<u>Listee Models:</u>
				2685079	RFTICO524T	RXG11B7
	RFTICO548T			RXG11E7		
	RFTICO620T			RXG11F7		
	RFTICO720T			RXG11M7		
	RFT1CO730T			RXG11P7		
	RFT1CO006T			RXG11RD		
	RFT1CO012T			RXG11JD		
	RFT1CO024T			RXG11BD		



Certificate: 2491248
Project: 70111653

Master Contract: 254977
Date Issued: DRAFT, 2017

RFT1CO048T	RXG11ED
RFT1CO060T	RXG11ND
RFT1CO110T	RXG11FD
RFT1CO524LT	RXG12B7
RFT1CO548LT	RXG12E7
RFT1CO620LT	RXG12F7
RFT1CO720LT	RXG12M7
RFT1CO730LT	RXG12P7
RFT1CO006LT	RXG12RD
RFT1CO012LT	RXG12JD
RFT1CO024LT	RXG12BD
RFT1CO048LT	RXG12ED
RFT1CO060LT	RXG12ND
RFT1CO110LT	RXG12FD
RFT1CO524L	RXG13B7
RFT1CO548L	RXG13E7
RFT1CO620L	RXG13F7
RFT1CO720L	RXG13M7
RFT1CO730L	RXG13P7
RFT1CO006L	RXG13RD
RFT1CO012L	RXG13JD
RFT1CO024L	RXG13BD
RFT1CO048L	RXG13ED
RFT1CO060L	RXG13ND
RFT1CO110L	RXG13FD
JQX-14FT 1C	RXG15B7
JQX-14FT 1C	RXG15E7
JQX-14FT 1C	RXG15F7
JQX-14FT 1C	RXG15M7
JQX-14FT 1C	RXG15P7
JQX-14FT 1C	RXG15RD
JQX-14FT 1C	RXG15JD
JQX-14FT 1C	RXG15BD
JQX-14FT 1C	RXG15ED
JQX-14FT 1C	RXG15ND
JQX-14FT 1C	RXG15FD
RFT2CO524T	RXG21B7
RFT2CO548T	RXG21E7
RFT2CO620T	RXG21F7
RFT2CO720T	RXG21M7
RFT2CO730T	RXG21P7
RFT2CO006T	RXG21RD
RFT2CO012T	RXG21JD
RFT2CO024T	RXG21BD
RFT2CO048T	RXG21ED
RFT2CO060T	RXG21ND
RFT2CO110T	RXG21FD



Certificate: 2491248
Project: 70111653

Master Contract: 254977
Date Issued: DRAFT, 2017

RFT2CO524LT	RXG22B7
RFT2CO548LT	RXG22E7
RFT2CO620LT	RXG22F7
RFT2CO720LT	RXG22M7
RFT2CO730LT	RXG22P7
RFT2CO006LT	RXG22RD
RFT2CO012LT	RXG22JD
RFT2CO024LT	RXG22BD
RFT2CO048LT	RXG22ED
RFT2CO060LT	RXG22ND
RFT2CO110LT	RXG22FD
RFT2CO524L	RXG23B7
RFT2CO548L	RXG23E7
RFT2CO620L	RXG23F7
RFT2CO720L	RXG23M7
RFT2CO730L	RXG23P7
RFT2CO006L	RXG23RD
RFT2CO012L	RXG23JD
RFT2CO024L	RXG23BD
RFT2CO048L	RXG23ED
RFT2CO060L	RXG23ND
RFT2CO110L	RXG23FD
JQX-14FT 2C	RXG25B7
JQX-14FT 2C	RXG25E7
JQX-14FT 2C	RXG25F7
JQX-14FT 2C	RXG25M7
JQX-14FT 2C	RXG25P7
JQX-14FT 2C	RXG25RD
JQX-14FT 2C	RXG25JD
JQX-14FT 2C	RXG25BD
JQX-14FT 2C	RXG25ED
JQX-14FT 2C	RXG25ND
JQX-14FT 2C	RXG25FD
SRU05-E	RGZ E1S35M
SRU08-E	RGZ E1S48M

2641926 July 3, 2013

Original Report
2487965

Submittor Model No.

Listee Model No.

SNC05-E-AR	SSLZVA1
SNC05-E-B	SSLZVA2
SNC05-E-CR	SSLZVA3
SNC05-E-DR	SSLZVA4
SNC05-S-AR	SSLZRA1
SNC05-S-B	SSLZRA2
SNC05-S-CR	SSLZRA3
SNC05-S-DR	SSLZRA4



Certificate: 2491248
Project: 70111653

Master Contract: 254977
Date Issued: DRAFT, 2017

2593554	January 22, 2013	<u>Submitter Report</u> 2578324	<u>Model No.</u> SKC08-S SKC14-S	<u>Listee Model No.</u> RXZE2S114S RXZE2S114S
2491248	January 16, 2012	Multiple Listing. <u>Original Report</u> 2487965	<u>Model No.</u> SRC05-E SRC08-E SNC05-E-A SNC05-S-A SNC05-E-B SNC05-S-B SNC05-E-C SNC05-S-C SNC05-E-D SNC05-S-D	<u>Listee Model No</u> RSZ E1S35M RSZ E1S48M RSLZVA1 RSLZRA1 RSLZVA2 RSLZRA2 RSLZVA3 RSLZRA3 RSLZVA4 RSLZRA4