

Versatile Altistart softstart drives

The new ATS22

> June 2010



The ATS22 is the next generation in softstarters.

The devices incorporate an embedded bypass function, meaning fewer components, less cabling and an overall smaller footprint, while offering true three phase control. The ATS22 has a wide power range and benefits from a new HMI design with the 'simply start' concept, which allows 10 basic parameters for adjustment and then simply press start. (A second level of parameters is available for advance fine-tuning).

Other benefits of this next generation in softstarter technology include full starter and motor protections, Fieldbus communication, Modbus and CANopen embedded.

The ATS22 incorporates a simple display, with a reduced number of keys and an easy to use diagnostic function, LED for current status, a trip history and selectable values to monitor.




Product features:

- > Space saving through compact size
- > Panel wiring reduction with simplicity of wiring
- > Energy saving through system efficiencies
- > Provides a solution for customers requiring powers from 7.5 to 315kW
- > Full three phase control
- > Embedded power bypass function
- > Motor protection with electronic overload
- > Easy interface with parameter display and on-board communications

Literature:

- > ATS22 catalogue DIA2ED2090804EN



Material	Description	MPG
ATS22 3Ph 400V Chassis		
ATS22D17Q	ATS22 softstarter 17A 400V	VT
ATS22D32Q	ATS22 softstarter 32A 400V	VT
ATS22D47Q	ATS22 softstarter 47A 400V	VT
ATS22D62Q	ATS22 softstarter 62A 400V	VT
ATS22D75Q	ATS22 softstarter 75A 400V	VT
ATS22D88Q	ATS22 softstarter 88A 400V	VT
ATS22C11Q	ATS22 softstarter 110A 400V	VT
ATS22C14Q	ATS22 softstarter 140A 400V	VT
ATS22C17Q	ATS22 softstarter 170A 400V	VT
ATS22C21Q	ATS22 softstarter 210A 400V	VT
ATS22C25Q	ATS22 softstarter 250A 400V	VT
ATS22C32Q	ATS22 softstarter 320A 400V	VT
ATS22C41Q	ATS22 softstarter 410A 400V	VT
ATS22C48Q	ATS22 softstarter 480A 400V	VT
ATS22C59Q	ATS22 softstarter 590A 400V	VT
ATS22 3Ph 600V Chassis with 200V control		
ATS22D17S6	ATS22 softstarter 17A 600V 220V CI	VT
ATS22D32S6	ATS22 softstarter 32A 600V 220V CI	VT
ATS22D47S6	ATS22 softstarter 47A 600V 220V CI	VT
ATS22D62S6	ATS22 softstarter 62A 600V 220V CI	VT
ATS22D75S6	ATS22 softstarter 75A 600V 220V CI	VT
ATS22D88S6	ATS22 softstarter 88A 600V 220V CI	VT
ATS22C11S6	ATS22 softstarter 110A 600V 220V CI	VT
ATS22C14S6	ATS22 softstarter 140A 600V 220V CI	VT
ATS22C17S6	ATS22 softstarter 170A 600V 220V CI	VT
ATS22C21S6	ATS22 softstarter 210A 600V 220V CI	VT
ATS22C25S6	ATS22 softstarter 250A 600V 220V CI	VT
ATS22C32S6	ATS22 softstarter 320A 600V 220V CI	VT
ATS22C41S6	ATS22 softstarter 410A 600V 220V CI	VT
ATS22C48S6	ATS22 softstarter 480A 600V 220V CI	VT
ATS22C59S6	ATS22 softstarter 590A 600V 220V CI	VT
ATS22 3Ph 600V Chassis with 100V control		
ATS22D17S6U	ATS22 softstarter 17A 600V 110V CI	VT
ATS22D32S6U	ATS22 softstarter 32A 600V 110V CI	VT
ATS22D47S6U	ATS22 softstarter 47A 600V 110V CI	VT
ATS22D62S6U	ATS22 softstarter 62A 600V 110V CI	VT
ATS22D75S6U	ATS22 softstarter 75A 600V 110V CI	VT
ATS22D88S6U	ATS22 softstarter 88A 600V 110V CI	VT
ATS22C11S6U	ATS22 softstarter 110A 600V 110V CI	VT
ATS22C14S6U	ATS22 softstarter 140A 600V 110V CI	VT
ATS22C17S6U	ATS22 softstarter 170A 600V 110V CI	VT
ATS22C21S6U	ATS22 softstarter 210A 600V 110V CI	VT
ATS22C25S6U	ATS22 softstarter 250A 600V 110V CI	VT
ATS22C32S6U	ATS22 softstarter 320A 600V 110V CI	VT
ATS22C41S6U	ATS22 softstarter 410A 600V 110V CI	VT
ATS22C48S6U	ATS22 softstarter 480A 600V 110V CI	VT
ATS22C59S6U	ATS22 softstarter 590A 600V 110V CI	VT
ATS22 Accessories		
VW3G22400	Fan 220V for D17Q, D32Q, D47Q	VY
VW3G22401	Fan 220V for D62Q, D75Q, D88Q, C11Q	VY
VW3G22402	Fan 220V for C14Q, C17Q	VY
VW3G22U400	Fan 110V for D17, D32, D47	VY
VW3G22U401	Fan 110V for D62, D75, D88, C11	VY
VW3G22U402	Fan 110V for C14, C17	VY
VW3G2101	Remote keypad IP54	VY
VW3G2102	Remote keypad IP65	VY
VW3A1008	protection IP65 for remote keypad	VY

For more information please contact us
on 0870 608 8 608 or visit www.schneider-electric.co.uk