


IN EACH PHASE CONNECT TO TAPS	
PRIMARY VOLTS	2-5 %FCBN
480	H1-H4
456	H1-H3
432	H1-H2



TRANSFORMER SPECIFICATIONS:

7.5 KVA 1Ø 60 HZ
 PRIMARY VOLTAGE 480
 SECONDARY VOLTAGE 120/240
 115°C RISE ABOVE
 180°C INSULATION SYSTEM
 APPROXIMATE WEIGHT: 145 LBS
 GUARANTEED SOUND LEVEL: 40 dB
 PRIMARY MAIN BREAKER: HDL26020
 SECONDARY MAIN BREAKER: Q0240
 PANELBOARD INTERIOR: QON112L125PI WITH 10 AVAILABLE SPACES.

- NOTES:
- 1) NEMA 3R ENCLOSURE.
 - 2) MINIMUM FIELD CLEARANCES: 13.00/[330] SIDE AND 21.00/[533] VERTICAL.
 - 3) CONDUIT ENTRY AREA ARE SHOWN SHADED ABOVE, LOCATIONS ARE SIDES AND BOTTOM.
 - 4) SUITABLE FOR SERVICE ENTRANCE.

DUAL DIMENSIONS: INCHES
MILLIMETERS

SEALED MINI POWER-ZONE
 UNIT SUBSTATION
 CATALOG NO MPU7S40F
 1 PHASE, 7.5kVa
 PRIMARY 480, SECONDARY 120/240



DWG# MPU7S40F
NO.