



Main

For independent switching of two loads via make contacts. With integrated bus coupler and screw terminals. For installation on DIN rails EN 50022. The 230 V switch output can be operated with a manual switch.

Complementary

The bus is connected using a bus connecting terminal; a data rail is not necessary. A green LED indicates readiness for operation after the application has been loaded.

KNX software functions:

Operation as break or make contact, delay functions for each channel, staircase lighting function with/without manual OFF function, cut-out warning for staircase lighting function, blocking and additional logic operation or priority control, scenes, status feedback function per channel, central function, comprehensive parameterisation for bus voltage failure and recovery, parameterisable download behaviour.

Nominal voltage: AC 230 V, 50-60 Hz

For each switching contact:

Nominal current: 16 A, $\cos\phi = 0.6$

Incandescent lamps: AC 230 V, max. 3600 W

Halogen lamps: AC 230 V, max. 2500 W

Fluorescent lamps: AC 230 V, max. 2500 VA

Capacitive load: AC 230 V, 16 A, max. 200 μF

Device width: 2.5 modules = approx. 45 mm

Contents: With bus connecting terminal and cable cover.

Colour: light grey

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.