



NOTES:

- PLEASE REFER TO APC INSTALLATION GUIDE.
- △ UTILITY SOURCE MUST BE 2WIRE+GROUND, PROVIDED BY OTHERS.
RECOMMENDED INPUT BRANCH CIRCUIT BREAKER RATINGS
FOR SINGLE PHASE INPUT 60A, FOR TWO PHASE INPUT 30A.
- DASHED LINES BETWEEN UNITS (- - -) REPRESENT CABLING PROVIDED BY OTHERS.
- RECOMMENDED MAXIMUM OUTPUT BREAKER RATING IS 60A. MAXIMUM VA IS LIMITED TO 10kVA.
- INSTALLATION MUST COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL CODES.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF
AMERICAN POWER CONVERSION AND SHALL NOT BE COPIED,
REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR
THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION
FROM APC. THIS DRAWING IS BASED UPON LATEST AVAILABLE
INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

APC
www.apc.com

TITLE:
ISOLATION/STEP-DOWN TRANSFORMER 10kVA
INPUT: 200-240V AC 2PH/400V AC 2PH
OUTPUT: 200-240V AC/120V AC
SYSTEM ONE LINE DIAGRAM

PROJECT: SUBMITTAL DRAWINGS | SHEET 1 OF 1

DWG NO:	APTF10KW01-SD		REV:	0
DRAWN:	BALAMURUGAN	13-SEP-07	ANGLE	
ENGINEER:	K.WHITE/B.BUNGAYAO	13-SEP-07	PROJECTION	
APPROVED:	M.TAVARES	13-SEP-07	NA	