

5


SKU Numbers	Cabinet	WEIGHT in lb/kg	CENTER OF GRAVITY		
			Center of Gravity in Inches [mm]		
			X-Distance	Y-Distance	Z-Distance
GVMSB180KGS	Power Cabinet	1032 / 469	11.81 [300]	37.40 [950]	14.92 [379]
	I/O Cabinet	463 / 210	7.48 [190]	33.46 [850]	9.02 [229]
GVMRB180KGS	Power Cabinet	1032 / 469	11.81 [300]	37.40 [950]	14.92 [379]
	I/O Cabinet	463 / 210	7.48 [190]	33.46 [850]	9.02 [229]
GVMPB180KGS	Power Cabinet	1032 / 469	11.81 [300]	37.40 [950]	14.92 [379]
	I/O Cabinet	463 / 210	7.48 [190]	33.46 [850]	9.02 [229]
GVMSB225KGS	Power Cabinet	1087 / 494	11.81 [300]	37.40 [950]	14.92 [379]
	I/O Cabinet	462 / 210	7.48 [190]	33.46 [850]	9.02 [229]
GVMRB225KGS	Power Cabinet	1087 / 494	11.81 [300]	37.40 [950]	14.92 [379]
	I/O Cabinet	462 / 210	7.48 [190]	33.46 [850]	9.02 [229]
GVMPB225KGS	Power Cabinet	1087 / 494	11.81 [300]	37.40 [950]	14.92 [379]
	I/O Cabinet	462 / 210	7.48 [190]	33.46 [850]	9.02 [229]
GVMMODBCN		306 / 139	7.24 [184]	39.37 [1000]	15.75 [400]
GVMMODBCW		462 / 210	13.74 [349]	39.37 [1000]	15.75 [400]
GVMCBCWUE /		3995 / 1816	17.71 [450] (each cabinet)	39.37 [1000] (each cabinet)	15.75 [400] (each cabinet)
GVMCBC2WUE/		7997 / 3635			
GVMCBC2WUF/		6378 / 2899			
GVMCBC3WUF		9579 / 4354			
GVMSBC450KG/		1069 / 485	29.65 [753]	35.83 [910]	11.61 [295]
GVMSBC675KG		1113 / 505	29.65 [753]	35.63 [905]	12.01 [305]
GVMSBCLB675KG		1290 / 585	38.39 [975]	35.43 [900]	12.01 [305]

Modular battery cartridge

GVMMBTU	66 / 30	(1 STRING =(4)GVMMBTU)
---------	---------	-------------------------

4

TYPICAL REPRESENTATION OF CENTER OF GRAVITY FOR POWER/INPUT OUTPUT/MODULAR BATTERY/ CLASSIC BATTERY/SYSTEM BYPASS CABINET



NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
3. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
- △4. FOR NUMBER OF STRINGS CORRESPONDING TO VARIOUS RUNTIMES REFER TO SUBMITTAL DRAWINGS GVMMODBCW / GVMMODBCN.
- △5. THIS INFORMATION PROVIDES CONSERVATIVE CENTER OF GRAVITY CALCULATION.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE: Galaxy VM PRODUCTS TYPICAL INSTALLATION DETAILS FOR RAISED FLOOR APPLICATION WEIGHT AND CENTER OF GRAVITY DATA

PROJECT: DRAWINGS SHEET 1 OF 5

DWG NO: GVMANCHORING-RF

DRAWN BY: BALAMURUGAN 28-FEB-14

ENGINEER: C ANDERSEN/Z WILLIAM 28-FEB-14

APPROVED BY: M DESHPANDE 28-FEB-14


REV. 0

THIRD


ANGLE

PROJECTION

TYPICAL RAISED FLOOR FRAME DETAILS FOR
SKU : GVMCBCWUE



TYPICAL RAISED FLOOR FRAME DETAILS FOR
SKUs: GVMCBC2WUE /GVMCBC2WUF



NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
3. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
4. RAISED FLOOR FRAME SHOWN IN THIS DRAWING IS TYPICAL.
5. ANCHORING BOLTS ARE NOT SUPPLIED.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE: Galaxy VM
PRODUCTS TYPICAL INSTALLATION DETAILS
FOR RAISED FLOOR APPLICATION
CLASSIC BATTERY CABINETS


PROJECT: DRAWINGS SHEET 3 OF 5

DWG NO: GVMANCHORING-RF REV. 0

DRAWN BY: BALAMURUGAN 28-FEB-14 THIRD

ENGINEER: C ANDERSEN/Z WILLIAM 28-FEB-14 ANGLE

APPROVED BY: M DESHPANDE 28-FEB-14 PROJECTION



BASE TOP VIEW

NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
3. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
4. RAISED FLOOR FRAME SHOWN IN THIS DRAWING IS TYPICAL.
5. ANCHORING BOLTS ARE NOT SUPPLIED.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.




TITLE: Galaxy VM
PRODUCTS TYPICAL INSTALLATION DETAILS
FOR RAISED FLOOR APPLICATION
CLASSIC BATTERY CABINET


PROJECT: DRAWINGS **SHEET:** 4 OF 5

DWG NO: GVMANCHORING-RF	REV. 0
DRAWN BY: BALAMURUGAN	28-FEB-14
ENGINEER: C ANDERSEN/Z WILLIAM	28-FEB-14
APPROVED BY: M DESHPANDE	28-FEB-14
	THIRD ANGLE PROJECTION

TYPICAL RAISED FLOOR FRAME DETAILS FOR
SKUs: GVMSBC450KG /GVMSBC675KG



TYPICAL RAISED FLOOR FRAME DETAILS FOR SKU: GVMSBCLB675KG



NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
3. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
4. RAISED FLOOR FRAME SHOWN IN THIS DRAWING IS TYPICAL.
5. ANCHORING BOLTS ARE NOT SUPPLIED.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE: Galaxy VM
PRODUCTS TYPICAL INSTALLATION DETAILS
FOR RAISED FLOOR APPLICATION
SYSTEM BYPASS CABINETS

PROJECT: DRAWINGS SHEET 5 OF 5

DWG NO: GVMANCHORING-RF REV. 0

DRAWN BY: BALAMURUGAN	28-FEB-14	THIRD
ENGINEER: C ANDERSEN/Z WILLIAM	28-FEB-14	ANGLE
APPROVED BY: M DESHPANDE	28-FEB-14	PROJECTION