



Application Guide
Switches

CAT. NO.

MGU5.241.XX

MGU5.242.XX

MGU5.243.XX

Unica

Thank you for choosing **Schneider Electric** Unica Switches. To ensure proper application of our product, please read through the following information before installation and use.

This application guide applies to the following Unica products.

Cat No.

Description



MGU5.241.XX 16 A X 250 V 1 Gang 2 Way Switch



MGU5.242.XX 16 A X 250 V 2 Gang 2 Way Switch



MGU5.243.XX 16 A X 250 V 3 Gang 2 Way Switch

IMPORTANT NOTE


1. Electrical installation must be carried out by a qualified electrician.
2. Please check your local wiring regulations before actual installation.

SPECIFICATIONS

Voltage	: 250 Vac
Mounting Centre	: 60.3 mm
Compliance	: IEC 60669-1 , SASO GSO IEC 60669-1

WIRING DIAGRAM

2-Way Wiring Diagram




PRODUCT CARE


When cleaning, use a soft damp cloth / tissue to remove dust or dirt. Ensure the product is switched off during cleaning. DO NOT USE caustic cleaning agents.

MOUNTING INSTRUCTION


1. Align and place the Insert on the wall box.



2. Fasten with screws on both sides.



3. Assemble the Cover frame on the Insert, ensuring proper engagement by a clear "click" sound.



UNMOUNTING INSTRUCTION

1. To remove the Cover frame, carefully insert a screwdriver between the Cover frame and the Wall surface. Then twist the screwdriver to dislodge the Cover frame from the Insert.
2. Use the other hand to support and remove the Cover frame.

