



# NKCR7.E164353 - AUXILIARY DEVICES CERTIFIED FOR CANADA

## Auxiliary Devices Certified for Canada

See General Information for Auxiliary Devices Certified for Canada

### SCHNEIDER ELECTRIC INDUSTRIES S A, DBA TELEMECANIQUE

8001 Knightdale Blvd  
Knightdale, NC 27545 USA

E164353

### Investigated to CAN/CSA C22.2 No. 14-13

**Auxiliary Device Enclosed Hand held Remote controller, Control panel base station** Model(s) ZARB followed by 12 or 18, followed by H or W. May be followed by M.

**Auxiliary Device Enclosed Hand held Remote controller, Package of Remote and Control panel base** Model(s) XAR followed by S or SK, followed by 8D, 8L or 12D, followed by 12W, 12H, 18W or 18H.

**Auxiliary Device Enclosed Hand held Remote controller, Remote** Model(s) ZART followed by 8D, 8L or 12D. May be followed by M.

**Auxiliary Device Open type** Model(s) XB5AS84449, XB5AS86449B4

**Auxiliary Device Open type Hand held Remote controller, "Field bus Comm Analog card"** Model(s) ZARCFBA01

**Auxiliary Device Open type Hand held Remote controller, "Network communication card"** Model(s) ZARCIOT01

**Auxiliary Device Open type Tower Light** Model(s) XVGU3SHAG, XVGU3SHAV, XVGU3SWG, XVGU3SWV

### Investigated to CAN/CSA C22.2. No. 14-10

**Auxiliary devices** Model(s) LA4SKC1Y+, LA4SKE1Y+, XPSAXE5120C, XPSAXE5120P, XPSBCE3110C, XPSBCE3110P, XPSBCE3410C, XPSBCE3410P, XPSBCE3710C, XPSBCE3710P

**Auxiliary devices, limit switches** Model(s) XCMU21\*

**Enabling switches, grip type** Model(s) XY2-AU1, XY2-AU2

**LED beacons** Model(s) LRSC followed by -12 or -24, followed by R, Y, G or B, followed by -A.

LRX followed by -12 or -24, followed by R, Y, G or B, followed by -A.

XVR followed by 08 or 10, followed by B or J, followed by 03, 04, 05 and 06, may be followed by any letters (R, O, G, B or C).

**LED Beacons** Model(s) XVR08B03, XVR08B04, XVR08B05, XVR08B06, XVR08J03, XVR08J04, XVR08J05, XVR08J06, XVR10B03, XVR10B04, XVR10B05, XVR10B06, XVR10J03, XVR10J04, XVR10J05, XVR10J06

**LED mini sign towers** Model(s) LEU followed by T or G, followed by WB or blank, followed by -AC, may be followed by W, followed by -1 thru -5.

LOU followed by T, followed by WB or blank, followed by -AC, may be followed by W, followed by -1 thru -5.

XVC followed by 4, followed by M, followed by 1 through 5, may be followed by 5, may be followed by S, may be followed by T, may be followed by any letters (R, O, G, B or C).

XVC followed by 4, followed by M, followed by 1 thru 5, may be followed by 5, may be followed by S, followed by T or blank, may be followed by any letters (R, O, G, B or C).

XVC followed by 6, followed by M, followed by 1 through 5, may be followed by 5, may be followed by S, may be followed by K, may be followed by T, may be followed by any letters (R, O, G, B or C).

XVC4M1, XVC4M15S, XVC4M2, XVC4M25S, XVC4M3, XVC4M35S, XVC4M4, XVC4M45S, XVC4M5, XVC4M55S, XVC6M1, XVC6M15S, XVC6M15SK, XVC6M1K, XVC6M2, XVC6M25S, XVC6M25SK, XVC6M2K, XVC6M3, XVC6M35S, XVC6M35SK, XVC6M3K, XVC6M4, XVC6M45S, XVC6M45SK, XVC6M4K, XVC6M5, XVC6M55S, XVC6M55SK, XVC6M5K

**LED rotating light beacons** Model(s) LRLK may be followed by B, followed by -12 or -24, followed by R, Y, G or B, followed by -A.

LRMT followed by -12, -24, -120 or -230, followed by B, G, R or Y, followed by -A, may be followed by L.

XVR followed by 12, followed by B or J, followed by 03, 04, 05 and 06, may be followed by S, may be followed by any letters (R, O, G, B or C).

XVR followed by 13 followed by B, J, G or M, followed by 03, 04, 05 and 06, may be followed by L, may be followed by any letters (R, O, G, B or C).

XVR12B03, XVR12B03S, XVR12B04, XVR12B04S, XVR12B05, XVR12B05S, XVR12B06, XVR12B06S, XVR12J03, XVR12J03S, XVR12J04, XVR12J04S, XVR12J05, XVR12J05S, XVR12J06, XVR12J06S, XVR13B03, XVR13B03L, XVR13B04, XVR13B04L, XVR13B05, XVR13B05L, XVR13B06, XVR13B06L, XVR13G03L, XVR13G04L, XVR13G05L, XVR13G06L, XVR13J03, XVR13J04, XVR13J05, XVR13J06, XVR13M03L, XVR13M04L, XVR13M05L, XVR13M06L

**LED sign towers** Model(s) UTL followed by B or blank, followed by -AC, followed by W or blank, followed by -1 thru -5.

XVC followed by 1, followed by M, followed by 1 through 5, may be followed by K or SK, may be followed by any letters (R, O, G, B or C).

XVC1M1K, XVC1M1SK, XVC1M2K, XVC1M2SK, XVC1M3K, XVC1M3SK, XVC1M4K, XVC1M4SK, XVC1M5K, XVC1M5SK

**LED tower lights** Model(s) UTL may be followed by B, followed by -24, followed by -1 thru -5.

XVC followed by 1, followed by B, followed by 1 through 5, may be followed by S, followed by K, may be followed by T, may be followed by any letters (R, O, G, B or C).

XVC1B1K, XVC1B1KT, XVC1B1SK, XVC1B1SKT, XVC1B2K, XVC1B2KT, XVC1B2SK, XVC1B2SKT, XVC1B3K, XVC1B3KT, XVC1B3SK, XVC1B3SKT, XVC1B4K, XVC1B4KT, XVC1B4SK, XVC1B4SKT, XVC1B5K, XVC1B5KT, XVC1B5SK, XVC1B5SKT

**Low voltage intelligent motor protection relays** Model(s) LR97D followed by 015, 07, 25 or 38, followed by B, E, F7 or M7.

LT47 followed by 06, 30 or 60, followed by B, E, F7 or M7, followed by S or A.

**MOV, Diode and LED socket modules** Model(s) RUW240BD, RUW241P7, RUW242B7, RUW242P7, RXM021BN, RXM021FP, RXM021RB, RXM040W, RXM041BN7, RXM041FU7

**Overload relays** Model(s) LR3D3, followed by two numbers, may be followed by one letter, may be followed by 3 or 6.

**Safety switches** Model(s) XCS-MP50L\*, XCS-MP59L\*, XCS-MP70L\*, XCS-MP79L\*, XCS-MP80L\*, XCS-MP89L\*

**Tower Light, "Series XVGU"** Model(s) XVGU3SHAG, XVGU3SHAV, XVGU3SWG, XVGU3SWV

## Investigated to CAN/CSA-C22.2 No. 14

**AS-interface fail safe monitors** Model(s) ASiSAFEMON1, ASiSAFEMON1B, ASiSAFEMON2, ASiSAFEMON2B

## Investigated to CAN/CSA-C22.2 No. 60947-4-1 (2nd Ed)

**Coil suppressors** Model(s) LAD4BB may be followed by V and a letter

**Low voltage intelligent motor protection relays** Model(s) LR97D followed by 015, 07, 25 or 38, followed by B, E, F7 or M7

LT47 followed by 06, 30 or 60, followed by B, E, F7 or M7, followed by S or A

**Thermal overload relays** Model(s) LR3-D-32 followed by three digit numbers followed by A65

Model(s) LA7 D followed by 1064, 2064, 3058 or 3064

## Investigated to CAN/CSA-C22.2 No.60947-1-13 and CAN/CSA C22.2 No.60947-5-1-14

**Auxiliary Device Open type** Model(s) DPEAN followed by 01, 02, 04, 10, 11, 13, 20, 22, 31 or 40, may be followed by 6 or 3, may be followed by 5040, may be followed by S (for LADN22 only)

LA1-DC followed by 22, may be followed by 6 or 3

LA1-DN followed by 01, 02, 04, 10, 11, 13, 20, 22, 31 or 40, may be followed by 6 or 3, may be followed by 5040, may be followed by S (for LADN22 only)

LA8DN followed by 01, 02, 04, 10, 11, 13, 20, 22, 31 or 40, may be followed by 6 or 3, may be followed by 5040, may be followed by S (for LADN22 only)

LAD-8N followed by 01, 02, 04, 10, 11, 13, 20, 22, 31 or 40, may be followed by 6 or 3, may be followed by 5040, may be followed by S (for LADN22 only)

LAD-C followed by 01, 02, 04, 10, 11, 13, 20, 22, 31 or 40, may be followed by 6 or 3, may be followed by 5040, may be followed by S (for LADN22 only)

LAD-N followed by 01, 02, 04, 10, 11, 13, 20, 22, 31 or 40, may be followed by 6 or 3, may be followed by 5040, may be followed by S (for LADN22 only)

**Auxiliary contactors** Model(s) CAD ac coil devices, followed by two digit numbers may be followed by one digit number, followed by one or two letters, may be followed by a digit number and maybe followed by S335

**Auxiliary contacts** Model(s) CAD dc coil devices followed by two digit numbers may be followed by one digit number, followed by one or two letters, may be followed by a digit number and maybe followed by S207

**Auxiliary Devices** Model(s) CA2-DN122 with or without Nos. -9, A60, -A65, with or without No. H7

CA2-DN131 with or without Nos. -9, A60, -A65, with or without No. H7

CA2-DN140 with or without Nos. -9, A60, -A65, with or without No. H7

CA3 DN followed by two digits, may be followed by \*6, may be followed by a suffix letter

CA3-DK22 may be followed by a suffix letter may be followed by a suffix letter

GV4ADM1111

**Auxiliary devices** Model(s) LA1SK02, LA1SK11, LA1SK20, LA4SKC1 followed by a letter, LA4SKE1 followed by a letter

**Auxiliary switch contact blocks, open type** Model(s) LA1-DX followed by a two digit number, \*may be followed by 6

LA1-DY followed by a two digit number, \*may be followed by 6

LA1-DZ followed by a two digit number, \*may be followed by 6

**Auxiliary switch units** Model(s) LA1-KN followed by a 2 or 3 digit number, may be followed by 7, M or P

**Coil suppressors** Model(s) LAD4 followed by two or three letters and control wiring kits

**Control relays** Model(s) CA2SK followed by 11 or 20, followed by a letter, followed by a digit number or a letter

CA3SK followed by 11 or 20, followed by a letter, followed by a digit number or a letter

**Control switches** Model(s) CA2-DK22 may be followed by a suffix letter may be followed by a suffix letter

CA2-DN followed by two digits, may be followed by \*6, may be followed by a suffix letter

CA2-KN followed by a 2 or 3 digit number may be followed by one or two letters and a one or two digit number

LA4-K followed by E1B, E1E, E1UG, C1B, C1E, A1U, A1F, or E1FC

**Industrial control relay with mechanically interlocked, alternating contacts** Model(s) CA2SKE20

**input indicator and coil suppressor kit modules** Model(s) LA4-D followed by a letter, followed by a letter or digit number, followed or not by a letter

**Input indicator and coil suppressor kit modules** Model(s) LA9-D0998 followed by two digits, may be followed by \*6, may be followed by a suffix letter

**Magnetic Motor Controllers** Model(s) LA2-D20 may or may not be followed by H7, A65, or H35

LA2-D22 may or may not be followed by H7, A65, or H35

LA2-D24 may or may not be followed by H7, A65, or H35

LA3-D20 may or may not be followed by H7, A65, or H35

LA3-D22 may or may not be followed by H7, A65, or H35

LA3-D24 may or may not be followed by H7, A65, or H35

**Magnetic motor controllers or auxiliary devices** Model(s) LA1-D followed by 04, 10, 11, 13, 20, 22, 40 or 1111, may or may not be followed by H7, A65 or H35

**Magnetically operated control switches** Model(s) CA3-KN

CA4-KN followed by a 2 or 3 digit number, may be followed by one or two letters and one or two digit numbers

CAK followed by a 2 or 3 digit number, followed by one letters and one digit numbers, maybe followed by S335

CAK followed by a 2 or 3 digit number, followed by two letters, maybe followed by S207 or S335

**Mechanical Latching Mechanisms** Model(s) LA6-DK followed by a number, may be followed by 6, followed by one or two letters

LAD6K10 may be followed by a suffix letter may be followed by a suffix letter

**Operator modules** Model(s) GC2DSP, LTMCU, LTMCUC, LTMCUF

**Plug-in devices** Model(s) LAD4-D followed by 3, followed by B, E, S, G, U, R, or N

LAD4-RC followed by 3, followed by B, E, S, G, U, R, or N

LAD4-T followed by 3, followed by B, E, S, G, U, R, or N

LAD4-V followed by 3, followed by B, E, S, G, U, R, or N

**Thermistor protection units for operation with PTC (Positive Temperature Coefficient) thermistor probe** Model(s) LT3

followed by SE00, or SA00, or SM00, followed by one or two letters

**Timer** Model(s) LAD-R0 may be followed by 6 or 3, LAD-T0 may be followed by 6 or 3, LAD-T4 may be followed by 6 or 3

**Timers** Model(s) LAD-R2 may be followed by 6 or 3, LAD-R4 may be followed by 6 or 3, LAD-S2 may be followed by 6 or 3, LAD-T2 may be followed by 6 or 3

## Investigated to CAN/CSA-C22.2 No.60947-1-13 and CAN/CSA-C22.2 No.60947-4-1-14

**Adapter** Model(s) LAD7B10 may be followed by S183 and wiring kits Cat. No. LAD7C1 and LAD7C2

**Adapter base** Model(s) LA7-D

**Ambient compensated and differential electronic thermal overload relays** Model(s) LR9D followed by two or four digit numbers, LR9F

**Ambient compensated and differential thermal overload relays** Model(s) LR3D3 followed by two digit numbers may be followed by a L or blank, may be followed by 3 or 6

LRD3

**Auxiliary Devices** Model(s) LR3-D35 followed by two digit numbers, may be followed by 6

**Contacting Mounting Adaptor** Model(s) LA7-D4054 may be followed by A65

**Low voltage intelligent motor protection relays, "Type TeSys T"** Model(s) LTMEV40 may be followed by 08, 27 or 100, may be followed by M, P, D, C or E, followed by BD or FM. Filter LTM9F for use with TeSys T

LTMR may be followed by 08, 27 or 100, may be followed by M, P, D, C or E, followed by BD or FM. Filter LTM9F for use with TeSys T

**Low voltage intelligent motor protection relays, filters** Model(s) LTM9F (Dedicated for TeSys T)

**Multifunction Motor Protection Relay** Model(s) LT6 followed by POM005FM or POM025FM

**Overload Relay** Model(s) LA7-D09 followed by 54 or 64 followed or not by A60 or A65

**Overload relay adaptors for use with overload relay** Model(s) LR2-D1, LR2-D2, LR2-D3, LR2-D4, LR3-D1, LR3-D2, LR3-D3, LR3-D4

**Thermal overload relay** Model(s) LR2-D25 followed by two digit numbers, may be followed by 6. Adapter base, Cat. No. LA7-D LR2-D35 followed by two digit numbers, may be followed by 6

**Thermal overload relays** Model(s) LR-D15 followed by two digit numbers, may be followed by 6 or S165, may be followed by A1 LR1 followed by 40, 63, 80 followed by three digit numbers may or may not be followed by A65

LR1-09 followed by three digit numbers followed or not by A65

LR1-12 followed by three digit numbers followed or not by A65

LR1-16 followed by three digit numbers followed or not by A65

LR1-25 followed by three digit numbers followed or not by A65

LR1-D followed by 32, followed by three digit numbers followed by A65

LR2 D33 followed by two digit numbers may be followed by 6 or by A66

LR2 D43 followed by two digit numbers may be followed by 6 or by A66

LR2-D13 followed by two digit numbers, may be followed by 6

LR2-D15 followed by two digit numbers, may be followed by 6 or S165, may be followed by A1

LR2-D23 followed by two numbers, may be followed by 6

LR2K followed by -0301, -0302, -0303, -0304, -0305, -0306, -0307, -0308, -0310, -0312, -0314, -0316

LR3 D33 followed by two digit numbers may be followed by 6 or by A66

LR3 D43 followed by two digit numbers may be followed by 6 or by A66

LR3 followed by 09, 12, 16 and 25 followed by three digit numbers followed or not by A65

LR3-D followed by 40, 63, 80 followed by three digit numbers may or may not be followed by A65

LR3-D13 followed by two digit numbers, may be followed by 6

LR3-D15 followed by two digit numbers, may be followed by 6 or S165, may be followed by A1

LR3-D23 followed by two numbers, may be followed by 6

LR3-D25 followed by two digit numbers, may be followed by 6

LR4-D followed by 09, 12, 16 and 25 followed by three digit numbers followed or not by A65

LRD 33 followed by two digit numbers may be followed by 6 or by A66

LRD 43 followed by two digit numbers may be followed by 6 or by A66

LRD followed by two digit numbers followed by L, may be followed by one digit number, may be followed by S183

**Thermal overload relays, adapters** Model(s) LAD7B106 may be followed by S183(#)

**Thermal overload relays, wiring kits** Model(s) LAD7C1(#), LAD7C2(#)

## Investigated to

**Adapters** Model(s) 9065SAD75

**Auxiliary Device Enclosed Accessories for flush kit: Metal bezel, earthplates** Model(s) ZB4 BZ, followed by three digit number.

**Auxiliary Device Enclosed Boots (accessories)** Model(s) ZBD, ZBG, ZBP or ZB2-BP followed by any alphanumeric number.

**Auxiliary Device Enclosed Plastic bezel, plastic bezel label support, plastic brace., Cat. No.** Model(s) ZB5 AZ followed by three digit number.

**Auxiliary Device Open type LED pilot light transcient voltage suppressors subunit** Model(s) ZBZ VG or ZBZ VM

**Open type, Thermal overload relays with ambient compensation** Model(s) LR3D followed by two digit numbers may be followed by one digit number, may be followed by S183(#)

LRD followed by two digit numbers may be followed by one digit number, may be followed by S183 (#)

**Thermal overload relays** Model(s) LR3D followed by two digit numbers followed by L,

# - Investigated to ANSI/UL 60947-1, ANSI/UL 60947-4-1A, CAN/CSA-C22.2 No. 60947-1 and CAN/CSA-C22.2 No. 60947-4-1A

\* - May be followed by additional numbers and letters.

+ - followed by a two or three digit or alphanumeric number

[Click here to view the Colombia Market Access Certification](#)

Trademark and/or Tradename:  , **ARROW** ,  **Telemecanique** ,  ,  ,  , 

Last Updated on 2019-01-29

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"