



DEVICE RATINGS (RECOMMENDED/PRESENT) (DEVICE MAKE-SCHNEIDER ELECTRIC)					
LOCATION	DEVICE ID	DEVICE	RATING		
			@380V	@400V	@415V
FEEDER	UIB	MCCB	3200AF (NW32H2)	3200AF (NW32H2)	3200AF (NW32H2)
CLASSIC BATTERY CABINET	BB	MCCB	600AF		
BATTERY BREAKER CABINET	BB	ACB	4000AF		
BATTERY BREAKER BOX	BB	MCCB	600AF/1000AF		

9

**LEGEND:**  
 --- AC CABLE (PROVIDED BY OTHERS)  
 --- 500VDC CABLE (PROVIDED BY OTHERS)

**NOTES:**

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. REFER TO PRODUCT INSTALLATION DOCUMENTATION FOR SITE PREPARATIONS.
3. DRAWING DEPICTS POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF PHYSICAL LAYOUT. REFER TO MECHANICAL DRAWINGS FOR EQUIPMENT LAYOUT.
4. FINAL SELECTIONS ARE RESPONSIBILITY OF ENGINEER OF RECORDS BASED ON INSTALLED CONDITIONS AND SCC/SELECTIVE CO-ORDINATION/ARC-FLASH ANALYSIS.
- Δ5. INPUT AC SOURCE TO BE 3 WIRE+PE OR 4 WIRE+PE. TN, TT AND IT POWER DISTRIBUTION SYSTEM WITH NO EARTHED LINE CONDUCTORS ARE SUPPORTED.
6. BACK FEED PROTECTION "BF2" BUILT INTO UPS MODULE.
- Δ7. CONFIGURATION APPLICABLE FOR 7 OR 8 NUMBER OF BATTERY STRINGS.
- Δ8. USE OF BBC IS MANDATORY IF NUMBER OF BATTERY STRINGS ARE 3 OR LESS.
- Δ9. CONFIGURATION APPLICABLE IF NUMBER OF BATTERY STRINGS ARE BETWEEN 4 AND 8.  
BATTERY BREAKER RATING (PER STRING) IS 1000A IF NUMBER OF BATTERY STRINGS ARE FROM 4 TO 6.  
BATTERY BREAKER RATING (PER STRING) IS 600A IF NUMBER OF BATTERY STRINGS ARE 7 OR 8.
- Δ10. SINGLE FEED KIT (OH-9161) IS PART OF UPS SKU AND MUST BE INSTALLED FOR THIS CONFIGURATION.
- Δ11. SKUs ARE ETO (ENGINEER TO ORDER) ITEMS.
- Δ12. MAXIMUM INPUT SHORT-CIRCUIT WITHSTAND: I<sub>cw</sub>=100ka RMS SYMMETRICAL.
- Δ13. A READILY ACCESSIBLE BREAKER IS REQUIRED FOR UPSTREAM CURRENT PROTECTION.  
MAXIMUM FAULT CURRENT DISCONNECTION TIME: 46 SECONDS@200% I<sub>n</sub>.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

**Schneider Electric**

**TITLE:** GALAXY VX  
 Input: 380/400/415V AC 3PH 50Hz SINGLE FEED  
 Output: 380/400/415V AC 3PH 50Hz 1000kW  
 1000kW EXPANDABLE TO 1500kW UPS 1MOD W BATT.  
 SYSTEM ONE LINE DIAGRAM

**PROJECT:** DRAWINGS **SHEET** 1 OF 1

**DWG NO:** GVX1000K1500HBC1M1-SD

**DRAWN BY:** BALA **30-MAY-18**

**ENGINEER:** S ANDERSEN **30-MAY-18**

**APPROVED BY:** H N / D M / G S **30-MAY-18**

**REV.** 6

**ANGLE**

**PROJECTION**

**N. A.**

CURRENT DATA IN AMPS @1000KW (SKU# GVX1000K1500HS)			
	@380V	@400V	@415V
NOMINAL INPUT (NO CHARGING)	1601	1519	1463
MAXIMUM INPUT CURRENT**	1771	1702	1638
NOMINAL OUTPUT CURRENT	1519	1443	1391
FULL LOAD BATTERY CURRENT (@ VMIN)	2728		
** NOMINAL INPUT VOLTAGE AND FULL CHARGE.			

CURRENT DATA IN AMPS @1500KW (SKU# GVX1000K1500HS)			
	@380V	@400V	@415V
NOMINAL INPUT (NO CHARGING)	2401	2279	2194
MAXIMUM INPUT CURRENT**	2657	2552	2457
NOMINAL OUTPUT CURRENT	2279	2165	2087
FULL LOAD BATTERY CURRENT (@ VMIN)	4092		
** NOMINAL INPUT VOLTAGE AND FULL CHARGE.			

