

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product
Produit

Uninterruptible Power Supplies

Name and address of the applicant
Nom et adresse du demandeur

American Power Conversion Corp.
85 Rangeway Road Building 2, NORTH BILLERICA MA 01862
UNITED STATES OF AMERICA

Name and address of the manufacturer
Nom et adresse du fabricant

American Power Conversion Corp.
85 Rangeway Road Building 2, NORTH BILLERICA MA 01862
UNITED STATES OF AMERICA

Name and address of the factory
Nom et adresse de l'usine

American Power Conversion CAV 2
Lot 10, Block 16, Phase IV, PEZA, ROSARIO, CAVITE
PHILIPPINES

Note: When more than one factory, please report on page 2
Note: Lorsque il y a plus d'une usine, veuillez utiliser la 2^{ème} page

Additional Information on page 2

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Trademark (if any)
Marque de fabrique (si elle existe)

APC

Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

TMP

Model / Type Ref.
Ref. De type

(see attached model matrix)

Additional information (if necessary may also be reported on page 2)
Les informations complémentaires (si nécessaire, peuvent être indiqués sur la 2^{ème} page)

Class I, max. 40°C ambient temperature

Additional Information on page 2

PUBLICATION

EDITION

A sample of the product was tested and found to be in conformity with
Un échantillon de ce produit a été essayé et a été considéré conforme à la

IEC 62040-1-1(ed.1)

As shown in the Test Report Ref. No. which forms part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de référence qui constitue partie de ce Certificat

1924400-3335-0040/146814

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**

VDE Prüf- und Zertifizierungsinstitut GmbH
VDE Testing and Certification Institute
Zertifizierungsstelle / Certification



E. Biehl

Date: 2011-03-24

Signature:



Ref. Certif. No.

DE1-33490/M3

American Power Conversion CAV 3
Lot 3, Block 14, Phase III, PEZA, ROSARIO, CAVITE
PHILIPPINES

American Power Conversion Corp. BV
Ballybrit Business Park, GALWAY
IRELAND

American Power Conversion Brazil LTDA
Al. Xingu 850, 06455-030 BARUERI - SP
BRAZIL

APC India Pvt. Ltd.
187/3, 188 Jigani Village Jigani Hobli, 562106
BANGALORE
INDIA

APC (Suzhou) UPS Co., Ltd.
No. 339 Suhong Road, Suzhou Industry Park,
215021 Suzhou City, Jiangsu
CHINA

Additional information (if necessary)
Information complémentaire (si nécessaire)

Input: AC 110 / 120 V, max.15A/12A, 50 / 60 Hz

Output: AC 110 / 120 V, max. 15A/12A, max. 750VA/525W, max. 1000VA/700W, max. 1440VA/1008W, 50 / 60 Hz

VDE Prüf- und Zertifizierungsinstitut GmbH
VDE Testing and Certification Institute
Zertifizierungsstelle / Certification

Date: 2011-03-24

Signature:

E. Biehl

Model Matrix:

APC version	IBM version	IBM optional	IBM RoHS	Dell versions
SUA750 SMT750xxxxxxxxxx SMT750RMxxxxxxxxxx (x can be any alphanumeric, +, *, #, _, - or blank)	IBM750	2130-1TX, 74P4902, 74P4901, 39Y8872	IBMR750, 2130-R1X	DLA750
SUA1000 SMT1000xxxxxxxxxx SMT1000RMxxxxxxxxxx (x can be any alphanumeric, +, *, #, _, - or blank)	IBM1000	2130-3TX, 74P4904, 74P4903, 39Y8876	IBMR1000, 2130-R3X	DLA1000
SUA1500 SMT1500xxxxxxxxxx SMT1500RMxxxxxxxxxx (x can be any alphanumeric, +, *, #, _, - or blank)	IBM1500	2130-5TX, 74P4906, 74P4905, 39Y8881	IBMR1500, 2130-R5X	DLA1500