

Product	Socket outlets
Applicant	Schneider Electric Danmark AS Lautrupvang 1 DK 2750 Ballerup Denmark
Manufacturer	Schneider Electric Danmark AS Lautrupvang 1 DK 2750 Ballerup Denmark
Factory	Elda-Eltra Elektrotechnika S.A. ul. Bugno 1 PL-78.400 Szczecinek Poland <input type="checkbox"/> See next page(s)
Ratings	16A 250V
Trade mark	LEXEL
Model / Type Ref.	101414
Principal characteristics	Flush-type two fold. Surface-type two fold and four fold. With shutters. Screw terminals. All colours. Standard sheet III, I and V. IP20, IP21, IP44 Class 0 and I <input type="checkbox"/> See next page(s)
A sample of the product was tested and found to be in conformity with	INST                    NEK-IEC 60884-1:2002;am1;am2 and NEK 502:2006
Replaces	This certificate replaces previous certificate No. P14219135, due to addition of new cover parts.
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	<input checked="" type="checkbox"/> Additional information on page 2
Additional model(s)	<input checked="" type="checkbox"/> See next page(s)

Date of issue 18-08-2015



Nastaran Vadoodi

Certification Department

**Nemko AS**

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway  
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com  
ENTERPRISE NUMBER NO974404532

Product Socket outlets  
Pos. No 1  
Model / Type Ref. 101414-02  
Trade mark (if different from page 1)  
Rating 16A 250V  
Principal characteristics Flush-type two fold. Surface-type two fold and four fold. With shutters. Screw terminals. All colours. Standard sheet III, I and V. IP20, IP21, IP44 Class 0 and I

Product Socket outlets  
Pos. No 2  
Model / Type Ref. 101443  
Trade mark (if different from page 1)  
Rating 16A 250V  
Principal characteristics Flush-type two fold. surface-type two fold and four fold. With shutters. Screw terminals. All colours. Standard sheet III, I and V. IP20, IP21, IP44 Class 0 and I

Product Socket outlets  
Pos. No 3  
Model / Type Ref. 101443-02  
Trade mark (if different from page 1)  
Rating 16A 250V  
Principal characteristics Flush-type two fold. Surface-type two fold and four fold. With shutters. Screw terminals. All colours. Standard sheet III, I and V. IP20, IP21, IP44 Class 0 and I

Additional information The design of the socket-outlet with base type 101414-02 and 101443-02 is consisting of plastic threads in socket for connecting cover to socket base. The design of the socket-outlet base type 101414 and 101443 is consisting of metal threads in socket for connecting cover to socket base.

Date of issue 18-08-2015



Nastaran Vadoodi  
Certification Department

## Attachment to certificate No. P14219135

Order No. 292938

Socket	Terminals	IP-class	Mounting	Earth-type*	Design	Included parts (Cover parts etc.)
<b>Flush-type</b>						
101414 101414-02 101443 101443-02 (Flush-type 1, 2)	Screw or Screwless terminals - Bridge connections / Through connections	20	Flush-type with metal or composite fixing frame semi flush	S	Trend	101392
				U		100465
				S		100464
				S	Decora	101433
				U		101063
				U		101284
				S	Senso	101281
				C		101283
				U		101425
				S	Artic	101426
				S		101515
				U	Neutral	101516
				S		Unica
				U	101528	
				C	101535	
				F	101530	
				S	101531	
				U	101532	
				C	101533	
				F	101534	
				S	Robust	101610
				F	Alombard	74220
				S	Lyx	100813
				S	Trend HP	100818
				U		100819
				S	Van-Geel	100969
				S	Trend-Solid	101548, 101549, 101550***
101414 101414-02 (Flush type 3)			Composite fixing frame and metal fixing frame semi flush	S	Actic Decor	101554 + outer frame***
				S	Renova	101367, 101364
				U		101365, 101364
				F		101470, 101364
				C		101471, 101364
101414 101414-02 (Flush type 4)			Metal fixing	S	Decora	101133
				S	Round	101155

## Attachment to certificate No. P14219135

Order No. 292938

			frame 110368				
101443 101443-02 (Flush type 3)			Full-flush with metal fixing frame	S	Trend	101578	
				S	Trend Solid	101580, 101548, 101549***	
				S	Artic	101581	
				S	Artic Decor	101582 + outer frame***	
				S	Exxact	BBV35087	
				S	M - SMART	NHA44968	
101443/101443- 02 (Flush type 1,2)			Semi flush with metal fixing frame	S	Exxact	BBV35087	
				U		S1B13009	
				S		S1B13009 with pilot lamp	
				S		S1A67876	
				U		BBV42385	
				S		BBV42390	
				S		M - SMART	NHA44972
				S		SYS - DESIGN	NHA50152
				S		SYS - ARTEC	

Surface-type						
101414* 101414-02*	Screw or Screwless terminals - Bridge connections / Through connections	20	Surface type	U	Trend	100542
				U	Quick-Rot 4W Exxact	101439
				U	ROT	100780
		21		S	Quick-Rot	100571
				S		100541
				S	Quick-Rot 4W Exxact	101083
				U	Artic	101428
				S	Artic	101429
				S	ROT	100779
101414 101414-02 101443* 101443-02		44	Flush-type  Surface- type	S	Aqua-Trend  Exxact NOTE 1	101165
101443-02		20	Surface- type	S	Robust	101604

## Attachment to certificate No. P14219135

Order No. 292938

NOTE 1 : Available with lockable lids.

* = Socket types		**= (Earth-type):	
Flush types		U	Without earth contact
1	Metallic "Standard"	S	With side-earth contact
2	Composite "Standard"	F	With pin-earth contact
3	Composite "Renova"	C	With pin earth contact (CZ)
4	Metallic "Diagonal"		
5	Metallic "Full-Flush"		
Surface types		***=Changeable frames	
1	2-way with backplate	101549 may be exchanged by metal plate or glass plate	
2	2-way without backplate	Outer frame consisting of backframe of plastic, and a plate of plastic, metal or glass	
3	4-way composition		
<p>Flush-type socket-outlet types 1, 2 and 4 and surface-type socket-outlet types 1, 2 and 3 comply with the requirement for unintentional contact with test finger to current-carrying parts according to EN 60529 (IPX0B)</p>			