

CERTIFICATE

Issued to:
Applicant:
American Power Conversion Holding Inc.
3F, No. 205, Sec. 3, Beixin Road,
Xindian District,
231 New Taipei City, Taiwan

Licensee:
Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road,
Houjie Town,
523963 Dongguan Guangdong, China

Product : Plug-in Surge Adaptor
Trade name(s) : APC by Schneider Electric
Type(s)/model(s) : PME1W-GR, PME1W-KR, PME1W-RS, PME1W-SP, PME1WB-GR,
PME1WB-KR, PME1WB-RS, PME1WB-SP, PME1WU2-GR, PME1WU2-KR,
PME1WU2-RS, PME1WU2-SP, PME1WU2B-GR, PME1WU2B-KR,
PME1WU2B-RS and PME1WU2B-SP

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard IEC 60884-1:2002, IEC 60884-1:2002/A1:2006, IEC 60884-1:2002/A2:2013, IEC 60884-2-5:2017, DIN VDE 0620-2-1:2016, DIN VDE 0620-2-1:2016/A1:2017, EN 62368-1:2014, EN 62368-1:2014/A11:2017, EN 61643-11:2012 and EN 61643-11:2012/A11:2018
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 2025917


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR certification agreement and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 6 August 2019 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 35-109435

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



S.L. Vasylyeva
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Plug-in Surge Adaptor
Trade name(s)	: APC by Schneider Electric
Type(s)/model(s)	: PME1W-GR, PME1W-KR, PME1W-RS, PME1W-SP, PME1WB-GR, PME1WB-KR, PME1WB-RS, PME1WB-SP, PME1WU2-GR, PME1WU2-KR, PME1WU2-RS, PME1WU2-SP, PME1WU2B-GR, PME1WU2B-KR, PME1WU2B-RS and PME1WU2B-SP
Rated current	: 16 A MAX.
Rated voltage	: 220-250 V~
Earthing	: with earthing contacts
Description	: body of thermoplastic material

Product data – type PME1WB-GR, PME1WB-KR, PME1WB-RS, PME1WB-SP, PME1W-GR, PME1W-KR, PME1W-RS and PME1W-SP

Design	: provided with AC Surge Protective Device
--------	--

Product data – type PME1WU2B-GR, PME1WU2B-KR, PME1WU2B-RS, PME1WU2B-SP, PME1WU2-GR, PME1WU2-KR, PME1WU2-RS and PME1WU2-SP

Design	: provided with AC Surge Protective Device and dual port USB-Charger
USB charger	: 5 Vdc 2,4 A (total output)

TESTS**Test requirements**

IEC 60884-1:2002
IEC 60884-1:2002/A1:2006
IEC 60884-1:2002/A2:2013
IEC 60884-2-5:2017
DIN VDE 0620-2-1:2016
DIN VDE 0620-2-1:2016/A1:2017
EN 62368-1:2014
EN 62368-1:2014/A11:2017
EN 61643-11:2012
EN 61643-11:2012/A11:2018

Test result

The test results are laid down in DEKRA test file 435248700, 435249100 and 605006300.

Additional information

The list of components is laid down at test report 4352487.50.

Conclusion

The examination proved that all requirements were met.

Factory location

Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road,
Houjie Town,
523963 Dongguan Guangdong, China