

CERTIFICATE

Issued to:

Applicant:

American Power Conversion Holdings Inc., Taiwan
Branch
5F., No. 189, Sec. 2, Jiuzong Rd., Neihu Dist.,
11494 Taipei City, Taiwan

Licensee:

Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road, Houjie
Town,
523963 Dongguan, Guangdong, China

Product : Multiple portable socket-outlets with SPD(s)
Trade name(s) : APC or APC by Schneider Electric
Type(s)/model(s) : PM6-GR, PM6-RS, PM8-GR, PM8-RS, PMF83VT-GR, PMF83VT-RS

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard(s) IEC 60884-1:2002, IEC 60884-1:2002/A1:2006, IEC 60884-1:2002/A2:2013, IEC 60884-2-7:2011, IEC 60884-2-7:2011/A1:2013, EN 61643-11:2012, EN 61643-11:2012/A11:2018, EN 61643-21:2001, EN 61643-21:2001/A1:2009, EN 61643-21:2001/A2:2013, NEN 1020:2019, NEN-IEC 60884-1:2019, NEN-IEC 60884-1:2019/A1:2019, NEN-IEC 60884-1:2019/A2:2019, DIN VDE 0620-2-1:2016 and DIN VDE 0620-2-1:2016/A1:2017
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 2025917


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 20 January 2022 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 4318493.01 REV.1

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



K. Lin
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Multiple portable socket-outlets with SPD(s)
Trade name(s)	: APC or APC by Schneider Electric
Type(s)/model(s)	: PM6-GR, PM6-RS, PM8-GR, PM8-RS, PMF83VT-GR and PMF83VT-RS
Rated current	: 16 A
Rated voltage	: 250 V~
Rated power	: MAX. 2500 W (Limited to 10 A by means of circuit breaker)
Earthing	: with side earthing-contacts
Design	: non-rewirable, with shutters
Standard sheet	: III of NEN 1020
Applied flexible cord	: H05VV-F 3G1,0 mm ²
Certification mark	: complies with the requirements
Cord termination	: soldered connection
Description	: body of thermoplastic material

Product data – type PM6-GR

Design	: 6-fold, provided with circuit-breaker, two-pole rocker switch and AC Surge Protective Device
--------	--

Product data – type PM6-RS

Design	: 6-fold, provided with circuit-breaker, two-pole rocker switch and AC Surge Protective Device
--------	--

Product data – type PM8-GR

Design	: 8-fold, provided with circuit-breaker, two-pole rocker switch and AC Surge Protective Device
--------	--

Product data – type PM8-RS

Design	: 8-fold, provided with circuit-breaker, two-pole rocker switch and AC Surge Protective Device
--------	--

Product data – type PMF83VT-GR

Design	: 8-fold, provided with circuit-breaker, two-pole rocker switch, AC Surge Protective Device, TV and Phone Surge Protective Devices
--------	--

Product data – type PMF83VT-RS

Design	: 8-fold, provided with circuit-breaker, two-pole rocker switch, AC Surge Protective Device, TV and Phone Surge Protective Devices
--------	--

TESTS**Test requirements**

IEC 60884-1:2002
IEC 60884-1:2002/A1:2006
IEC 60884-1:2002/A2:2013
IEC 60884-2-7:2011

IEC 60884-2-7:2011/A1:2013
EN 61643-11:2012
EN 61643-11:2012/A11:2018
EN 61643-21:2001
EN 61643-21:2001/A1:2009
EN 61643-21:2001/A2:2013
NEN 1020:2019
NEN-IEC 60884-1:2019
NEN-IEC 60884-1:2019/A1:2019
NEN-IEC 60884-1:2019/A2:2019
DIN VDE 0620-2-1:2016
DIN VDE 0620-2-1:2016/A1:2017

Test result

The test results are laid down in DEKRA test file 610944100, 611076400, 437751600.

Additional information

The product also complies with Clause 10.5 of DIN VDE 0620-2-1:2021, BS EN 61643-11:2012 + A11:2018, BS EN 61643-21:2001 + A1:2009 + A2:2013.

Remark: The type nos. PM6-RS, PM8-RS, PMF83VT-RS are technically identical to the products PM6-GR, PM8-GR, PMF83VT-GR. The last two letters indicate the country code only.

This certificate replaces certificate No. 4318493.01 which we hereby declare invalid.

The list of components is laid down in test report 4377516.50/51, 6109441.50, 6110764.51/52.

Conclusion

The examination proved that all requirements were met.

Factory location

Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road, Houjie Town,
523963 Dongguan, Guangdong, China