



Ref. Certif. No.

SI-1443IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEMESYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC**CB TEST CERTIFICATE
CERTIFICAT D'ESSAI OC**Product
Produit

AC/DC Adaptor (Plug in Power Supply)

Name and address of the applicant
Nom et adresse du demandeurGlobTek Inc.
Corporate Headquarters, 186 Veterans Dr Northvale, NJ
07647 / USAName and address of the manufacturer
Nom et adresse du fabricant

Same as above

Name and address of the factory
Nome et adresse de l'usine

See annex to the cetificate

Ratings and principal characteristics
Valeurs nominales et caractéristiques principalesInput: 100-240 Va.c.; 50-60 Hz; 0,6 A
Output: See annex to the certificateTrademark (if any)
Marque de fabrique (si elle existe)

GlobTek

Model / Type Ref.
Ref. De typeGT-41062-18VV-X.X-TZ
See annex to the certificateAdditional information (if necessary)
Information complémentaire (si nécessaire)

/

PUBLICATION**EDITION**A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 60950-1:2001

1stAs shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

T223-0006/06

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**Slovenski institut za kakovost in meroslovje
Slovenian Institute of Quality and Metrology
Tržaška c. 2, SI-1000 Ljubljana, Slovenia

Date: 2006-01-09

Signature: Vojko Koron

RATINGS AND PRINCIPAL CHARACTERISTICS:

<u>Model:</u>	<u>Output Ratings</u>	<u>Transformer</u>	<u>Class</u>
GT-41062-1805-X.X	5Vdc / 3,2A	XF00209	II
GT-41062-1806-X.X	6Vdc / 3,0A	XF00209	II
GT-41062-1807-X.X	7Vdc / 2,57A	XF00209	II
GT-41062-1809-X.X	9Vdc / 2,0A	XF00168	II
GT-41062-1812-X.X	12Vdc / 1,5A	XF00168	II
GT-41062-1815-X.X	15Vdc / 1,2A	XF00168	II
GT-41062-1818-X.X	18Vdc / 1,0A	XF00169	II
GT-41062-1820-X.X	20Vdc / 0,9A	XF00169	II
GT-41062-1824-X.X	24Vdc / 0,75A	XF00169	II
GT-41062-1805-X.X-T2	5Vdc / 3,6A	XF00210	II
GT-41062-1806-X.X-T2	6Vdc / 3,0A	XF00210	II
GT-41062-1807-X.X-T2	7Vdc / 2,57A	XF00210	II
GT-41062-1809-X.X-T2	9Vdc / 2,0A	XF00211	II
GT-41062-1812-X.X-T2	12Vdc / 1,5A	XF00211	II
GT-41062-1815-X.X-T2	15Vdc / 1,2A	XF00211	II
GT-41062-1818-X.X-T2	18Vdc / 1,0A	XF00212	II
GT-41062-1820-X.X-T2	20Vdc / 0,9A	XF00212	II
GT-41062-1824-X.X-T2	24Vdc / 0,75A	XF00212	II
GT-41062-1805-X.X-T3	5Vdc / 3,6A	XF00210	I
GT-41062-1806-X.X-T3	6Vdc / 3,0A	XF00210	I
GT-41062-1807-X.X-T3	7Vdc / 2,57A	XF00210	I
GT-41062-1809-X.X-T3	9Vdc / 2,0A	XF00211	I
GT-41062-1812-X.X-T3	12Vdc / 1,5A	XF00211	I
GT-41062-1815-X.X-T3	15Vdc / 1,2A	XF00211	I
GT-41062-1818-X.X-T3	18Vdc / 1,0A	XF00212	I
GT-41062-1820-X.X-T3	20Vdc / 0,9A	XF00212	I
GT-41062-1824-X.X-T3	24Vdc / 0,75A	XF00212	I
GT-41062-1805-X.X-T3A	5Vdc / 3,6A	XF00210	I
GT-41062-1806-X.X-T3A	6Vdc / 3,0A	XF00210	I
GT-41062-1807-X.X-T3A	7Vdc / 2,57A	XF00210	I
GT-41062-1809-X.X-T3A	9Vdc / 2,0A	XF00211	I
GT-41062-1812-X.X-T3A	12Vdc / 1,5A	XF00211	I
GT-41062-1815-X.X-T3A	15Vdc / 1,2A	XF00211	I
GT-41062-1818-X.X-T3A	18Vdc / 1,0A	XF00212	I
GT-41062-1820-X.X-T3A	20Vdc / 0,9A	XF00212	I
GT-41062-1824-X.X-T3A	24Vdc / 0,75A	XF00212	I



Slovenski inštitut za
kakovost in meroslovje
Slovenian Institute of
Quality and Metrology

ANNEX to CB Test Certificate No.: SI-1443

page 2 of 2

DESCRIPTION OF THE MODEL NAME:

41062: represents the Series Code

"VV" denotes Rated Output Voltage


"X.X" denotes voltage differentiator

"TZ" = plug connection, where "2" is C8; "3" is C14, "3A" is C6 and model without "TZ" is for direct plug in connection

LIST OF FACTORY LOCATIONS:

GLOBTEK INC.,

Ljubljana, 2006-01-09



Slovenski inštitut za
kakovost in meroslovje
Slovenian Institute of
Quality and Metrology
Vilavska 2, 1000 Ljubljana
Slovenija / Slovenia

Podpis pooblaščenega osebe / Authorized signature