


CATALOG NUMBER	A		B		C	
	IN	MM	IN	MM	IN	MM
NC26S	26.12	663	17.70	436	6.16	156
NC32S	32.12	816	23.70	602	9.16	233
NC38S	38.12	968	29.70	754	12.16	309
NC44S	44.12	1121	35.70	907	15.16	385
NC50S	50.12	1273	41.70	1059	18.16	461
NC56S	56.12	1425	47.70	1212	21.16	537
NC62S	62.12	1578	53.70	1364	24.16	614
NC68S	68.12	1730	59.70	1516	27.16	690
NC74S	74.12	1883	65.70	1669	30.16	766
NC80S	80.12	2035	71.70	1821	33.16	842
NC26F	27.52	699	17.70	436	6.16	156
NC32F	33.52	851	23.70	602	9.16	233
NC38F	39.52	1004	29.70	754	12.16	309
NC44F	45.52	1156	35.70	907	15.16	385
NC50F	51.52	1309	41.70	1059	18.16	461
NC56F	57.52	1461	47.70	1212	21.16	537
NC62F	63.52	1613	53.70	1364	24.16	614
NC68F	69.52	1766	59.70	1516	27.16	690
NC74F	75.52	1918	65.70	1669	30.16	766
NC80F	81.52	2071	71.70	1821	33.16	842
NC86S	86.12	2187	77.70	1974	36.16	918
NC86F	87.52	2071	77.70	1974	36.16	918
NC35S	35.12	892	26.70	678	10.66	271
NC35F	36.52	928	26.70	678	10.66	271
NC41S	41.12	1044	32.70	831	13.66	347
NC41F	42.52	1080	32.70	831	13.66	347
NC92S	92.12	2340	83.70	2126	39.16	995



DUAL DIMENSIONS: INCHES
MILLIMETERS

PANELBOARD COVER
TRIM TYPE 1
SURFACE/FLUSH



DWG# PWFDS-SYTI-0164
NO.