

China RoHS Declaration

Obligations defined in the "Administrative Measures for the Restriction of Hazardous Substances in Electric Appliances and Electronic Products" called China RoHS and released January 21st 2016

Dear customer,

In accordance with the requirements of China RoHS, you will find below information regarding the compliance of Schneider Electric products.

Please note that the information contained herein may be subject to change as new data becomes available or as regulations evolve. Schneider Electric will only disclose to its customers the information mandated/required by applicable regulations (for China RoHS, Hazardous Substance Table and EFUP only).

Shall you need any further information or have specific questions (eg. related to phased out products), our [Customer Care Centers](#) will support you. Please Note: You can find more information about Schneider Electric environmental commitment on [this webpage](#).

尊敬的客户：

根据中国 RoHS 的相关要求，以下是关于施耐德电气产品合规性的信息。

请注意，随着新数据的出现或法规的变化，本文所包含的信息可能会有所变动。施耐德电气仅向客户披露适用法规所要求的信息（对于中国 RoHS，仅限于有害物质表和环保使用期限 EFUP）。

如果您需要更多信息或有具体问题（例如关于已淘汰产品），我们的客户服务中心将为您提供支持。

请注意：您可以在本网页上了解更多关于施耐德电气环境承诺的信息。

Best Regards,

Vanessa MILER-FELS

VP Environment



这些产品的环保使用期为

The Environment Friendly Using Period for this products is: 20

组件名称 Component name	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr6+)	多溴化联苯 (PBB)	多溴联苯醚 (PBDE)	邻苯二甲酸二(2-乙基)己酯 (DEHP)	邻苯二甲酸丁基苄酯 (BBP)	邻苯二甲酸二正丁酯 (DBP)	邻苯二甲酸二异丁酯 (DIBP)
CPTB PLUG 5mm NA FMLE MCSCW 3 1X3 PA	X	O	O	O	O	O	O	O	O	O
CPTB PLUG 5mm NA FMLE MCSCW 4 1X4 PA	X	O	O	O	O	O	O	O	O	O
Crystal 25MHz 30ppm 50ppm 16pF	X	O	O	O	O	O	O	O	O	O
Diode Schottky 100V 10A TO220AB	X	O	O	O	O	O	O	O	O	O
Diode Schottky 100V 2A	X	O	O	O	O	O	O	O	O	O

DO214ACSM A										
Diode Schottky 200V 10A D2PAK	X	O	O	O	O	O	O	O	O	O
Diode Schottky 60V 2A DO214ACSM A	X	O	O	O	O	O	O	O	O	O
Diode STD Recovery 600V 1A DO214ACSM A	X	O	O	O	O	O	O	O	O	O
Diode Ultrafast 200V 2A DO214AASMB	X	O	O	O	O	O	O	O	O	O
Diode Ultrafast 400V 2A DO214AASMB	X	O	O	O	O	O	O	O	O	O
ESD-TVS BI 1 33V 36.7V 41V 54V 600W	X	O	O	O	O	O	O	O	O	O
ESD-TVS UNI 1 18V 20V 23.1V 30.6V 600W	X	O	O	O	O	O	O	O	O	O
	X	O	O	O	O	O	O	O	O	O

ESD-TVS UNI 1 24V 26.7V 29.5V 38.9V 600W										
ESD-TVS UNI 1 5V 6.4V 7.14V 10.5V 600W	X	O	O	O	O	O	O	O	O	O
ESD-TVS UNI 1 6V 6.67V 7.37V 10.3V 400W	X	O	O	O	O	O	O	O	O	O
FUS 5A TD SMD 6.1x2.7	X	O	O	O	O	O	O	O	O	O
MOSFET N 100V 7mohm 78A DFN56 5	X	O	O	O	O	O	O	O	O	O
MOSFET P -60 V 180 mohm -2.6 A SOT223 4	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0201 240ohm 1% 200ppm/°C 0.0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 0ohm 0% 999ppm 0.063W	X	O	O	O	O	O	O	O	O	O
	X	O	O	O	O	O	O	O	O	O

RES THK FLM 0402 1.96kohm 1% 100ppm/°C 0										
RES THK FLM 0402 1000ohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 100kohm 1% 100ppm 0.063	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 100ohm 1% 100ppm/°C 0.0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 10kohm 1% 100ppm 0.063W	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 10kohm 1% 100ppm 0.125W	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 10ohm 1% 100ppm/°C 0.06	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 11kohm 1% 100ppm/°C	X	O	O	O	O	O	O	O	O	O

0.0										
RES THK FLM 0402 13kohm 1% 100ppm 0.063W	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 1Mohm 1% 100ppm/°C 0.06	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 2.2kohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 2.49kohm 1% 100ppm/°C 0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 20kohm 1% 100ppm/°C 0.0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 220kohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 220ohm 1% 100ppm/°C 0.0	X	O	O	O	O	O	O	O	O	O
	X	O	O	O	O	O	O	O	O	O

RES THK FLM 0402 22kohm 1% 100ppm/°C 0.0										
RES THK FLM 0402 22ohm 1% 100ppm/°C 0.06	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 3.01kohm 1% 100ppm/°C 0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 3.6kohm 1% 100ppm 0.063	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 33.2kohm 1% 100ppm 0.06	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 33kohm 1% 100ppm 0.063W	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 390ohm 1% 100ppm/°C 0.0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 39kohm 1% 100ppm	X	O	O	O	O	O	O	O	O	O

0.063W										
RES THK FLM 0402 4.7kohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 4.87kohm 1% 100ppm/°C 0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 43.2kohm 1% 100ppm/°C 0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 470ohm 1% 100ppm/°C 0.0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 47kohm 1% 100ppm/°C 0.0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 49.9ohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 499ohm 1% 100ppm/°C 0.0	X	O	O	O	O	O	O	O	O	O
	X	O	O	O	O	O	O	O	O	O

Schneider Electric Industries SAS
 Postal address:
 Le Hive, 35 rue Joseph Monier - CS 30323
 F-92506 Rueil Malmaison Cedex
 Phone: +33 (0)4 76 57 60 60
<http://www.schneider-electric.com>

Legal information:
 Société par actions simplifiée au capital de 896,313,776 €
 954 503 439 rcs Nanterre - code APE : 2712Z
 Siret : 954 503 439 01719
 n°ident. TVA : FR 04 954 503 439

RES THK FLM 0402 5.1kohm 1% 100ppm/°C 0.										
RES THK FLM 0402 5.76kohm 1% 100ppm 0.06	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 6.2kohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 680ohm 1% 100ppm/°C 0.0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 82.5kohm 1% 100ppm 0.06	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 82kohm 1% 100ppm 0.063W	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 9.09kohm 1% 100ppm 0.06	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0402 9.1kohm 1% 100ppm	X	O	O	O	O	O	O	O	O	O

0.063										
RES THK FLM 0402 9.53kohm 1% 100ppm 0.06	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0603 10ohm 1% 100ppm/°C 0.1W	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0603 15.4kohm 1% 100ppm/°C 0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0603 15ohm 1% 100ppm 0.1W	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0603 3.48kohm 1% 100ppm/°C 0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0603 30kohm 1% 100ppm 0.1W	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0603 4.99kohm 1% 100ppm/°C 0	X	O	O	O	O	O	O	O	O	O
	X	O	O	O	O	O	O	O	O	O

RES THK FLM 0603 470kohm 1% 100ppm/°C 0.										
RES THK FLM 0805 1000ohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0805 13.7kohm 1% 100ppm/°C 0	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0805 150kohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 0805 2.2kohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 1206 10ohm 1% 200ppm 0.25W	X	O	O	O	O	O	O	O	O	O
RES THK FLM 1206 6.8kohm 1% 100ppm/°C 0.	X	O	O	O	O	O	O	O	O	O
RES THK FLM 1206 68ohm	X	O	O	O	O	O	O	O	O	O

1% 100ppm/°C 0.5W										
RES THK FLM 2010 1.5ohm 1% 500ppm/°C 0.7	X	O	O	O	O	O	O	O	O	O
RES THK FLM 2010 1Mohm 1% 100ppm 0.5W	X	O	O	O	O	O	O	O	O	O
RES THN FLM 0402 100kohm 0.1% 25ppm	X	O	O	O	O	O	O	O	O	O
RES THN FLM 0402 24.9kohm 0.1% 25ppm 0.0	X	O	O	O	O	O	O	O	O	O
RES THN FLM 0603 47kohm 0.1% 25ppm/° C 0.	X	O	O	O	O	O	O	O	O	O
Standoff THRU HO RD - M3 x 15mm STL	X	O	O	O	O	O	O	O	O	O
Timing RTC 3V 85°C SO 8	X	O	O	O	O	O	O	O	O	O

The following hazardous substance disclosure table applies to SXWASP3XX10001

○ : 表示该有害物质在该部件所有均质材料中的含量均不超出电器电子产品有害物质限制使用国家标准要求 (Limit requirements of GB/T 26572-2025).

O: Indicates that the content of this hazardous substance in all homogenous materials for this part does not exceed the requirements of the national standard for the restriction of the use of hazardous substances in electrical and electronic products (Limit requirements of GB/T 26572-2025).

× : 表示该有害物质至少在该部件的某一均质材料中含量超出电器电子产品有害物质限制使用国家标准要求 (Limit requirements of GB/T 26572-2025).

X: Indicates that the content of this hazardous substance in at least one of the homogenous materials used for this part exceeds the requirements of the national standard for the restriction of the use of hazardous substances in electrical and electronic products (Limit requirements of GB/T 26572-2025).

以上未列出的部件，表明其有害物质含量均不超出电器电子产品有害物质限制使用国家标准要求