



5386



UKCA Type Examination Certificate Number: **0120/SGS0137**

Schneider Electric Pvt. Ltd

Hosur Main Road
12A, Attibele Industrial Area
Neralur (PO), Bangalore -562107
India

Instrument Identification

PM5331, PM5341, PM5111

Polyphase, Active Import/ Export (kWh), Transformer Operated, Electricity Meter

Instrument Traceable Number

0120/ SGS0137

has been assessed and certified as meeting the requirements of

Measuring Instruments Regulations 2016 as amended

on Active electrical energy meters, Schedule 1, Module B

It is certified that the manufacturer's technical design and specimen for the above instrument has been examined and, based on the evidence submitted, it is considered that the instrument conforms to the requirements of Annex V, as referenced in the UK Measuring Instruments Regulations 2016, as amended

This certificate must be used in conjunction with a certificate covering the product verification as required in Schedule 1, Module D or Schedule 1, Module F

This certificate is valid until 16th October 2023

Issue 1

Certification is based on report number(s)

Certification is based on report number(s)

EMA180141/MID Issue 6 Issued 18th November 2014, EMA223584/1 Issued 7th June 2016

EMA225834/1/PM5341 Issued 21st June 2016

EMA299735/1

Authorised Signature

Rae Jackson

Contact Address

SGS United Kingdom Limited, Approved Body 0120
Units 12A & 12B, South Industrial Estate, Bowburn, Durham, DH6 5AD, UK
t +44 (0)191 377 2000 f +44 (0)191 377 2020 www.sgs.com




	UKCA Type Examination Certificate Number:	
	0120/SGS0137	
	Issue Number: 1	Dated: 4 th April 2022

1. Technical Data

Manufacturer	Schneider Electric
Meter Type	PM5331, PM5341, PM5111
Voltage Rating (U_n)	63.5/110-277/480V
Current Rating ($I_{min} - I_{ref} (I_{max})$)	0.05-5(6)A
Frequency (F_n)	50Hz
Active Accuracy Class (kWh)	C(kWh)
Type of circuit	3P4W, 3P3W
Temperature Range	-25°C to +70°C
Software/ Firmware Version No's	For HW Ver. A1 (Not in production) Model: PM5111 OS - New: v1.6.5 (Checksum 0x13 E1); Earlier: 1.6.4 / 1.6.2 / 1.6.0 / 1.4.7 / 1.2.2 / 1.2.1 Model: PM5331 OS - New: v1.6.5 (Checksum 0x CB 6B); Earlier: 1.6.4 / 1.6.2 / 1.6.0 / 1.4.7 / 1.2.2 / 1.2.1 Model: PM5341 OS - New: v1.6.5 (Checksum 0x D0 6F); Earlier: 1.6.4 / 1.6.2 / 1.6.0 / 1.4.7 / 1.2.2 For HW Ver. B1/B2 (In production) Model: PM5111 OS - New: v2.4.3 (Checksum 0x 50 90); Earlier: 2.4.2 / 2.2.2 / 2.2.1 / 2.2.0 Model: PM5331 OS - New: v2.4.3 (Checksum 0x 76 B0); Earlier: 2.4.2 / 2.2.2 / 2.2.1 / 2.2.0 Model: PM5341 OS - New: v2.4.4 (Checksum 0x A2 B5); Earlier: 2.4.3 / 2.2.3 / 2.2.1 / 2.2.0
Identification Location	LCD
Bill Of Materials No's	PM5111 Power Supply - HRB46840 or NVE50463 Controller - HRB47633 or EAV69955 or NVE50496 PM5331 Power Supply - HRB46838 or NVE50412 Controller - HRB44401 or EAV69954 or NVE50494 PM5341 Power Supply - HRB46838 or NVE50412 Controller - EAV69953 or NVE50488
IP Rating	IP54 Front Display Meter body not rated, must be fitted in an IP51 Enclosure
Insulation Protective Class	Class II
LED Pulse Constant	10,000imp/ kWh
Impulse Voltage Rating	6kV
AC Voltage Rating	4kV
Main Cover Sealing Type	Tamper evident self-locking rivet
Integrity of meter	Inaccessible without breaking seals
Intended Location of the Meter	Indoor
Type of Register	LCD
Terminal Arrangement(s)	DIN
Location of Manufacturers Address	Associated Documents


	UKCA Type Examination Certificate Number:	
	0120/SGS0137	
	Issue Number: 1	Dated: 4 th April 2022

2. Photograph of Meter and Sealing Plan



	UKCA Type Examination Certificate Number:	
	0120/SGS0137	
	Issue Number: 1	Dated: 4 th April 2022

Main Cover Seal



	UKCA Type Examination Certificate Number:	
	0120/SGS0137	
	Issue Number: 1	Dated: 4 th April 2022

3. Examples of Nameplates



	UKCA Type Examination Certificate Number:	
	0120/SGS0137	
	Issue Number: 1	Dated: 4 th April 2022

4. Calculation of the composite error/ MPE

During the type approval examination the influence factors for temperature, frequency and voltage are determined per load point. The table below represents the sum of the square values per load, determined via the following formula:-

$$\delta e(T, U, f) = \sqrt{(\delta e^2(T, I, \cos\phi) + \delta e^2(U, I, \cos\phi) + \delta e^2(f, I, \cos\phi))}$$

where

$\delta e(T, I, \cos\phi)$ = Additional error due to variation of the temperature at the same load

$\delta e(U, I, \cos\phi)$ = Additional error due to variation of the voltage at the same load

$\delta e(f, I, \cos\phi)$ = Additional error due to variation of the frequency at the same load

		Influence Factors For Temperature, Frequency & Voltage						
Current	PF Cos	-25°C	-10°C	5°C	30°C	40°C	55°C	70°C
Imin	1.0	0.42	0.28	0.16	0.18	0.26	0.36	0.38
Itr	1.0	0.42	0.27	0.16	0.19	0.28	0.40	0.46
10Itr	1.0	0.32	0.20	0.14	0.19	0.24	0.31	0.32
Imax	1.0	0.31	0.20	0.14	0.19	0.25	0.32	0.49
Itr	0.5ind	0.62	0.43	0.29	0.29	0.44	0.68	0.84
10Itr	0.5ind	0.61	0.41	0.27	0.30	0.42	0.60	0.76
Imax	0.5ind	0.60	0.40	0.27	0.30	0.41	0.61	0.76
Itr	0.8cap	0.42	0.22	0.13	0.18	0.24	0.30	0.30
10Itr	0.8cap	0.21	0.13	0.12	0.16	0.19	0.20	0.16
Imax	0.8cap	0.21	0.13	0.12	0.16	0.19	0.20	0.16
Line 1								
Itr	1.0	0.43	0.33	0.17	0.19	0.31	0.37	0.46
10Itr	1.0	0.36	0.24	0.20	0.23	0.28	0.34	0.35
Imax	1.0	0.34	0.21	0.17	0.21	0.23	0.34	0.34
Itr	0.5ind	0.64	0.42	0.36	0.29	0.36	0.59	0.82
10Itr	0.5ind	0.60	0.37	0.30	0.34	0.41	0.56	0.75
Imax	0.5ind	0.62	0.37	0.26	0.28	0.40	0.60	0.72
Line 2								
Itr	1.0	0.46	0.22	0.18	0.18	0.26	0.36	0.46
10Itr	1.0	0.23	0.16	0.13	0.18	0.23	0.27	0.29
Imax	1.0	0.27	0.17	0.14	0.19	0.25	0.31	0.29
Itr	0.5ind	0.63	0.34	0.23	0.33	0.40	0.71	0.78
10Itr	0.5ind	0.56	0.37	0.22	0.24	0.37	0.54	0.68
Imax	0.5ind	0.57	0.35	0.23	0.25	0.31	0.55	0.72
Line 3								
Itr	1.0	0.35	0.22	0.13	0.23	0.25	0.44	0.52
10Itr	1.0	0.41	0.24	0.17	0.21	0.30	0.37	0.38
Imax	1.0	0.38	0.23	0.14	0.20	0.26	0.32	0.36
Itr	0.5ind	0.66	0.48	0.26	0.33	0.53	0.81	1.09
10Itr	0.5ind	0.73	0.47	0.37	0.39	0.53	0.76	0.86
Imax	0.5ind	0.70	0.36	0.30	0.32	0.39	0.69	0.87

	UKCA Type Examination Certificate Number:	
	0120/SGS0137	
	Issue Number: 1	Dated: 4 th April 2022

5. Annex of Variants

Product Variant Identification Details:

Type Designation	Description of meter
------------------	----------------------

Model -	Description
PM5111 -	Polyphase, Active Import/ Export (kWh), Transformer Operated, RS485 with 1 Digital Output
PM5331 -	Polyphase, Active Import/ Export (kWh), Transformer Operated, RS485 with 2 Digital Outputs, 2 Digital Inputs, 2 Electromechanical Relays
PM5341 -	Polyphase, Active Import/ Export (kWh), Transformer Operated, RS485 with 2 Digital Outputs, 2 Digital Inputs, 2 Electromechanical Relays, Ethernet

Modifications to the meter(s) described according to approval No. **0120/SGS0137** must be notified to the issuing body to confirm the meter(s) continuing compliance to the relevant pattern approval standard(s).

	UKCA Type Examination Certificate Number:	
	0120/SGS0137	
	Issue Number: 1	Dated: 4 th April 2022

6. Document Revision History

Issue	Date	Comments
1	04/042022	Initial Issue

This document is issued by the Company subject to its General Conditions for Certification Services, available on request or accessible at <https://www.sgs.com/en/terms-and-conditions/general-conditions-for-certification-services-english>

Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful, and offenders may be prosecuted to the fullest extent of the law.

Unless otherwise stated the results shown in this test report refer only to the sample(s) tested *and such sample(s) are retained for 28 days only.*

END OF CERTIFICATE