


**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**T36EN13G6S**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Max. Continuous Current Rating: 600V / 90A  
 Certifications: UL Listed, CSA, CE  
 RoHS: Yes  
 Termination Method: Power Line: Screw Clamp, Power Load: Lug, Control Circuit: Screw Clamp  
 Weight (lbs): 15.1  
 Power Line Size (AWG): #14 - 1/0  
 Power Load Size (AWG): #14 - 1/0  
 Control Wire Size (AWG): #12 - #16  
 Thermal Overload Type: Motor Logic Solid State  
 Thermal Overload Trip Class: Class 10/20 Selectable  
 Mounting: Panel

**Specification:**

Description: TeSys N Sz 3 open starter, 3 pole, 120 VAC, Separate Control  
 Type: FVNR  
 Voltages Code: G6 at 120VAC  
 Control Type: Separate Control  
 Coil Consumption: Inrush 660 VA  
 Sealed 55 VA

**Three Phase**

200V	230V	460V	575V
25 HP	30 HP	50 HP	50 HP