



5386

SGS

UKCA Type Examination Certificate Number: **0120/SGS0131/R1**

Schneider Electric Pvt. Ltd

Hosur Main Road
12A, Attibele Industrial Area
Neralur (PO), Bangalore -562107
India

Instrument Identification:
PM5561, PM5661, PM5761

Polyphase, Active Import/ Export (kWh), Transformer Operated, Auxiliary power supply, RS485, Dual Ethernet, 2 digital outputs, 4 digital inputs

Instrument Traceable Number
0120/SGS0131

has been assessed and certified as meeting the requirements of

Measuring Instruments Regulations 2016 (as amended) on Active electrical energy meters, Schedule 1B, Module B

It is certified that the manufacturer's technical design and specimen for the above instrument has been examined and, based on the evidence submitted, it is considered that the instrument conforms to the requirements of Schedule 1E, as referenced in the UK Measuring Instruments Regulations 2016, as amended

This certificate must be used in conjunction with a certificate covering the product verification as required in Schedule 1B, Module D or Schedule 1B, Module F

Certification is based on report number(s): EMA175578 MID Issue 1 dated 7th February 2014,
EMA175578/TR50579 dated 4th April 2018, EMA287946/1 dated 1st April 2021,
EMA297438/1 dated 24th December 2021
ERTL(N)2020/20IQ0102 dated 4th December 2020
EMA299734/1

This certificate is valid until 4th December 2033
Issue 4

Authorised Signature

Lewis Lee

Contact Address
SGS United Kingdom Limited, Approved Body 0120
Units 12A & 12B, South Industrial Estate, Bowburn, Durham, DH6 5AD, UK
t +44 (0)191 377 2000 f +44 (0)191 377 2020 www.sgs.com





UKCA Type Examination Certificate Number:

0120/SGS0131/R1

Issue Number: 4

Dated: 14th April 2026**Technical Data**

Manufacturer	Schneider Electric
Meter Type	PM5561, PM5661, PM5761
Voltage Rating (<i>Un</i>)	3 x 230/400V
Current Rating (<i>I_{min}</i> – <i>I_{ref}</i> (<i>I_{max}</i>))	Ansi 0.05-5(10)A MID 0.05-5(6)A
Frequency (<i>Fn</i>)	50Hz
Active Accuracy Class (<i>kWh</i>)	C (kWh)
Type of circuit	3p3w, 3p4w
Temperature Range	-25°C to +70°C
PM5561 Software/ Firmware Version No's	OS: V10.0.0.0 or V10.1.0.0 or V10.3.2 or V10.5.2.0 or V10.6.Z or V10.6.4 or V10.7.1 or V10.7.3 or 10.8.2 or 12.0.4 or 12.1.0, 12.2.0 or 12.4.0 or 12.4.1 or 12.5.0
PM5561 CRC Checksum No's	9A66 or 61CD or 9C84 or 7196 or 1496 or 1CE3 or A29D or 148A or 0x4B24 or 0xB20D or 0xB904 or 0x4288 or 0x0D8A, or 0xE591 or 0x8630 or 0xEE6A or 0x671C
PM5661 Software/ Firmware Version No's	OS: V11.0.0 or V14.0.1 or V14.02
PM5661 CRC Checksum No's	0x8456 or 0x9692 or 0x368D
PM5761 Software/ Firmware Version No's	OS: V11.0.0 or V14.0.1 or V14.02
PM5761 CRC Checksum No's	0x1169 or 0x4C2D or 0x5ECE
BoM No's	PM5561 Comms HRB13411 PM5561 Main-Analog_HRB13412 PM5561 PSU R63230-828-50/MFR93449 PM5561 Digital IO R63230-831-50 PM5661 PM5761 COMM CARD GDE33229 PM5661 PM5761 Main Analog MFR94350 PM5661 PM5761 PSU MFR93449 PM5661 PM5761 RCM IO MFR13113
IP Rating	IP54 Front Display Meter body not rated, must be fitted in an IP51 Enclosure
Insulation Protective Class	Class II
LED Pulse Constant	10,000imp/kWh
Impulse Voltage Rating	6kV
AC Voltage Rating	4kV
Main Cover Sealing Type	Tamper evident self-locking rivet
Integrity of meter	Inaccessible without breaking seals
Intended Location of the Meter	Indoor
Type of Register	LCD
Terminal Arrangement(s)	DIN
Location of Manufacturers Address	Associated Documents

SGS

UKCA Type Examination Certificate Number:

0120/SGS0131/R1

Issue Number: 4

Dated: 14th April 2026

**1. Photograph of Meter and Sealing Plan
(PM5561 shown for representation. Similar plan available on PM5661 & PM5761)**



Main Cover Seal




Voltage Terminal Cover Sealing Point

Auxiliary Terminal Cover Sealing Point



Current Terminal Cover Sealing Points

2. Examples of Nameplates



3. Calculation of the composite error/ MPE

During the type approval examination the influence factors for temperature, frequency and voltage are determined per load point. The table below represents the sum of the square values per load, determined via the following formula:-

$$\delta e(T, U, f) = \sqrt{(\delta e^2(T, I, \cos\phi) + \delta e^2(U, I, \cos\phi) + \delta e^2(f, I, \cos\phi))}$$

where

$\delta e(T, I, \cos\phi)$ = Additional error due to variation of the temperature at the same load

$\delta e(U, I, \cos\phi)$ = Additional error due to variation of the voltage at the same load

$\delta e(f, I, \cos\phi)$ = Additional error due to variation of the frequency at the same load

Influence Factors for temperature, frequency and voltage								
Current	PF Cos	-25°C	-10°C	5°C	30°C	40°C	55°C	70°C
lmin	1.0	0.23	0.16	0.09	0.02	0.06	0.11	0.13
ltr	1.0	0.24	0.17	0.10	0.02	0.05	0.10	0.15
10ltr	1.0	0.21	0.15	0.08	0.03	0.08	0.13	0.20
lmax	1.0	0.23	0.17	0.10	0.04	0.07	0.13	0.22
ltr	0.5ind	0.11	0.10	0.08	0.09	0.11	0.15	-0.32
10ltr	0.5ind	0.12	0.08	0.06	0.06	0.07	0.08	-0.10
lmax	0.5ind	0.51	0.08	0.05	0.09	0.05	0.05	0.05
ltr	0.8cap	0.11	0.26	0.14	0.06	0.12	0.22	0.36
10ltr	0.8cap	0.35	0.24	0.13	0.05	0.12	0.22	0.33
lmax	0.8cap	0.10	0.25	0.13	0.05	0.12	0.20	0.31
L1								
ltr	1.0	0.20	0.14	0.08	0.03	0.05	0.10	0.14
10ltr	1.0	0.20	0.14	0.08	0.02	0.06	0.11	0.21
lmax	1.0	0.41	0.15	0.09	0.02	0.06	0.13	0.24
ltr	0.5ind	0.15	0.11	0.09	0.10	0.12	0.20	-0.34
10ltr	0.5ind	0.13	0.09	0.07	0.08	0.09	0.09	-0.12
lmax	0.5ind	0.12	0.09	0.06	0.06	0.06	0.07	0.07
L2								
ltr	1.0	0.24	0.16	0.09	0.03	0.08	0.13	0.18
10ltr	1.0	0.23	0.17	0.09	0.03	0.08	0.15	0.20
lmax	1.0	0.25	0.22	0.10	0.03	0.07	0.15	0.25
ltr	0.5ind	0.07	0.08	0.07	0.06	0.08	0.12	-0.28
10ltr	0.5ind	0.11	0.08	0.06	0.06	0.06	0.06	-0.10
lmax	0.5ind	0.09	0.06	0.05	0.05	0.05	0.07	0.13
L3								
ltr	1.0	0.25	0.17	0.10	0.03	0.07	0.12	0.13
10ltr	1.0	0.21	0.15	0.08	0.04	0.08	0.15	0.16
lmax	1.0	0.23	0.16	0.09	0.03	0.08	0.15	0.19
ltr	0.5ind	0.08	0.08	0.07	0.08	0.09	0.12	-0.27
10ltr	0.5ind	0.13	0.10	0.07	0.08	0.08	0.10	-0.13
lmax	0.5ind	0.11	0.08	0.06	0.02	0.07	0.09	-0.05



UKCA Type Examination Certificate Number:

0120/SGS0131/R1

Issue Number: 4

Dated: 14th April 2026

4. Annex of Variants


Product Variant Identification Details:

Type Designation

Description of meter

PM5561	Polyphase, Active Import/ Export (kWh), Transformer Operated, Auxiliary power supply, RS485, Dual Ethernet, 2 digital outputs, 4 digital inputs, ground module METSEPM55GRMD (optional)
PM5661	Polyphase, Active Import / Export (kWh), Transformer Operated, Auxiliary power supply, RS485, Dual Ethernet, 2 digital outputs, 2 digital inputs, 2 residual current measurement inputs, ground module METSEPM55GRMD (optional)
PM5761	Polyphase, Active Import / Export (kWh), Transformer Operated, Auxiliary power supply, RS485, Dual Ethernet, 2 Digital Outputs, 2 digital inputs, 2 residual current measurement inputs, sag-swell detection & waveform capture, ground module METSEPM55GRMD (optional)

Modifications to the meter(s) described according to approval No. **0120/SGS0131/R1** must be notified to the issuing body to confirm the meter(s) continuing compliance to the relevant pattern approval standard(s).

	UKCA Type Examination Certificate Number:	
	0120/SGS0131/R1	
	Issue Number: 4	Dated: 14 th April 2026

5. Document Revision History

Issue	Date	Comments
1	05/12/2023	Initial Issue
2	25/06/2025	New software versions 12.1.0, 12.2.0 and 12.4.0 and CRC's 0x0D8A, 0xE591 and 0x8630 for model PM5561.
3	14/11/2025	New software version 12.4.1 and CRC 0xEE6A for model PM5561
4	14/04/2026	New software version 12.5.0 and CRC 0x671C for model PM5561

This document is issued by the Company subject to its General Conditions for Certification Services, available on request or accessible at <https://www.sgs.com/en/terms-and-conditions/general-conditions-for-certification-services-english>

Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful, and offenders may be prosecuted to the fullest extent of the law.

Unless otherwise stated the results shown in this test report refer only to the sample(s) tested *and such sample(s) are retained for 28 days only.*

END OF CERTIFICATE